

PHILIPS

Bulb

LED

9W-65W

E26

Soft White

046677541019



Soft white light, no compromise on light quality

Philips LED lusters provide a beautiful, soft white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this light bulb is the perfect replacement for your incandescent lusters..

Choose for a sustainable solution

- Saves up to 80% Energy

Light beyond illumination

- A simple LED for everyday use
- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 13 cm
- Weight: 0.075 kg
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: ANSI
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 650 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 125 mA
- Efficacy: 72 lm/W

Packaging information

- EAN: 046677541019
- EOC: 541010
- Product title: 9BR30/LED/827/FR/P/ND 6/1FB

Power consumption

- Power factor: >0.5
- Voltage: 120 V
- Wattage: 9 W
- Wattage equivalent: 65 W

Product dimensions & weight

- Length: 13 cm

Rated values

- Rated beam angle: 110 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated luminous flux: 650 lumen
- Rated power: 9 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677541019
- Net weight: 0.095 kg
- Gross weight: 0.115 kg
- Height: 13.100 cm
- Length: 9.100 cm
- Width: 9.100 cm
- Material number (12NC):
929001947903



Issue date: 2023-11-08
Version: 0.76

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com