







220V 240V





















	Lumen (lm)	CCT (K)	Power (W)	Driver	UGR	Through-wiring	kg
DN470C	— 2000 — — –	830	16.4	PSU	22	– Yes	1.3
			16.2	DIA-VLC			
		840	16.4	PSU			
			16.2	DIA-VLC			
DN471C		830	16.4	PSU	- 19		
			16.2	DIA-VLC			
		840	16.4	PSU			
			16.2	DIA-VLC			

## 0 5




Dimensions in mm











- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- This luminaire is not suitable for use as emergency lighting.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
- Clean with dry cloth.


















## © 2020 Signify Holding.

All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding. The Netherlands