

Since
1894

**BEAUTIFUL LIGHT,
BUILT TO PERFORM**

 **MAZDA**

GREAT LIGHT SOLID DESIGN

4



Bulbs

8




Candles &
Lustre

12



Spots

16



Tubes

There's an art to creating a quality lighting scheme that exceeds your customers' expectations - without going over their budget. Now you can master it beautifully with MAZDA's new portfolio of LED lamps.

QUALITY WHEN IT COUNTS

The MAZDA name has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting. From retail and residential projects to commercial and industrial installations, they have been developed to meet the challenging requirements of a wide range of lighting applications.

We've designed our range using the very latest LED technology, from classic bulbs and elegant candles to hand-working tubes and directional spots. So you can promise your customers excellent performance and efficiency from their lighting installation, with instant energy savings.

They'll love the light quality too. With a choice of lumens, color temperatures and beam angles, our high quality LED solutions create the perfect ambience for every space. Light that's designed to create a great first impression, with value that lasts.



MASTERING LIGHT SINCE 1894

MAZDA has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting:

- Engineered for performance
- Up to 25,000 hours reliable lifetime
- Superb light quality
- Save up to 85% energy

MAZDA LED BULBS

INSTANT ENERGY SAVINGS

With MAZDA's range of LED bulbs you can create exactly the right ambience.

- Classic bulb shape
- Frosted or clear finish
- 2700K or 4000K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy



MZD LED 40W E27 840
A60 ND

12NC: **929001252232**
EAN1: **3139188161436**

6 WATT > **40** WATT **4000 K**
500 lm



MZD LED 40W E27 827
A60 ND

12NC: **929001252132**
EAN1: **3139188161412**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W A60 E27
CDL FR ND

12NC: **929001365032**
EAN1: **3139188162266**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 60W A60 E27
827 FR ND

12NC: **929001313532**
EAN1: **3139188161450**

9 WATT > **60** WATT **2700 K**
806 lm



MZD LED 60W A60 B22
WW FR ND RF

12NC: **929001365432**
EAN1: **3139188162969**

9 WATT > **60** WATT **2700 K**
806 lm



MZD LED 60W A60 E27
CDL FR ND

12NC: **929001365332**
EAN1: **3139188162327**

9 WATT > **60** WATT **6500 K**
806 lm



MZD LED 60W A60 E27
840 FR ND

12NC: **929001365232**
EAN1: **3139188161474**

9 WATT > **60** WATT **4000 K**
806 lm



MZD LED 75W A60 E27
827 FR ND

12NC: **929001365532**
EAN1: **3139188161498**

11 WATT > **75** WATT **2700 K**
1055 lm



MZD LED 75W A60 E27
840 FR ND

12NC: **929001365632**
EAN1: **3139188161511**

10 WATT > **75** WATT **4000 K**
1055 lm



MZD LED 75W A60 E27
865 FR ND

12NC: **929001359132**
EAN1: **3139188162488**

10 WATT > **75** WATT **6500 K**
1055 lm

MAZDA LED BULBS INSTANT ENERGY SAVINGS





MZD LED 100W E27 827
A67 FR ND



MZD LED 100W A60 E27
CDL FR ND

12NC: **929001252932**
EAN1: **3139188161535**

14 **100** **2700 K**
WATT WATT 1521 lm

12NC: **929001359232**
EAN1: **3139188162501**

14 **100** **6500 K**
WATT WATT 1521 lm

80
CRI

220-240 Vac

15,000h

non dimmable

Product type	Energy Consumption	Color temperature	Lumen output	12NC	EAN1
		K	lm		
MZD LED 40W E27 840 A60 ND 1CT/6	6	4000	500	929001252232	3139188161436
MZD LED 40W E27 827 A60 ND 1CT/6	6	2700	470	929001252132	3139188161412
MZD LED 40W A60 E27 CDL FR ND 1CT/6 G3	5	6500	470	929001365032	3139188162266
MZD LED 60W A60 E27 827 FR ND 1CT/6 G3	9	2700	806	929001313532	3139188161450
MZD LED 60W A60 B22 WW FR ND RF 1BC G3 1CT/6	9	2700	806	929001365432	3139188162969
MZD LED 60W A60 E27 CDL FR ND 1CT/6 G3	9	6500	806	929001365332	3139188162327
MZD LED 60W A60 E27 840 FR ND 1CT/6 G3	9	4000	806	929001365232	3139188161474
MZD LED 75W A60 E27 827 FR ND 1CT/6 G3	11	2700	1055	929001365532	3139188161498
MZD LED 75W A60 E27 840 FR ND 1CT/6 G3	10	4000	1055	929001365632	3139188161511
MZD LED 75W A60 E27 CDL FR ND 1CT/6 G3	10	6500	1055	929001359132	3139188162488
MZD LED 100W E27 827 A67 FR ND 1CT/6	14	2700	1521	929001252932	3139188161535
MZD LED 100W A60 E27 CDL FR ND 1CT/6 G3	14	6500	1521	929001359232	3139188162501

MAZDA LED CANDLES & LUSTRE DESIGNED FOR ATMOSPHERE

With an elegant design and frosted finish, our LED candles also offer significant energy savings.

- Elegant shape
- Frosted finish
- Warm white light
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy



MZD LED 25W B35 E14
827 CL ND

12NC: **929001253132**
EAN1: **3139188162709**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W E14 827
B35 FR ND

12NC: **929001253032**
EAN1: **3139188161351**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W B35 E14
CW FR ND

12NC: **929001359432**
EAN1: **3139188162549**

3 WATT **25** WATT **4000 K**
250 lm



MZD LED 25W B35 E14
CDL FR ND

12NC: **929001388832**
EAN1: **3139188162563**

3 WATT **25** WATT **6500 K**
250 lm



MZD LED 25W P45 E27
827 CL ND

12NC: **929001253532**
EAN1: **3139188162761**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W P45 E14
827 CL ND

12NC: **929001253432**
EAN1: **3139188162747**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W E27 827
P45 FR ND

12NC: **929001253332**
EAN1: **3139188161399**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W E14 827
P45 FR ND

12NC: **929001253232**
EAN1: **3139188161375**

4 WATT **25** WATT **2700 K**
250 lm



MZD LED 25W P45 E14
CW FR ND

12NC: **929001263832**
EAN1: **3139188162822**

4 WATT **25** WATT **4000 K**
250 lm



MZD LED 25W P45 E14
CDL FR ND

12NC: **929001388932**
EAN1: **3139188162587**

3 WATT **25** WATT **6500 K**
250 lm



MZD LED 40W B35 E14
WW FR ND

12NC: **929001253632**
EAN1: **3139188162723**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W B35 E14
CW FR ND

12NC: **929001263732**
EAN1: **3139188162884**

5 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W B35 E14
CDL FR ND

12NC: **929001389032**
EAN1: **3139188162686**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E27
WW FR ND

12NC: **929001253832**
EAN1: **3139188162808**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E14
WW FR ND

12NC: **929001253732**
EAN1: **3139188162785**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E27
CW FR ND

12NC: **929001264032**
EAN1: **3139188162860**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E14
CW FR ND

12NC: **929001263932**
EAN1: **3139188162846**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E27
CDL FR ND

12NC: **929001389232**
EAN1: **3139188162624**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E14
CDL FR ND

12NC: **929001389132**
EAN1: **3139188162600**

5 WATT > **40** WATT **6500 K**
470 lm

A⁺
EEI label**80**
CRI

220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy Consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 25W B35 E14 827 CL ND 1CT/10	B35	4	15000	2700	250	35 x 106	929001253132	3139188162709
MZD LED 25W E14 827 B35 FR ND 1CT/10	B35	4	15000	2700	250	35 x 106	929001253032	3139188161351
MZD LED 25W B35 E14 CW FR ND 1CT/10 G3	B35	3	15000	4000	250	37 x 109	929001359432	3139188162549
MZD LED 25W B35 E14 CDL FR ND 1CT/10 G3	B35	3	15000	6500	250	37 x 109	929001388832	3139188162563
MZD LED 25W P45 E27 827 CL ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253532	3139188162761
MZD LED 25W P45 E14 827 CL ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253432	3139188162747
MZD LED 25W E27 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253332	3139188161399
MZD LED 25W E14 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253232	3139188161375
MZD LED 25W P45 E14 CW FR ND 1CT/10	P45	4	15000	4000	250	45 x 90	929001263832	3139188162822
MZD LED 25W P45 E14 CDL FR ND 1CT/10 G3	P45	3	15000	6500	250	45 x 82	929001388932	3139188162587

A⁺
EEI label**80**
CRI

220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy Consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 40W B35 E14 WW FR ND 1CT/10	B35	6	15000	2700	470	35 x 106	929001253632	3139188162723
MZD LED 40W B35 E14 CW FR ND 1CT/10	B35	5	15000	4000	470	37 x 109	929001263732	3139188162884
MZD LED 40W B35 E14 CDL FR ND 1CT/10 G3	B35	5	15000	6500	470	37 x 109	929001389032	3139188162686
MZD LED 40W P45 E27 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 90	929001253832	3139188162808
MZD LED 40W P45 E14 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 90	929001253732	3139188162785
MZD LED 40W P45 E27 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 80	929001264032	3139188162860
MZD LED 40W P45 E14 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 85	929001263932	3139188162846
MZD LED 40W P45 E27 CDL FR ND 1CT/10 G3	P45	5	15000	6500	470	45 x 77	929001389232	3139188162624
MZD LED 40W P45 E14 CDL FR ND 1CT/10 G3	P45	5	15000	6500	470	45 x 82	929001389132	3139188162600



MZD LED 50W GU10 827
36D ND 1CT/10

12NC: **929001250432**
EAN1: **313918816125200**

4.7 WATT > **50** WATT **2700 K**
345 lm



MZD LED 50W GU10 840
36D ND 1CT/10

12NC: **929001247032**
EAN1: **313918816266200**

4.7 WATT > **50** WATT **4000 K**
380 lm



MZD LED 50W GU10 865
36D ND 1CT/10

12NC: **929001259132**
EAN1: **313918816264800**

4.7 WATT > **50** WATT **6500 K**
380 lm



MZD LED 50W GU10 WH
60D ND 1CT/10

12NC: **929001186532**
EAN1: **313918816127600**

5.5 WATT > **50** WATT **3000 K**
345 lm



MZD LED 50W GU10 CW
60D ND 1CT/10

12NC: **929001186632**
EAN1: **313918816129000**

5.5 WATT > **50** WATT **4000 K**
370 lm



MZD LED 65W GU10 827
36D ND 1CT/10

12NC: **929001371132**
EAN1: **313918816163400**

6 WATT > **65** WATT **2700 K**
490 lm



MZD LED 65W GU10 840
36D ND 1CT/10

12NC: **929001371232**
EAN1: **313918816165800**

5.5 WATT > **65** WATT **4000 K**
500 lm



MZD LED 350lm GU10 840
120D ND 1CT/10

12NC: **929001358532**
EAN1: **313918816167200**

5.5 WATT > **32** WATT **4000 K**
350 lm



MZD LED 500lm GU10 827
120D ND 1CT/10

12NC: **929001372032**
EAN1: **313918816171900**

5.5 WATT > **40** WATT **2700 K**
500 lm



MZD LED 500lm GU10 840
120D ND 1CT/10

12NC: **929001358632**
EAN1: **313918816169600**

5 WATT > **42** WATT **4000 K**
500 lm



MZD LED 500lm GU10 865
120D ND 1CT/10

12NC: **929001372132**
EAN1: **313918816173300**

5 WATT > **42** WATT **6500 K**
500 lm



MZD LED 35W GU5.3 827
12V 36D ND 1CT/10

12NC: **929001210932**
EAN1: **313918816183200**

4.5 WATT > **35** WATT **2700 K**
345 lm



MZD LED 35W GU5.3 840
12V 36D ND 1CT/10

12NC: **929001245932**
EAN1: **313918816185600**

4.5 WATT > **35** WATT **4000 K**
380 lm



MZD LED 50W GU5.3 827
12V 36D ND 1CT/10

12NC: **929001211032**
EAN1: **313918816187000**

8 WATT > **50** WATT **2700 K**
621 lm



MZD LED 50W GU5.3 840
12V 36D ND 1CT/10

12NC: **929001246032**
EAN1: **313918816189400**

8 WATT > **50** WATT **4000 K**
630 lm



MZD LED 50W GU5.3 WH
12V 50D ND 1CT/10

12NC: **929001199432**
EAN1: **313918816131300**

8 WATT > **50** WATT **3000 K**
650 lm



MZD LED 50W GU5.3 CW
12V 50D ND 1CT/10

12NC: **929001199532**
EAN1: **313918816133700**

8 WATT > **50** WATT **4000 K**
700 lm

A⁺

EEI label

80

CRI



220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy Consumption	Beam angle	Switch Cycle (times)	Input Current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 50W GU10 827 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001250432	313918816125200
MZD LED 50W GU10 840 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001247032	313918816266200
MZD LED 50W GU10 865 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001259132	313918816264800
MZD LED 50W GU10 WH 60D ND	PAR16	6	60	15000	46	50	50 x 55	929001186532	313918816127600
MZD LED 50W GU10 CW 60D ND	PAR16	6	60	15000	46	50	50 x 55	929001186632	313918816129000
MZD LED 65W GU10 827 36D ND	PAR16	6	36	15000	48	50	50 x 56	929001371132	313918816163400
MZD LED 65W GU10 840 36D ND	PAR16	6	36	15000	44	50	50 x 56	929001371232	313918816165800
MZD LED 350lm GU10 840 120D ND	PAR16	6	120	15000	40	50	50 x 58	929001358532	313918816167200
MZD LED 500lm GU10 827 120D ND	PAR16	6	120	15000	58	50	50 x 56	929001372032	313918816171900
MZD LED 500lm GU10 840 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001358632	313918816169600
MZD LED 500lm GU10 865 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001372132	313918816173300

A⁺

EEI label

80

CRI



220-240 Vac



15,000h





non dimmable

Product type	Lamp type	Energy Consumption	Beam angle	Switch Cycle (times)	Input Current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 35W GU5.3 827 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001210932	313918816183200
MZD LED 35W GU5.3 840 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001245932	313918816185600
MZD LED 50W GU5.3 827 12V 36D ND	MR16	9	36	15000	710	50	50 x 46	929001211032	313918816187000
MZD LED 50W GU5.3 840 12V 36D ND	MR16	9	36	15000	710	50	50 x 46	929001246032	313918816189400
MZD LED 50W GU5.3 WH 12V 50D ND	MR16	9	50	15000	700	50	50 x 48	929001199432	313918816131300
MZD LED 50W GU5.3 CW 12V 50D ND	MR16	9	50	15000	700	50	50 x 48	929001199532	313918816133700

MAZDA LED TUBES FOR BRIGHTER LIGHTING

Our LED tubes provide high quality light to illuminate any space.

- 600mm, 1200mm and 1500mm lengths
- 4000K and 6500K
- Instant start
- 25,000 hours lifetime
- Save up to 55% energy



MZD LEDtube 600mm
8W 840

MZD LEDtube 600mm
8W 865

MZD LED tube 1200mm
14.5W 840

MZD LEDtube 1200mm
14.5W 865

12NC: **929001855632**
EAN1: **8718696717455**

12NC: **929001855732**
EAN1: **8718696717479**

12NC: **929001855832**
EAN1: **8718696717417**



12NC: **929001855932**
EAN1: **8718696717431**

8 WATT **18** WATT **4000 K**
800 lm

8 WATT **18** WATT **6500 K**
800 lm

14.5 WATT **36** WATT **4000 K**
1600 lm

14.5 WATT **36** WATT **6500 K**
1600 lm



MZD LEDtube 1500mm
20W 840

MZD LEDtube 1500mm
20W 865

12NC: **929001855432**
EAN1: **8718696717370**

12NC: **929001855532**
EAN1: **8718696717394**

20 WATT **58** WATT **4000 K**
2200 lm

20 WATT **58** WATT **6000 K**
2200 lm

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⊗
non dimmable

Product type	Lamp type	LED	Input Current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
NEW MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	871869671745500
NEW MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	871869671747900
NEW MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	871869671741700
NEW MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	871869671743100
NEW MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	871869671737000
NEW MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	871869671739400

GREAT LIGHT
SOLID DESIGN





Engineered for performance
Up to 25,000 hours reliable lifetime
Superb light quality
Save up to 85% energy

MAZDA | I.B.R.S. / C.C.R.I. Numéro 10461 | 5600 VB Eindhoven, the Netherlands | WWW.MAZDALIGHTING.COM

 **MAZDA**