

# PHILIPS


Bulb

LED

8W-60W

E27

Warm White



8718696577073



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

### Light beyond illumination

- A simple LED for everyday use

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## A simple LED for everyday use



The Philips everyday LED is the perfect lamp for your basic lighting needs. It provides the beautiful light and dependable performance that you expect from LED at an affordable price.

# Specifications

### Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

### Lamp dimensions

- Height: 11 cm
- Weight: 0.049 kg
- Width: 6 cm

### Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

### Light characteristics

- Beam angle: 200 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Light Colour Category: Warm White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

### Miscellaneous

- EyeComfort: Yes

### Other characteristics

- Lamp current: 70 mA
- Efficacy: 100 lm/W

### Packaging information

- EAN: 8718696577073
- EOC: 871869657707300
- Product title: LED 60W A60 E27 WW 230V FR ND SRP 1BC/6

#### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 8 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A+

#### Product dimensions and weight

- Length: 11 cm

#### Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 8 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696577073
- Net weight: 0.065 kg
- Gross weight: 0.081 kg
- Height: 16.600 cm
- Length: 10.000 cm
- Width: 6.100 cm
- Material number (12NC):  
929001234390



Issue date: 2023-11-08  
Version: 0.166

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)