

# PHILIPS


Bulb

LED

7.5 W-60 W

E27

Cool White



8718696577257



## Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High-quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

### Light beyond illumination

- A simple LED for everyday use

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## A simple LED for everyday use



The Philips everyday LED is the perfect lamp for your basic lighting needs. It provides the beautiful light and dependable performance that you expect from LED at an affordable price.

# Specifications

### Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

### Lamp dimensions

- Height: 11 cm
- Weight: 0.049 kg
- Width: 6 cm

### Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

### Light characteristics

- Beam angle: 200 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

### Miscellaneous

- EyeComfort: Yes

### Other characteristics

- Lamp current: 70 mA
- Efficacy: 107 lm/W

### Packaging information

- EAN: 8718696577257
- EOC: 871869657725700
- Product title: LED 60W A60 E27 CW 230V FR ND SRP 1BC/6

#### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 7.5 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A+

#### Product dimensions and weight

- Length: 11 cm

#### Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 7.5 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696577257
- Net weight: 0.065 kg
- Gross weight: 0.081 kg
- Height: 16.600 cm
- Length: 10.000 cm
- Width: 6.100 cm
- Material number (12NC):  
929001234790



Issue date: 2023-11-08  
Version: 0.155

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)