

PHILIPS

Lamp (Dimmable)

LED

10.5W-75W

B22

Warm Glow

Dimming



8718699770945



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Dims to a warm glow

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Glass Frosted Design

The look you love, the performance you expect. Classic frosted glass designs that replicate the soft glowing light of traditional bulbs, for a perfect fit throughout your home.

Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Lamp dimensions

- Height: 10.4 cm
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 270 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2700-2200 K
- Light Colour Category: Warm Glow
- Nominal luminous flux: 1055 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 927-922 | CCT of 2700K-2200K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 60 mA
- Efficacy: 100 lm/W

Packaging information

- EAN: 8718699770945
- EOC: 871869977094500
- Product title: LED classic 75W A60 B22 FR WGD90 SRT4

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W

Product dimensions and weight

- Length: 10.4 cm

Rated values

- Rated beam angle: 270 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1055 lm
- Rated power: 10.5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699770945
- Net weight: 0.060 kg
- Gross weight: 0.098 kg
- Height: 14.600 cm
- Length: 6.500 cm
- Width: 6.300 cm
- Material number (12NC): 929002392801



Issue date: 2023-11-07
Version: 0.129

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com