



PHILIPS

LED lamps


Field Selectable Products



Field selectable
lamps price guide

June 2023





With the unique convenience of adjustable color temperatures and/or lumen outputs, our new field selectable product line makes it easy to always have the right product for the job.



EvoKit Click
1x4, 2x2, & 2x4 retrofit kits
with selectable CCT & Lumens



MainsFit CorePro
(UL Type-B) TLED lamps
with selectable CCT



MainsFit CorePro
PLED lamps
with selectable CCT



MasterClass
LED corn cob lamps
with selectable CCT & Lumens



MasterClass high wattage
LED corn cob lamps
with selectable CCT

Field Selectable products give you the added benefit of carrying one SKU versus multiple SKUs, keeping your inventory low and turns high. These field selectable products are priced right and are all part of our Ready to go offering!

Learn more about additional Ready to go offerings at:
www.signify.com/readytogo

Philips field selectable products



EvoKit Click 1x4, 2x2, & 2x4 retrofit kits with selectable CCT & Lumens

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Packaging	Price
269696	929002749013	EvoKit CLKES 1x4 UNV 0-10 P4	17/22/25	2650/3250/3650	80	3500/4000/5000	4 pack	
269738	929002749113	EvoKit CLKES 1x4 UNV 0-10 P1	17/22/25	2650/3250/3650	80	3500/4000/5000	Single Pack	
269753	929002749213	EvoKit CLKES 2x2 UNV 0-10 P4	17/22/25	2650/3250/3650	80	3500/4000/5000	4 pack	
269803	929002749313	EvoKit CLKES 2x2 UNV 0-10 P1	17/22/25	2650/3250/3650	80	3500/4000/5000	Single Pack	
269829	929002749413	EvoKit CLKES 2x4 UNV 0-10 P4	20/26/30	3150/3900/4300	80	3500/4000/5000	4 pack	
269837	929002749513	EvoKit CLKES 2x4 UNV 0-10 P1	20/26/30	3150/3900/4300	80	3500/4000/5000	Single Pack	



MainsFit CorePro (UL Type-B) TLED lamps with selectable CCT (120-277V) 240° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	MOL (in)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Price
579672	929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	14.5	48	1800	82	3000/3500/4000/5000/6500	50,000	



MainsFit CorePro PLED lamps with selectable CCT (120-277V) 120° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	MOL (in)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Price
577890	9290034776	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	8	5.9	975/1000/1050	83	3000/3500/4000	30,000	
577908	9290034777	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	8	4.7	975/1000/1050	83	3000/3500/4000	30,000	
577916	9290034778	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	11	5.9	1425/1450/1500	83	3000/3500/4000	30,000	
577924	9290034779	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	11	4.7	1425/1450/1500	83	3000/3500/4000	30,000	



MasterClass LED corn cob HID replacement lamps with selectable CCT & Lumens

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Price
570465	929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	36	150 (100-150)	4800/5000/5000	80	3000/4000/5000	50,000	
570473	929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	45	175 (150-175)	5800/6200/6200	80	3000/4000/5000	50,000	
570481	929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	54	250 (150-250)	7000/7500/7500	80	3000/4000/5000	50,000	
570499	929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	63	250 (175-250)	7800/8500/8500	80	3000/4000/5000	50,000	



MasterClass high wattage LED corn cob lamps with selectable CCT



Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Price
583682	929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	80	250	11500/12000/12000	80	3000/4000/5000	50,000	
583690	929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	115	320	15800/17000/17000	80	3000/4000/5000	50,000	
583708	929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	145	400	20500/22000/22000	80	3000/4000/5000	50,000	

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLt-2158BR 08/23 philips.com/LEDlamps

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.