

## UHBS Selectable Series

### HIGH BAY

- Compact, 13" and 15" round die cast aluminum housing
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor ready port for quick plug and play install
- 120-347 volt operating range



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
UHBS-1218-MV-L84050-U	Round, White*	320W Halide, 4-T5HO 54W	4000K-5000K	120-347V	12,000-18,000	81-120	080083256471	<b>S-PEIA6S</b>
UHBS-2436-MV-L84050-U	Round, White*	750W Halide, 8-T5HO 54W	4000K-5000K	120-347V	24,000-36,000	145-238	080083256488	<b>S-Z5HGE1</b>

\* Medium Distribution. Note: DLC Premium items are noted in bold.

#### Accessories

Catalog Number	Description	UPC
Y-TOGGLE-10-2PK	Mounting Toggle and 10' Cable	080083259557
UHBS SENSOR REMOTE	Sensor remote	080083260249
UHBS-WG13	13 DIA Wire Guard	080083273348
UHBS-WG15	15 DIA Wire Guard	080083273355

#### PIR Sensor

Catalog Number	Description	UPC
UHBS-SENSOR PK	PIR Sensor, 360 Lens	080083257898

## SPHB Selectable Series

### HIGH BAY

- 2 Compact, lightweight designs for easy install
- Up to 36,000 selectable lumens and 4000K/5000K selectable CCT
- Sensor Ready port for quick plug and play install
- Great for industrial, manufacturing, gymnasium, and warehouse



Selectable lumen output and colour temperature with an easy to access toggle switch.



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
SPHB-1224SE-M-UNV-L84050-CD-SP1-U	Med. Distr	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	12,000-24,000	82/123/166	080083289264	S-01PR4D
SPHB-2436SE-M-UNV-L84050-CD-SP1-U	Med. Distr	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,000-36,000	162/209/251	080083289288	S-7V2YTC

## LHBS Series

### HIGH BAY

- Economical industrial high bay/low bay LED linear luminaire
- CCT (4000/5000K) and lumen select for greater flexibility
- Standard diffused lens provides added protection and glare control
- Energy-efficient, one-for-one replacement of linear fluorescent and HID fixtures
- Perfect for industrial, manufacturing, gymnasium and warehouse applications



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LHBS-1218-UNV-L84050-U	Lensed HB Select*	4-T8, 3-T5HO, 175W MH	4000K-5000K	120-277V	13,000-18,000	85-124	080083274741	<b>S-J1KSFT</b>
LHBS-1824-UNV-L84050-U	Lensed HB Select*	6-T5HO, 8-T8, 400W MH	4000K-5000K	120-277V	18,800-24,000	119-156	080083275625	<b>S-24YMLJ</b>
LHBS-2436-UNV-L84050-U	Lensed HB Select*	8-T5HO, 10-T8, 750W MH	4000K-5000K	120-277V	24,388-36,000	155-246	080083276141	<b>S-EUK8B9</b>

\* Medium Distribution. Note: DLC Premium items are noted in bold.

## VHB Series

### HIGH BAY

- Designed for a wide variety of applications and mounting heights
- Precision designed optics; High impact polycarbonate optical LED lens
- Compact, lightweight design for ease of installation
- Lumen selectable models available
- Solution for spaces utilizing traditional linear fluorescent and HID high bay
- Ideal for industrial, commercial, manufacturing and gymnasium applications



Catalog Number	Description	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
VHB-1824-W-UNC-L840-CD-MP-U	Compact Linear, WD Distr, Selectable Lumens	400W HID, 6-T5HO 54W	4000K	347-480V	18,000-24,000	126-158	080083191611	<b>PKWWO6XP</b>
VHB-1824-W-UNV-L840-CD-MP-U	Compact Linear, WD Distr, Selectable Lumens	400W HID, 6-T5HO 54W	4000K	120-277V	18,000-24,000	126-158	080083191390	<b>PKWWO6XP</b>
VHB-24-W-UNC-L840-CD-MP-U	Compact Linear, WD Distr	400W HID, 6-T5HO 54W	4000K	347-480V	24,000 (Dedicated)	174	080083827282	<b>PJ92YFP9</b>
VHB-24-W-UNV-L840-CD-MP-U	Compact Linear, WD Distr	400W HID, 6-T5HO 54W	4000K	120-277V	24,000(Dedicated)	174	080083827299	<b>PJ92YFP9</b>

Note: DLC Premium items are noted in bold.

## F-Bay Accessories

Catalog Number	Description	UPC
MMS-OSFHUITW-120V/277V/347V	Modular motion sensor kit	080083590148
AYC-CHAIN/SET-U	V Hooks & 36" Chain Set	080083545704
HBAYC-CHAIN/SET-U	Hook-style V-Hangers	080083575756
Y-TOGGLE-10-2PK	Aircraft Cable Y-Toggle 120"	080083259557
MC12	Modular Cord & Plug	080083552498
MC6	Modular Cord & Plug	623961368455

## VT Series

### VAPORTITE

- Contemporary surface-mount fixture featuring rugged and durable construction
- Sealed and gasketed, reinforced fiberglass housing with a high impact lens
- Internal fasteners and tethers provide maximum protection and rigidity
- Optical performance for interior and exterior applications; IP65 certified; NSF Listed
- Ideal for parking garages, food processing, canopy, manufacturing and complex environmen



Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4VT2-LD5-6-DR-UNV-L835-CD1-WL-U	4' Fixed Output	3-T8, 1-T5HO	3500K	120-277V	6,197	50	080083146598	P1R4U9WP

## APVT Series

### VAPORTITE

- Durable polycarbonate housing with integral metal gear tray
- 4ft and 8ft sizes with CCT and lumen select capability
- UL Wet location, IP65 and operating temp -20C to 40C
- Stainless steel latches, single conduit hub, and mounting included



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4APVTLD-SL3C3	4' Selectable Output	3-T8 32W, 2-T5HO 54W	3500K-5000K	120-277V	3,000-6,000	21-46	080083264216	S-M39BJL



Good

Better

Best



		LHBS	SPHB	UHBS
APPLICABILITY <sup>1</sup>	Big Box Retail	★	★★	★★
	Sports / Recreation	★★	★★	★★
	Warehouses	★★★	★★★	★★
	Manufacturing	★★	★★★	★★
	Cold Storage	★	★★★	★
	Complex Environments		★	★★

		LHBS	SPHB	UHBS
FEATURES / PERFORMANCE	Lumen Range	12,000 - 36,000	12,000 - 36,000	12,000-36,000
	Selectable Lumens	12,000-18,000 or 18,000-24,000 or 24,000-36,000	12,000 - 24,000 or 24,000 - 36,000	12,000-18,000 or 24,000-36,000
	Efficacy (Max)	160 lm/W	158 lm/W	137 lm/W
	CRI	80	80	80
	Distribution	M	M	M
	Sizes	13' x 2' & 4'	12' x 18" or 12' x 36"	13" & 15"
	Housing <sup>2</sup>	CRS	CRS	Diecast
	Lensing	Acrylic	Polycarbonate	Polycarbonate
	Uplight	None	None	None
	Life (@ 60K hrs)	L84	L86	L91
	Ambient Range	-20C to 50C	-40C to 45C	-40C to 45C
	Emergency	None	Optional	None
	Ratings	Damp	Damp, IP5X	IP65, NSF, Wet Location
DLC	Premium	Premium	Standard	

		LHBS	SPHB	UHBS
INTEGRATED CONTROLS	Basic Occupancy		✓	
	Stand Alone Daylight / Occupancy		✓	✓
	WaveLinx		✓	

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable  
 2. CRS=Cold-rolled Steel, Extruded= Extruded Aluminum, Diecast=Diecast Aluminum.

## Compatible Controls

Warehouse facilities must meet requirements of ASHRAE Standard 90.1 2010. The High Bay Fixture Mount Sensor solves this by meeting and exceeding those requirements.



**OEF High Bay Fixture Mount Sensor**  
 See page 46