

LUMARK AP WALL MOUNTS

Lumark AP provides high-value outdoor lighting products that are in stock and supported with decades of experience and expertise in the industry.



ASWP Adjustable Slim Wall Pack Luminaire WALL MOUNT

- Adjustable slim wall pack available in small and medium sizes
- 3-colour selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages range from 2,100-10,200 lumens
- Internal toggle switches to easily adjust luminaire CCT and lumens
- Integrated button type photocontrol for dusk-to-dawn operation



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
ASWPLED1S	Small LED Wall Pack	Bronze	155W HID	3000K-5000K	120-347V	2,000-4,000	15-30W	080083265169	S-YWC5DG
ASWPLED2S	Medium LED Wall Pack	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	40-75W	080083265183	S-9DIVKW

Note: DLC Premium items are noted in bold.

WPM Wall Pack Luminaire WALL MOUNT

- LED wall pack available with selectable configurations
- Die-cast aluminum housing with hinged, removable die-cast aluminum door
- Heat and impact resistant borosilicate glass lens
- Energy and maintenance savings up to 89%
- Ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
WPMLED15S	Medium LED Wall Pack	Bronze	150W HID	3000K-5000K	120-347V	3,977-7,535	29-59	080083176144	PLAP4BWH9V52
WPMLED25S	Medium LED Wall Pack	Bronze	250W HID	3000K-5000K	120-347V	9,779-12,829	72-101	080083176168	PLCDOB65Z8EN

LSF Selectable Flood Luminaire FLOODLIGHT

- Available in 3 housing sizes and multiple lumen packages
- 3-colour selectable CCT: 3000K, 4000K, 5000K; 70CRI
- Lumen packages ranging from 1,700-20,000 lumens
- Knuckle, slipfitter, trunnion and yoke mounting types
- Integrated button type photocontrol for dusk-to-dawn operation



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LSF25-KN-PC	Knuckle Mount, Photocontrol	Bronze	155W HID	3000K-5000K	120-347V	1,700-4,000	11-25W	080083267705	S-W43YTM
LSF65-KN-PC	Knuckle Mount, Photocontrol	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	25-65W	080083267729	S-5HK1XN
LSF120-SF-PC	Slipfitter Mount, Photocontrol	Bronze	450W HID	3000K-5000K	120-347V	9,000-20,000	50-120W	080083267743	S-M4YHAF
LSF25-YK-PC	Yoke Mount, Photocontrol	Bronze	155W HID	3000K-5000K	120-347V	1,700-4,000	11-25W	080083267767	S-W43YTM
LSF65-YK-PC	Yoke Mount, Photocontrol	Bronze	375W HID	3000K-5000K	120-347V	5,000-10,000	25-65W	080083267781	S-5HK1XN
LSF120-TR-PC	Trunnion Mount, Photocontrol	Bronze	450W HID	3000K-5000K	120-347V	9,000-20,000	50-120W	080083267804	S-M4YHAF

Note: DLC Premium items are noted in bold.

CLCS Canopy Luminaire CEILING MOUNT

- LED canopy available with fixed output or selectable configurations
- 3-colour selectable CCT: 3000K, 4000K, 5000K
- High-performance, energy-efficient illumination
- Energy and maintenance savings up to 86% versus HID solutions
- Ideal for new or existing spaces including bank, retail, drive-thru, covered sidewalks and hospital entryways



Selectable CCT & Lumens

Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
CLCS17S	Small LED Canopy	Bronze	175W HID	3000K-5000K	120-277V	5,323-7,939	39-56	080083160006	P5MUAJIY
CLCS40S	Large LED Canopy	Bronze	400W HID	3000K-5000K	120-277V	12,614-17,427	91-123	080083160020	PUT80LSK

LAS Luminaire AREA/SITE

- Automatic dusk-to-dawn area lighting with included twistlock photocontrol
- 10-position, Field-Selectable lumens across 2 die-cast aluminum housing sizes
- Energy and maintenance savings up to 79% versus HID solutions up to 79%
- Pole mount arm or adjustable slipfitter mounting arm included
- Ideal for parking lots, walkways, building areas and other outdoor areas



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
LAS100P-T3	T3 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083248780	PP8AW4F5
LAS100P-T3-HV	T3 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083248841	PP8AW4F5
LAS100P-T4	T4 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083248803	POCHU9AS
LAS100P-T4-HV	T4 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083248865	POCHU9AS
LAS100P-T5	T5 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083248827	PMUFIF4F
LAS100P-T5-HV	T5 Distr., Pole Mount Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083248889	PMUFIF4F
LAS100S-T3	T3 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083155866	PP8AW4F5
LAS100S-T3-HV	T3 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083155989	PP8AW4F5
LAS100S-T4	T4 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083155880	POCHU9AS
LAS100S-T4-HV	T4 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083156009	POCHU9AS
LAS100S-T5	T5 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	120-277V	8,200-34,000	48-250	080083155903	PMUFIF4F
LAS100S-T5-HV	T5 Distr., Adjustable Slipfitter Arm	Bronze	1,000W HID	4000K	347-480V	8,200-34,000	48-250	080083156023	PMUFIF4F
LAS45P-T3	T3 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083248360	P1T4HG08
LAS45P-T3-HV	T3 Distr., Pole Mount Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083248728	P1T4HG08
LAS45P-T4	T4 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083248384	PJZTZ423
LAS45P-T4-HV	T4 Distr., Pole Mount Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083248384	PJZTZ423
LAS45P-T5	T5 Distr., Pole Mount Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083248704	PW39PQB3
LAS45P-T5-HV	T5 Distr., Pole Mount Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083248766	PW39PQB3
LAS45S-T3	T3 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083155804	P1T4HG08
LAS45S-T3-HV	T3 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083155927	P1T4HG08
LAS45S-T4	T4 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083155828	PJZTZ423
LAS45S-T4-HV	T4 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083155941	PJZTZ423
LAS45S-T5	T5 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	120-277V	4,900-20,000	30-150	080083155842	PW39PQB3
LAS45S-T5-HV	T5 Distr., Adjustable Slipfitter Arm	Bronze	450W HID	4000K	347-480V	4,900-20,000	30-150	080083155965	PW39PQB3

Note: DLC Premium items are noted in bold.



LUMARK WALL MOUNTS

Lumark combines value-engineered, specification-grade lighting features with market-leading retrofit installation solutions, to enable contractors to get on and off the job quickly and deliver superior illumination coverage.



XTOR Crosstour Luminaire WALL MOUNT

- Architectural style with super bright, energy-efficient LEDs
- Low-profile, rugged die-cast aluminum construction and stainless steel hardware
- Universal back box with sealed and gasketed optical compartment
- Wall, surface, post, bollard, low-level, inverted, floodlight mounting
- Ideal for multi-use facilities, pathway illumination and building entrances



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
XTOR1B	Small Full Cutoff	Carbon Bronze	70W HID	5000K	120-277V	1,418	12	080083777969	PRVAZAZR
XTOR2B	Small Full Cutoff	Carbon Bronze	100W HID	5000K	120-277V	2,135	18	080083778225	PGP4FYV3
XTOR3B	Small Full Cutoff	Carbon Bronze	150W HID	5000K	120-277V	2,751	26	080083778041	PWFZHYJH
XTOR3B-347V	Small Full Cutoff	Carbon Bronze	150W HID	5000K	347V	2,751	26	080083778386	PWFZHYJH
XTOR4B	Medium Full Cutoff	Carbon Bronze	250W HID	5000K	120-277V	4,269	38	080083778003	PUJ1NXGY
XTOR6B	Large Full Cutoff	Carbon Bronze	320W HID	5000K	120-277V	6,129	58	080083774807	X7BH39
XTOR6BRL	Large Refractive Lens	Carbon Bronze	320W HID	5000K	120-277V	6,225	58	080083774821	N/A
XTOR8B	Large Full Cutoff	Carbon Bronze	400W HID	5000K	120-277V	8,502	81	080083774814	P5557CRH
XTOR8BRL	Large Refractive Lens	Carbon Bronze	400W HID	5000K	120-277V	8635	81	080083774852	N/A
XTOR8BRL-347V	Large Refractive Lens	Carbon Bronze	400W HID	5000K	347V	8635	81	080083777068	N/A
XTOR12BRL	Large Refractive Lens	Carbon Bronze	450W HID	5000K	120-277V	13458	102	080083779581	PAEAG8NM
XTOR12BRL-347V	Large Refractive Lens	Carbon Bronze	450W HID	5000K	347V	13458	102	080083778201	PAEAG8NM

CTKR Caretaker Luminaire

AREA/SITE

- Rugged die-cast housing for durability in security applications
- Uniform distribution with excellent vertical illumination for maximum light coverage
- Wall/pole-mount bracket and integral slipfitter for versatility in mounting
- Versatile universal mounting plate allows quick and easy installation
- Low-cost, low-maintenance solution for residential street lighting, perimeter area lighting, parking areas, loading platforms, boat docks, access drives or pathways



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
CTKR3B	Area site with PC, UNV Mount Arm	Raw	250W HID	4000K	120-277V	9,741	71	080083865413	P3P0FHML

Note: DLC Premium items are noted in bold.

Accessories

Catalog Number	Description	Finish	UPC
SR-CARETAKER	Small Acrylic Refractor	Clear	08008377969

NFFLD Night Falcon Luminaire

FLOODLIGHT

- Cost-effective LED floodlight available in medium or large sizes
- Precision engineered and high-efficiency optics delivers superior uniformity
- Compact, robust die-cast aluminum housing, driver compartment and door
- 6H x 6V NEMA wide distribution
- Ideal for area lighting for security, building facade and signage



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
NFFLD-C25-T	Medium, Trunnion	Carbon Bronze	250W HID	4000K	120-277V	10,530	85	080083801220
NFFLD-C40-S	Medium, Slipfitter	Carbon Bronze	400W HID	4000K	120-277V	16,932	128	080083801206
NFFLD-C40-T	Medium, Trunnion	Carbon Bronze	400W HID	4000K	120-277V	16,932	128	080083801183
NFFLD-C40-T-347	Medium, Trunnion	Carbon Bronze	400W HID	4000K	347V	16,932	129	080083801060
NFFLD-L-C100-T	Large, Trunnion	Carbon Bronze	1,000W HID	4000K	120-277V	33,941	252	080083800902

NHR Night Harrier FLOODLIGHT

- Cutting edge innovated design offering years of maintenance-free service
- 3-colour selectable CCT: 3000K, 4000K, 5000K
- Lumen packages ranging from 5,500-22,000 lumens
- Slipfitter and trunnion mounting types
- Ideal for area lighting such as facade, wall washing, building and sign lighting



Catalog Number	Description	Finish	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
NHRS50UT	500W Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283903	S-2FNDXP
NHRS50US	500W Slipfitter Mount	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283910	S-2FNDXP
NHRS50HT	500W Trunnion Mount	Bronze	70W to 500W HID	3000K-5000K	347-480V	5,500-22,000	40-155W	080083283927	S-2FNDXP
NHRS50UT-BPC	500W Trunnion Mount, Photocontrol	Bronze	70W to 500W HID	3000K-5000K	120-277V	5,500-22,000	40-155W	080083283941	S-2FNDXP



TGS Series – Twin Head

SECURITY FLOODLIGHT

- Three different brightness levels using Lumen Select Technology
- Durable die-cast aluminum square head with UV resistant lens
- Easy install to wall or eave mounting, with integrated easy connector
- Switch activated, Dusk-to-Dawn, and motion activated models available
- Ideal for security lighting in residential and commercial applications



Dusk-To-Dawn models available



with sensor
also available in square head

Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
TGS2S402MSRB	Twin Head LED Flood	Bronze	180W HID	4000K	120V	1,500-2,500	20.9	080083801220	2362292
TGS2S402MSRW	Twin Head LED Flood	White	180W HID	4000K	120V	1,500-2,500	20.9	080083801206	2362292

ALP - Premium Area Light

AREA/SITE

- All-in-1 brightness adjustable and colour selectable premium LED area light
- Includes 3 LED brightness settings using physical switch on the fixture
- Includes 3 light colour temperatures using physical switch on fixture housing
- Dusk to Dawn nighttime on daytime off operation with replaceable Photocell



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
ALP90LSFSUNVDGY	Barn Light	Grey	250W HID	3000K-5000K	120-277V	4,450-9,300	28W/40W/60W	080083801220	S-JDR6ZI

ARFL Series

SLIMWALL AND FLOODLIGHT

- Modern slim flood light with decorative wall mount
- 5 selectable colour temperatures and photocell on/off with included remote control
- Nighttime on daytime off with photocontrol sensor or can be switch activated
- For illuminating areas such as driveways, backyards, garages, or signage.



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
ARFL15DBZ	Slim Wall Flood	Bronze	100W HID	2700K-5000K	120V	1,500	15	080083260928	2404319
ARFL30DBZ	Slim Wall Flood	Bronze	200W HID	2700K-5000K	120V	3,000	30	080083260942	2404320
ARFL50DBZ	Slim Wall Flood	Bronze	250W HID	2700K-5000K	120V	5,000	45	080083260966	N/A
ARFL80DBZ	Slim Wall Flood	Bronze	150W HID	2700K-5000K	120V	9,000	80	080083260980	2404323

SBL Solar Area Light

AREA/SITE

- Off-Grid – completely free to operate, plus no expensive wiring required
- All-in-one design with LED, Solar Panel, and Battery built in for easy installation
- Motion sensor included with 120° detection range and 25' distance
- 3 selectable modes of operation with remote control Including Motion, Dusk-to-dawn, and Motion + Dusk-to-dawn
- Battery runs up to 90mins at maximum output on full charge and lasts up to 500 cycles



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
SBL10A50GY	Motion, Dusk-to-Dawn	Grey	70W HID	5000K	Solar	1,000	7	080083260461
SBL30A50GY	Motion, Dusk-to-Dawn	Grey	100W HID	5000K	Solar	3,000	15	080083260508

SBL Solar Area Light

AREA/SITE

- Robust die-cast housing for harsh outdoor environments
- Integrated LED with traditional area light design
- Solar panel can be mounted two ways, on top of fixture, or remote mounted and can be mounted up to 25ft
- For illuminating areas such as driveways, backyards, garages, or signage.
- Three selectable modes of operation with remote control
- Premium PIR motion sensor with 180° detection range



Catalog Number	Description	Finish	Replaces	CCT	Voltage	Lumens	Watts	UPC
SBL100A50GY	High Output, Motion, Dusk-to-Dawn	Grey	250W HID	5000K	Solar	1,000	79.5	080083260546
SBL50A50GY	High Output, Motion, Dusk-to-Dawn	Grey	150W HID	5000K	Solar	5,000	33.5	080083260522

Halo Outdoor Accessories

Catalog Number	Description	UPC
EA24	SBL/ALP Mounting Arm	044427000717