


CGTS | CGT Series

FLAT PANEL

- Affordable contractor LED panel with fixed or selectable configurations
- Fits in shallow plenums with room to spare; Thin 2 1/8 - inch height
- 3 Colour Field-Selectable in 35/40/5000K and dedicated in 3500K, 4000K, 5000K
- 3 Field-Selectable Lumens: Low, Medium or High settings
- Ideal for office spaces, education, healthcare and retail merchandising



Selectable CCT & Lumens

Catalog Number	Description	Replaces	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CGTS-NUV	1'X4' Recessed Panel	3-T8, 3-T5	3500K-5000K	120-347V	3,500-4,500	30/35/40	080083247806	PLA9H842922L
22CGTS-NUV	2'x2' Recessed Panel	2-T8, 3-T8	3500K-5000K	120-347V	4,000-6,000	30/35/40	080083247837	PLDJXEJPEQR
24CGTS-NUV	2'x4' Recessed Panel	2-T8, 3-T8	3500K-5000K	120-347V	3,500-4,500	35/40/50	080083247851	PLJQJPJJ7TDJ

Note: DLC Premium items are noted in bold.

Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CGT4040C	1'X4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	4,000	39.4/38.8	080083879540	PGNH8KOZ
22CGT3535C	2'X2' Recessed Panel	3-T8	3500K	120-277V	3,500	31.4/31.7	080083880003	P6WE1HNZ
22CGT3540C	2'x2' Recessed Panel	3-T8	4000K	120-277V	3,500	31.4/31.7	080083880027	POYGNM7S
24CGT4535C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120-277V	4,500	38.8/38	080083880089	P28JP113
24CGT4540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	4,500	38.8/38	080083880102	PLTEVMIJ
24CGT4550C	2'x4' Recessed Panel	2-T8, 3-T8	5000K	120-277V	4,500	38.8/38	080083880126	P8BJJLKN
24CGT5540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120-277V	5,500	46.8/46.6	080083880188	P5F04P82

Accessories (Optional)

Catalog Number	Description	UPC
CGTSURF14	1'X4' CGT Surface Mount Kit	080083083145
CGTSURF22	2'x2' CGT Surface Mount Kit	080083083121
CGTSURF24	2'x4' CGT Surface Mount Kit	080083083107

Multi-Mount Selectable

FLAT PANEL

- Visually comforting panel mounts directly to the ceiling or wall reducing labor and material cost by removing the need for a surface mount kit
- Versatile mounting allows for surface, wall, recessed, or suspended with kit
- Selectable Colour Temperatures in 90 CRI Standard:
2x2/2x4/1x4: 35/40/5000K | 4' x 6": 27/30/35/40/5000K
- Selectable Lumens: Low, Medium, High settings
- Ideal choice for commercial office, school, and healthcare spaces



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
22MMS-L3C3-UNV	2'x2', Direct Mount Panel	3-T8 32W	3500K-5000K	120-277V	2,400-4,800	21/28/42	080083292042	S-28RRZT
24MMS-L3C3-UNV	2'x4', Direct Mount Panel	4-T8 32W	3500K-5000K	120-277V	3,500-6,200	28/36/48	080083292059	S-KJX1CZ
14MMS-L3C3-UNV	1'x4', Direct Mount Panel	2-T8 32W	3500K-5000K	120-277V	2,620-5,286	18/25/38	080083292035	S-V9CG2Y

Note: DLC Premium items are noted in bold.

FPanel Series

FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- Fixed and selectable configurations available
- Selectable switch to set colour temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal solution for office spaces, schools, healthcare facilities and retail merchandising areas



Dedicated CCT & Lumens

Catalog Number	Description	Replaces	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14FP4240C	1'X4' LED Flat Panel	2-T8 32W, 3-T8 32W	4000K	120-277V	4,451	39	080083833481	PBGLLF3K
22FP3240C	2'X2' LED Flat Panel	3-T8 32W, 3-T5 28W	4000K	120-277V	3,200	29	080083833542	PUOIG6S2
22FP4235C	2'x2' LED Flat Panel	3-T8	3500K	120-277V	4641	39	080083833580	P8HIK308
22FP4240C	2'x2' LED Flat Panel	3-T8	4000K	120-277V	4567	39	080083833603	PELH4PNQ
24FP4740C	2'x4' LED Flat Panel	2-T8 32W, 3-T8 32W	4000K	120-277V	4,858	40	080083833665	PGY6ID6B
24FP6440C	2'x4' LED Flat Panel	3-T8, 4-T9	4000K	120-277V	6,611	59	080083833726	Pending Approval

Accessories

Catalog Number	Description	UPC
FPSUS24	Suspension Kit for Panels (CGT, FP, FPX)	080083258895
FPXSURF14	1x4 LED Flat Panel Surface Mounting Kit	080083867424
FPXSURF22	2x2 LED Flat Panel Surface Mounting Kit	080083867387
FPXSURF24	2x4 LED Flat Panel Surface Mounting Kit	080083867400

Achieva™ Recessed Selectable TROFFER

- Ultra slim 1.5" center basket design fits into the shallowest of plenums
- 3 Colour Field-Selectable in 30/35/4000K in 80+ CRI
- 3 Selectable lumens in standard or HO options up to 8,150
- Ideal choice for commercial, institutional and healthcare facilities



Catalog Number	Description	Replaces	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14ARS-L3C3-NUV	1'x4', Troffer	2-T8	3500K-5000K	120-347V	2,800-4,600	20/25/34	080083287529	S-TKCBT4
22ARS-L3C3-NUV	2'x2', Troffer	3-T8, 2-T5	3500K-5000K	120-347V	2,800-4,300	20/27/33	080083287543	S-G4W4DW
24ARS-L3C3-NUV	2'x4', Troffer	2-T8, 3-T8	3500K-5000K	120-347V	3,400-6,300	25/33/47	080083287567	S-3KXXVF

Note: DLC Premium items are noted in bold.

