

PHILIPS

Real pros make the 'switch' to Philips



2700K | Amber

3000K | Warm White

4000K | Neutral White

5000K | Daylight

6500K | Cool daylight



3000K | Warm White

4000K | Neutral White

6500K | Cool daylight

5 colour temperatures in one lamp

- Always the right colour and brightness

Smooth dimming

- Dim to create your ambience, shift from functional to inviting

EyeComfort

- High quality of light designed for the comfort of your eyes

Energy Saving

- High efficacy of 100lm/W


**REAL
PROS**
**REAL
QUALITY**



Signify Product Code	Description	Consumption W	Brightness lm	Base Cap	Lamp Width mm	Lamp Height mm	Lamp Shape	Customer Code	Box QTY
929003785219	LEDBulb 9W E27 DS FR DIM	9	900	E27	60	110	A60	5CT9WE27DIMA60	6
929003785319	LEDBulb 9W B22 DS FR DIM	9	900	B22	60	110	A60	5CT9WB22DIMA60	6
929003785419	LEDBulb 14W E27 DS FR DIM	14	1400	E27	60	110	A60	5CT14WE27DIMA60	6
929003785519	LEDBulb 14W B22 DS FR DIM	14	1400	B22	60	110	A60	5CT14WB22DIMA60	6



Signify Product Code	Description	Consumption W	Brightness lm	Base Cap	Lamp Width mm	Lamp Height mm	Lamp Shape	Customer Code	Box QTY
929003785619	LEDStick 10W E27 DS FR DIM	10	1000	E27	41	107	T40	5CT10WE27DIMIT40	6
929003785719	LEDStick 10W B22 DS FR DIM	10	1000	B22	41	107	T40	5CT10WB22DIMIT40	6
929003785819	LEDStick 14W E27 DS FR DIM	14	1400	E27	41	133	T42	5CT14WE27DIMIT42	6
929003785919	LEDStick 14W B22 DS FR DIM	14	1400	B22	41	133	T42	5CT14WB22DIMIT42	6



Signify Product Code	Description	Consumption W	Brightness lm	Base Cap	Lamp Width mm	Lamp Height mm	Lamp Shape	Customer Code	Box QTY
929003780419	LEDSpot 50W MR16 DS DIM	5	550	GU5.3	50	55	MR16	3CTMR16DIM	6
929003780319	LEDSpot 50W GU10 DS DIM	5	550	GU10	50	60	PAR20	3CTGU10DIM	6