

PHILIPS

LED Lighting



For every moment that sparks bright!
Switch to high quality energy saving Philips LED lighting

Philips Trade Catalog 2024



©ignify

Lead the pack through **top tech**

Go for high-performance and energy-efficient
LED lighting solutions from Signify



Our global brands:

PHILIPS interact

www.signify.com/global/partnership

Signify is Official Lighting Partner of Mercedes-AMG PETRONAS F1 Team

©ignify




Official Lighting Partner
Mercedes-AMG
PETRONAS
FORMULA ONE TEAM

signify

Ready. Set. Install!

Power up your projects with innovative high-performance LED lighting from Signify



PHILIPS



Signify is Official Lighting Partner of Mercedes-AMG PETRONAS F1 Team

signify



Official Lighting Partner

AMG
PETRONAS
FORMULA ONE TEAM

Lighting Solutions for Professional and Consumer Applications

Philips Lighting's extensive portfolio range of luminaires provides the best lighting solutions for all your needs. Experience the highest quality products with perfect colour that brings all your moments to life.

Select the right light that has the power to transform!





Best Product

We provide highest-quality LED lighting solutions which are easy-to-install and designed to last with unbeatable quality.

Our products are engineered to maintain their output and light quality over their full warranted lifetime, providing unbeatable value for customers.

Whether you're looking for innovative indoor lighting solutions or reliable outdoor lighting, we have everything you need to brighten up your home, office or commercial (retail and public) areas.



Best Partner

Our commitment to being your best partner is evident in every aspect of our work. We believe in close cooperation before, during, and after projects to ensure your satisfaction.

Our technical consulting and intense customer support mean that you can count on quick and competent responses to any questions or concerns you may have.

We also work closely with shops near you, to ensure on-time product availability to best meet your needs.



Best Portfolio

We offer the right lighting for every application.

Our LED luminaries, available in a wide variety of shapes and sizes, are designed to create the perfect ambience for multipurpose ranges while delivering significant energy savings.

We take pride in our commitment to innovation, quality, and energy efficiency, and are constantly striving to develop new and better ways to meet the evolving needs of our customers.



Professional Luminaires



Essential Smartbright T5 Integrated LED Batten G3
(BN058)



Essential Smartbright T8 Integrated LED Batten G2
(BN016)



Essential Smartbright LED Wide Batten BN005C



TMS 012 LED Batten



Smartbright Waterproof G2
(WT068)



Essential Waterproof
(For Double-ended LED tube)
(WT069)



Speciality Tubes-Snow White TLED



SmartBright Bulkhead
(WL008C)



Essential SmartBright BulkHead (WT045C)



SmartBright Highbay G4
(BY239 G2)



Essential SmartBright G4 LED Projector/Track Light
(ST033T)



SmartBright Backlit Panel
(RC055B)



SmartBright Backlit Panel G2
(RC048B)



SmartBright Slim Panel G4
(RC091)



Essential SmartBright Floodlight G3 (BVP150)




Essential SmartBright G3 Floodlight Security (BVP150)




SmartBright Floodlight G3
(BVP151)



SmartBright LED Floodlight
(BVP17X)



SmartBright LED Streetlight
(BRP13X)



LED Strip UNILinear Flex IP65 (BGC201)

Essential Smartbright T5 Integrated LED Batten G3 (BN058)



Easy Plug n Play

Indoor Application

Interconnectable

Cove lighting

Application Areas

- Cove lighting
- Indoor general area lighting

Specs

Wattage (W)	3.4/6.5/9.6/13W
Color Temperature (K)	WW/ NW/ CW
Lumen Output (lm)	300/600/900/1200
Color Rendering Index (CRI)	80
Lifetime (hrs)	15000hrs
Power Factor	0.5
IP Rating	IP20

Essential Smartbright T8 Integrated LED Batten G2 (BN016)



Easy Plug n Play

3 CCT option

4f & 2ft versions

Long Life Time

Application Areas

- Retail
- Hospitality
- Office and general lighting

Specs

Wattage (W)	8W(L600), 16W (L1200)
Color Temperature (K)	WW/ NW/ CW
Lumen Output (lm)	L600 - 720 / 780 / 800 lm L1200- 1490 / 1560 / 1600 lm
Color Rendering Index (CRI)	>70
Lifetime (hrs)	15000hrs
Power Factor	0.5
IP Rating	IP20

Essential Smartbright LED Wide Battens (BN005C)



Indoor Application

High Lumens

Excellent aesthetics

4f & 2ft versions

Application Areas

- General lighting, indoor
- Indoor car park, industry, shop, office, school
- Long distance linear lighting

Specs

Wattage (W)	20W (L600) / 40W (L1200)
Color Temperature (K)	WW/ NW/ CW
Lumen Output (lm)	L600 - 2000 lm L1200 - 4000 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	20000hrs
Power Factor	0.9
IP Rating	IP20

TMS 012 LED Batten



Metal Body

Double Ended LED tubes

Conventional TMS Shape

Plug n Play

Application Areas

- Residential and commercial applications with any double end powered tube
- Compatible with double ended LED tubes

Specs

Length (m)	L600,L1200
Voltage	220-240V~ 50/60Hz
Insulation	Class I
Working temp	-20 ~ 40°C. (For Housing)
Connection	Inside wiring ; Middle entry;
Installation	Surface mounted, suspension
Housing color	Powder painting, RAL9003
Lamp options	DE 2xTLED L1200 / DE 1xTLED L1200 DE 2xTLED L600 / DE 1xTLED L600



Smartbright Waterproof G2 (WT068)



Long Life Time

IP 66 Rating

IK 08 rating

High Lumens

Application Areas

- Car parking
- Warehouse
- Utility rooms / Back-of-house areas

Specs

Wattage (W) 15W (L600) / 30W (L1200) / 46.5W (L1500)

Color Temperature (K) CW/ NW

Lumen Output (lm) L600 - 1800 lm

L1200 - 3600 lm

L1500 - 5600 lm

Color Rendering Index (CRI) 80

Lifetime (hrs) 30000 hrs

Power Factor 0.9

IP Rating IP66

Additional feature Through Wiring (TW) Version available

Essential Waterproof For Double-ended LED Tube (WT069)



PC body, UV rated

IK 08 Rating

Metal clips

IP65 Rating

Application Areas

- Parking Garages
- Offices
- Residential

Specs


Size L1200 (DE 1xTLED/2xTLED) , L600 (DE 1xTLED/2xTLED)

Housing material Polycarbonate body, UV rated

Mounting SS brackets

Color Light grey

Clips Stainless Steel



Speciality Tubes - Snow White TLED

Easy Installation

Energy savings

Highly energy efficient

No mercury



Application Areas

- Commercial buildings
- Industrial applications
- Back of house applications
- Utility rooms

Specs

Lamp Wattage	8W/ 20W
Lumen Output	Upto 2200lm
Size	L600/L1200
Color Temperature	12000k
Product Lifetime	15000 hrs
CRI	70

SmartBright Bulkhead (WL008C)



Oval and round shape option

Built-in sensor option

IK 06 Rating

30,000 hrs lifetime

Application Areas

- Residential
- Back-of-house areas
- Staircases
- Utility rooms

Specs

Lamp Wattage (W)	15W
Lumen Output (lm)	1300/1500lm
Color Temp. (K)	4000K
Product lifetime	30,000hrs
Power Factor	0.9
IP Rating	IP65
Color Rendering Index (CRI)	80

Essential SmartBright BulkHead (WT045C)



IP65 Rating

Up to 1,600 lumens

IK 06 Rating

Available in two sizes

Application Areas

- Residential
- Back-of-house areas
- Staircases
- Utility rooms

Specs

Wattage (W)	12W (dia. 120mm) / 20W (dia. 220mm)
Color Temperature (K)	4000K
Lumen Output (lm)	960/1600lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	20000Hrs
Power Factor	>0.5
IP Rating	IP65

4



SmartBright Highbay G4 (BY239 G2)



IP65 Rating

IK 06 rated

Metal Body

High efficiency

Application Areas

- Industry : Factories, warehouses, workshops, assembly lines, etc.
- High ceiling indoor : Shopping malls, airports, stadium, etc

Specs

Lamp Wattage (W)	60 /100/150/200 W
LumenOutput(lm)	7800/13000/19500/26000lm
Color Temp, (K)	4000/6500K
Product lifetime	30000hrs
CRI	80
Efficacy	130 lm/W

Essential SmartBright G4 LED Projector/Track Light (ST033T)



Black & White Color Body

3000k & 4000K CCT

Long Life Time

High Lumens

Application Areas

- Retail shop
- Fashion store
- Shopping mall

Specs

Wattage (W)	7 /10/20/30W
Color Temperature (K)	3000/4000K
Lumen Output (lm)	7W: 560/595 lm
	10W: 800/850 lm
	20W: 1600/1700 lm
	30W: 2400/2500 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	20000hrs
Power Factor	0.9
IP Rating	IP20



SmartBright Backlit Panel (RC055B)



Flicker Free

Long Life Time

IP20 rating

High Lumens

Application Areas

- Open office
- Schools
- Healthcare
- Retail

Specs

Wattage (W)	40W
Color Temperature (K)	4000/6500K
Lumen Output (lm)	3440 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	50,000 hrs (L60B50)
Power Factor	0.9
IP Rating	IP20

SmartBright Backlit Panel G2 (RC048B)



Flicker Free

Long Life Time

IP20 Rating

High Lumens

Application Areas

- Open office
- Schools
- Healthcare
- Retail

Specs

Wattage (W)	38W
Color Temperature (K)	4000K, 6500K
Lumen Output (lm)	3800 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	50,000 hrs (L60B50)
Power Factor	0.9
IK rating	IK04



SmartBright Slim Panel G4 (RC091)

Uniform Brightness

Side Lit Panel

Extra Slim Body

External Driver



Application Areas

- Offices
- Hospitals and Care Centers
- Retail

Specs

Wattage (W)	30W/ 40W/ 50W
Color Temperature (K)	4000/ 6500K
Lumen Output (lm)	3000/ 4000/ 5000lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	30,000 hrs
Power Factor	0.9
IP Rating	IP20
Size	60x60 / 30x120 / 60x120

Essential SmartBright Floodlight G3 (BVP150)



High Lumens

IP65 Rating

20,000 hrs lifetime

Easy to install

Application Areas

- Architectural lighting
- Landscape lighting
- Billboard lighting
- Parking area lighting
- Amenity

Specs

Lamp Wattage (W)	10W/ 20W/ 30W/ 50W/ 70W/
Lumen Output (lm)	10W - 900 to 1000 lm
	20W - 1880 to 2000 lm
	30W - 2820 to 3000 lm
	50W - 4700 to 5000 lm
	70W - 6580 to 7000 lm
	100W - 9400 to 10000 lm
	150W - 14100 to 15000 lm 200W - 18800 to 20000 lm
Color Temp. (K)	3000/4000/6500K
Product lifetime	20,000hrs
CRI	80
Power factor	0.9

Essential SmartBright G3 Floodlight Security (BVP150)



Up to 5000 lumens

IP65 Rating

Multiple CCT options

Easy to install

Application Areas

- Architectural lighting
- Landscape lighting
- Billboard lighting
- Parking area lighting
- Amenity
- Security

Specs

Lamp Wattage (W)	20W/30W/50W
Lumen Output (lm)	20W - up to 2000 lm
	30W - up to 3000 lm
	50W - up to 5000 lm
Color Temp. (K)	3000/4000/6500K
Product lifetime	20,000hrs
CRI	80
Power factor	0.9

SmartBright Floodlight G3 (BVP151)



High Lumens

IP 65 Rating

Wide beam

50,000 hrs lifetime

Application Areas

- Architectural lighting
- Landscape lighting
- Billboard lighting
- Parking area lighting
- Amenity

Specs

Wattage (W)	10/20/30/50/70/100/150/200W
Color Temperature (K)	6500K
Lumen Output (lm)	1200/2400/3600/6000/8400/12000/ 18000/24000lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	50000hrs
Power Factor	0.90
IK rating	IK07 - up to 50W IK08 - 70W/ 100W/ 150W/ 200W

SmartBright LED Floodlight (BVP17X)



High Lumens

Multiple CCT options

IP65 Rating

Up to 200W

Application Areas

- Architectural lighting
- Landscape lighting
- Billboard lighting
- Parking area lighting
- Amenity

Specs

Wattage (W)	30/50/70/100/150/200W
Color Temperature (K)	NW/ CW/ WW
Lumen Output (lm)	2600/4300/7800/11200/17000/22000lm
Color Rendering Index (CRI)	70
Lifetime (hrs)	30,000
Power Factor	>0.9
IK rating	IK07

SmartBright LED Streetlight (BRP13X)



Long lasting performance

Uniform Lighting

IK 08 Rating

Slim and Sleek design

Application Areas

- Road and Street
- Residential
- Security Lighting
- Parks
- Gated Communities

Specs

Wattage (W)	70/100/140W
Color Temperature (K)	3000K, 4000K, 6500K
Lumen Output (lm)	8,800/12,500/17,500 lm
Color Rendering Index (CRI)	70
Lifetime (hrs)	30,000
Power Factor	0.90
IP Rating/ IK Rating	IP66 / IK08

LED Strip UNILinear Flex IP65 (BGC201)



IP65 Rating

RGB option

Long Life Time

Vivid light colors

Application Areas

- Decorative lighting
- Guidance lighting
- Cove lighting

Specs

Lamp Wattage (W)	20W/5m , 37W/5m , 48W/5m , 50W/5m
Lumen Output (lm)	400lm/m , 800lm/m , 1100lm/m, 480lm/m
Color Temp. (K)	2500K/3000K/4000K/6500K/ RGB
CRI	80
IP Rating	IP65
Lifetime	20,000 hrs
Driver	24V



Consumer LED Lamps & Luminaires



					
Essential LED Bulbs	High Wattage LED Bulb	Battery LED Bulbs	Essential LED Sticks Non Dimmable	Filament LED Lamps	TrueForce Lamps
					
GU10 Spots	Essential MR16 (220-240V)	Essential MR16 (Works with 12V transformer)	Ecofit LED Tubes	Ecofit (Single Ended) LED Tubes	SL190 High wattage Spots
					
SL052 Spots	SmartBright DN027 Downlights			Meson Downlights	
					
COB Hybrid DN036 Downlight	DL360 Downlights (COB Hybrid Downlights in smaller cut outs)	External Driver Slim DL252 Downlight		HV HLS168 LED Strip (50 mts roll)	

Essential LED Bulbs



Uniform brightness

No Glare

Wide Voltage

ESMA approved

Application Areas

- Residential
- Commercial spaces
- Hospitality

Specs

Wattage (W)	9W/ 11W/ 13W
Color Temperature (K)	3000K/ 6500K
Lumen Output (lm)	900/ 950/ 1150/ 1250/ 1350/ 1450lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	10,000 hrs
Cap base: E27	E27

High Wattage LED Bulb



Uniform brightness

Suitable for indoor use

Low glare

High wattage and high lumen offering

Application Areas

- Residential and commercial spaces

Specs

Wattage (W)	19W
Color Temperature (K)	3000K/ 6500K
Lumen Output (lm)	2150/ 2200 lm
Color Rendering Index (CRI)	70
Lifetime (hrs)	10,000 hrs
Cap base	E27

Battery LED Bulbs



Uniform brightness

Significant energy savings

3 hours of emergency lighting

Long lifetime

Application Areas

- Residential and commercial spaces

Specs

Wattage (W)	7.5W
Color Temperature (K)	3000K/ 6500K
Lumen Output (lm)	700 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
Cap base	E27

Essential LED Sticks Non Dimmable



All round illumination

Cool, energizing light

Available in multiple wattages

Best use in compact & slim luminaire application

Application Areas

- Indoor lighting

Specs

Wattage (W)	6.5W/ 9W/ 11W
Color Temperature (K)	3000K/4000K/ 6500K
Lumen Output (lm)	550/ 600/ 750/ 806/ 950/ 1055 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	10,000 hrs
Cap base	E27

Filament LED Lamps



Like Original incandescent

Classic heritage design

No glare

90% energy saving

Application Areas

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Specs

Wattage (W)	4W/ 5.5W
Color Temperature (K)	2700K
Lumen Output (lm)	250/ 470 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
Cap base	E27

TrueForce Lamps



Low initial investment

Up to 9000lm

High energy efficiency

Replacement solutions for HID/CFLi

Application Areas

- Retail - Hyper markets, shopping mall
- Others - Transportation hubs, Convention centres,
- Sports hall

Specs

Wattage (W)	25W/ 30W/ 40W/ 50W/ 60W/ 80W
Color Temperature (K)	3000K/ 6500K
Lumen Output (lm)	2700/ 3200/ 4000/ 5000/ 7000/ 9000 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
Cap base	E27/ E40

GU10 Spots



Easy retrofit

Low maintenance cost

Delivering accent beam

Perfect for spotlighting

Application Areas

- Domestic Applications
- Retail and Hospitality

Specs

Wattage (W)	4.6W
Color Temperature (K)	2700K/ 3000K/ 6500K
Lumen Output (lm)	395/ 410 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
Cap base	GU10

Essential MR16 (Frosted form factor – works on mains voltage)



Retrofit low-voltage MR16 halogen lamps

Works on 220V-240V

Long lifetime

Lower maintenance costs

Application Areas

- Home lighting design
- Accent lighting
- Retail
- Hospitality

Specs

Wattage (W)	5W
Color Temperature (K)	2700K
Lumen Output (lm)	400lm
Color Rendering Index (CRI)	70
Lifetime (hrs)	10,000
Driver	No 12V driver required
Cap base	GU5.3
Beam angle	120 D

Essential MR16 (Works on mains voltage)



Retrofit low-voltage MR16 halogen lamps

Works on 220V-240V

Long lifetime

Lower maintenance costs

Application Areas

- Home lighting design
- Accent lighting
- Retail
- Hospitality

Specs

Wattage (W)	4.5W
Color Temperature (K)	3000K, 6500K
Lumen Output (lm)	400lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	10,000
Cap base	GU5.3
Beam Angle	36D

Essential MR16 (Works with 12V transformer)



Retrofit low-voltage MR16 halogen lamps

Directional beam angle

Long lifetime

Lower maintenance costs

Application Areas

- Home lighting design
- Accent lighting
- Retail
- Hospitality

Specs

Wattage (W)	4.5W
Color Temperature (K)	2700K, 6500K.
Lumen Output (lm)	400lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000
Driver	12V Driver required.
Cap base	GU5.3

Ecofit LED Tubes



Double ended LED tube

Plug and play solution

Easy to install/No rewiring required

Available in multiple CCT

Application Areas

- Indoor general lighting
- Parking lots
- Warehouses
- Public areas

Specs

Wattage (W)	8W/9W/16W/22W
Available lengths	600mm (8W/ 9W), 1200mm (16W/ 22W)
Color Temperature (K)	4000K/6500K
Lumen Output (lm)	800lm (600mm), 1600lm (1200mm), 2000lm (1200mm)
Color Rendering Index (CRI)	70
Lifetime (hrs)	15,000 hrs
Cap base	G13

Ecofit (Single Ended) LED Tubes



Single ended LED tube

Natural lighting effect

Application Areas

- Indoor general lighting
- Parking lots
- Warehouses
- Public areas

Specs

Wattage (W)	20W
Available lengths	1500mm
Color Temperature (K)	6500K
Lumen Output (lm)	2000 lm
Color Rendering Index (CRI)	73
Lifetime (hrs)	15,000 hrs
Cap base	G13

SL190 High Wattage Spots



Suitable for accent lighting

Energy savings

Replaces halogen luminaire

Adjustable head

Application Areas

- Hospitality
- Retail
- Home segments
- General lighting applications

Specs

Wattage (W)	8W
Color Temperature (K)	2700K/4000K/6500K
Cut out	90mm
Lumen Output (lm)	800lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs

SL052 Spots



Suitable for accent lighting

Energy savings

Replaces halogen luminaire

Adjustable head

Application Areas

- Hospitality
- Retail
- Home segments
- General lighting applications

Specs

Wattage (W)	5.8W
Color Temperature (K)	2700K/ 6500K
Lumen Output (lm)	600 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	25,000 hrs
IP Rating	IP20

DN027 Downlight

High lifetime downlight range

Available in round recessed, square, surface

High power factor

IP40 Front part

Application Areas

- Shopping mall
- Retail stores
- Residential
- Office

Round Recessed



Square Recessed



Surface Mounted



Specs

Color Rendering Index (CRI)	80
Color Temperature (K)	3000K/ 4000K/ 6500K
Lifetime (hrs)	30,000 hrs
IP Rating	IP20/ IP40 (front)

Cut outs (mm)	Wattage (W)	Lumens (lm)
90/100	6W	600 lm
125	9W	900 lm
150	9W 12W	900 lm 1200 lm
175	15W	1600 lm
200	19W	2100 lm

Cut outs (mm)	Wattage (W)	Lumens (lm)
100	6W	600 lm
125	9W	950 lm
150	13W	1300 lm

Cut outs (mm)	Wattage (W)	Lumens (lm)
150	9W	950 lm
175	12W	950 lm
200	15W	1200 lm
225	19W	1500 lm

Meson Downlights

Slim design for low ceiling

Ultra large diffuser with even light output

High lumen output for different application

Integrated driver with body flow curve

Application Areas

- Retail
- Offices
- Hospitality

Specs

Color Rendering Index (CRI)	80
Color Temperature (K)	3000K/ 4000K/ 6500K
Lifetime (hrs)	15,000 hrs
IP Rating	IP20

Round Recessed



Cut outs (mm)	Wattage (W)	Lumens (lm)
80	3.5W	235 lm
90	5W	430 lm
105	9W	680 lm
125	13W	960 lm
150	17W	1300 lm
175	21W	1500 lm
200	24W	1820 lm

Square Recessed



Cut outs (mm)	Wattage (W)	Lumens (lm)
105	9W	640 lm
125	13W	960 lm
150	17W	1280 lm

Surface Mounted



Cut outs (mm)	Wattage (W)	Lumens (lm)
150	17W	1300 lm
200	24W	1900 lm

COB Hybrid DN036 Downlight



Accent lighting

Up to 2400 lumens

High wattage offering

Suitable for low ceilings

Application Areas

- Retail
- Commercial buildings
- Shopping mall
- Residential
- Hospitality
- Office areas

Specs

Wattage (W)	30W
Color Temperature (K)	2700K/ 6500K
Lumen Output (lm)	2400 lm
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
IP Rating	IP20

DL360 Downlights (COB Hybrid Downlights in smaller cut outs)



Smaller cut outs available

Accent lighting

Creates natural ambiance

Suitable for low ceilings

Application Areas

- Retail
- Commercial buildings
- Shopping mall
- Residential
- Hospitality
- Office areas

Specs

Wattage (W)	6W/8W
Cut outs available (Round recessed)	70mm & 90mm
Color Temperature (K)	3000K/ 4000K/ 6500K
Lumen Output (lm)	450 lm/600 lm
Color Rendering Index (CRI)	80
IP Rating	IP20



External Driver Slim DL252 Downlight

External Driver

Available in recessed and surface mounted range

Metal housing

Super slim downlight

Application Areas

- Retail
- Offices
- Hospitality

Specs

Color Rendering Index (CRI)	80
Color Temperature (K)	3000K/4000K/6500K
Lifetime (hrs)	15,000 hrs
IP Rating	IP20

Round Recessed



Cut outs (mm)	Wattage (W)	Lumens (lm)
100	6W	400 lm
150	12W	900 lm
200	18W	1300 lm
275	24W	2000 lm

Surface Mounted



Cut outs (mm)	Wattage (W)	Lumens (lm)
150	12W	890 lm
200	18W	1300 lm
275	24W	2000 lm




HV HLS168 LED Strip (50 mts roll)

Plug and play solution

NO driver required

Built-in LED

Transparent



Connector required

Application Areas

- Creative lighting
- COVE lighting
- Furniture lighting
- Cabinets lighting

Specs

Wattage (W)	9W/m, 7.5W/m
Color Temperature (K)	3000K/ 4000K/ 6500K
Lumen Output (lm)	600lm/m, 350lm/m
Color Rendering Index (CRI)	80
Lifetime (hrs)	15,000 hrs
IP Rating	IP20

MASTER LED Professional Series



Master LED Bulbs



Crown Shape Master LED Candles & Luster Dimmable



Master Filament Bulb Dimmable



ExpertColor MR16 LED lamps



Master High Lumen MR16 Dimmable



Master MR16 LED Spot Dimmable



Master LED Spot MR16 Non-dimmable



Master Value MR16 LED Lamps



Master ExpertColor GU10 Spots



Master PAR LED



Master LED Spot PAR



Master Expert Color LEDspot LV AR111 Dimmable



Master LED Spot LV Non-dimmable



Sensor T8 LED Tubes



Master LED Tubes T5 Ultra Output



Master LED Tubes T5 High Output



Master T5 LED Tubes High Efficiency



Master LED Tubes T8 Ultra Efficiency



Master LED Tubes T8 Ultra Output



Master LED Tubes T8 High Output



CorePro LED Tubes T8 Ultra Output



CorePro T8 LED Tubes



Master Value LED Tubes T8 Ultra Output



Master Value LED Tubes High Output



Master LED Tube G5 Non-dimmable



LED PLC



TrueForce LED Mains



TrueForce LED Highbay



TrueForce LED Post Top



Master - LED HID SON T

Master LED Bulbs



Clear/frosted glass/
plastic options

Retrofit replacement for
conventional lamps

30% energy saving

Eye comfort

Application Areas

- For general lighting applications
- Staircase
- Lobbies
- Corridors

Specs

Lamp Wattage (W) 3.4W/5.9W/7.2W/8W/10.5W

Lumen Output (lm) 470/806/1055/1521lm

Color Temp. (K) 2000K-2700K

Product lifetime 25,000 hrs

CRI 80

Crown Shape Master LED Candles & Luster Dimmable



Retrofit replacement for
conventional lamps

IK 04 Rating

Long Life Time

High Lumens

Application Areas

- General lighting application in hospitality industry
- Stair wells
- Lobbies
- Corridors

Specs

Lamp Wattage (W) 5.5W

Lumen Output (lm) 470lm

Color Temp. (K) 2200K-2700K

Product lifetime 25,000 hrs

CRI 80





Master Filament Bulb

Dimmable



Filament LED technology

Energy saving

Classic heritage design

Clear glass bulbs/candles

Application Areas

- General lighting applications

Specs

Lamp Wattage (W)	2.8W/3.4W/5.9W/8W
Lumen Output (lm)	250/470/806lm
Color Temp. (K)	2000K-2700K
Product lifetime	25,000 hrs
CRI	80



ExpertColor MR16 LED Lamps



Custom color spectrum replication

Trimless design with V-groove lens

Broad transformer compatible dimming

MR16 retrofit option

Application Areas

- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- Home: living room, bedrooms, hall way
- Retail: exhibitions, display cabinets, shops, dressing rooms

Specs

Lamp Wattage (W)	6.7W
Lumen Output (lm)	450/480lm
Color Temp. (K)	2700/3000/4000K
Product lifetime	40,000hrs
CRI	97
Driver	12V



Master High Lumen MR16

Dimmable



Multiple beam angle choices

Intense accent beam

Energy saving

Dimmable for atmosphere control

Application Areas

- Residential
- Hospitality

Specs

Lamp Wattage (W)	7.5W
Lumen Output (lm)	660lm
Color Temp. (K)	2700/3000K
Product lifetime	40,000hrs
CRI	80
Driver	12V

Master MR16 LED Spot

Dimmable



Intense accent beam

Dimmable for atmosphere control

High CRI

Energy savings

Application Areas

- Home: Living room, bed room, hall way
- Hospitality: Hotel guest room, corridors, lobby, reception area, restaurant, bars, cafes
- Retail: Exhibitions, display cabinets, shops, dressing room, check out area

Specs

Lamp Wattage	6.5W
Lumen output	500lm
Color temp	2700K/3000/4000K
Product lifetime	40,000 hrs
CRI	90
Driver	12V

Master LED Spot MR16

Non-dimmable



Spots retrofit solution

Heat-sensitive object lighting

Dimmable for atmosphere control

Multiple beam angle choices

Application Areas

- General lighting applications in hospitality industries
- Lobbies
- Washrooms
- Receptions

Specs

Lamp Wattage (W)	3.9/4.9W
Lumen Output (lm)	240/415/450lm
Color Temp. (K)	2700/3000/4000K
Product lifetime	25,000hrs
CRI	80
Driver	12V

Master Value MR16

LED Lamps



Dimmable range

Patented intelligent driver

MR16 retrofit option

No UV/IR heat emission

Application Areas

- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)

Specs

Lamp Wattage (W)	7.5W
Lumen Output (lm)	621/630/660lm
Color Temp. (K)	2700/3000/4000K
Product lifetime	25,000hrs
CRI	80
Driver	12V

Master ExpertColor

GU10 spots



Warm halogen like
accent beam

Eyecomfort

Suitable for accent lighting

High CRI

Application Areas

- Residential and hospitality projects
- Applied in damp and dry locations

Specs

Lamp Wattage (W)	4.9W
Lumen Output (lm)	395lm
Color Temp. (K)	2700/4000K
Product lifetime	25,000 hrs
CRI	90

Master PAR LED



CDM PAR30L retrofit option

Mercury-free

No fading colors

UV- and IR-free light

Application Areas

- Shops
- Hotel
- Restaurants
- Museums

Specs

Lamp Wattage (W)	20W/32W
Lumen Output (lm)	1800/1850/3000lm
Color Temp. (K)	3000K/4000K/5700K
Product lifetime	25,000hrs
CRI	>80

Master LED Spot PAR



Retrofitable and compatible design

Dimmable range

UV- and IR-free light

Mercury-free

Application Areas

- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- Home: living room, bedrooms, hall way
- Retail: exhibitions, display cabinets, shops, dressing rooms

Specs

Lamp Wattage (W) 6W/13W

Lumen Output (lm) 520/1000lm

Color Temp. (K) 2700K

Product lifetime 25,000hrs

CRI 80/90

Master Expert Color LEDspot LV AR111 Dimmable



Award winning design

High intensity of beam

Retrofitable with G53 luminaires



Application Areas

- Retail: fashion, cosmetics, jewelry, food, concept stores, museums, exhibitions
- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- Home: dining room, living room, hall way

Specs

Lamp Wattage (W) 11W/15W

Lumen Output (lm) 650/680/950/1000lm

Color Temp. (K) 2700K/3000K

Product lifetime 40,000hrs

CRI 63/97

Driver 12V



Master LED Spot LV

Non-dimmable



MR16 retrofit option

Patented intelligent driver

No UV and Cool Beam (no IR)

Broad compatibility
with transformers

Application Areas

- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)

Specs

Lamp Wattage (W) 3.5W

Lumen Output (lm) 210lm

Color Temp. (K) 2700K

Product lifetime 40,000hrs

CRI 80

Driver 12V

Choose the right LED tube for every application

T8 fixture			
CorePro LEDtube SO	Corepro LEDtube UO	MASTER Value LEDtube HO	MASTER Value LEDtube UO
Up to 2200 lm	Up to 3500 lm	Up to 3100 lm	Up to 3700 lm

Value and features:



Application Areas



Industry

Burning hours: varies, max. 24/7
Light requirement: 200-500+ lux



Warehouses/factories

Burning hours: 12 hrs/day to 24/7
Light requirement: 200-300 lux



Car park

Burning hours: 24/7
Light requirement: 200+ lux



Supermarket/retail

Burning hours: 12 hrs/day to 24/7
Light requirement: 500+ lux



Office/school/healthcare

Burning hours: usually 12 hrs/day
Light requirement: 500+ lux



Public buildings

Burning hours: 12 hrs/day to 24/7
Light requirement: 100-500+ lux



				T5 fixture		
MASTER LEDtube HO	MASTER LEDtube UO	MASTER LEDtube UE	MasterConnect LEDtube	MASTER LEDtube HE	MASTER LEDtube HO	MASTER LEDtube UO
Up to 3100 lm	Up to 3700 lm	Up to 3700 lm	Up to 3700 lm	Up to 3000 lm	Up to 3900 lm	Up to 5600 lm



✓	✓	✓	✓		✓	✓
✓	✓	✓	✓		✓	✓
					✓	
✓	✓	✓	✓		✓	
✓	✓	✓	✓	✓		
✓			✓	✓	✓	

Sensor T8 LED Tubes



Easy installation

Visible light communication

Highly energy-efficient

In-built sensor

Application Areas

- Hospitality, retail, office, industrial applications

Specs

Lamp Wattage (W) 16W

Lumen Output (lm) 1800lm

Size L1200- 16W

Color Temp. (K) 6500K

Product lifetime 30,000hrs

CRI 80

Master LED Tubes T5 Ultra Output



Replacement of existing T5 lamps

Energy savings

No mercury

Instant on, no flicker

Application Areas

- Offices, shops, classrooms
- Industrial facilities and warehouses

Specs

Lamp Wattage (W) 36W

Lumen Output (lm) Upto 5600lm

Size L1500

Color Temp. (K) 3000K / 4500K / 6500K

Product lifetime 50000 hrs

CRI 80

Master LED Tubes T5 High Output



Replacement of existing T5 lamps

No mercury

Energy savings

Instant on, no flicker

Application Areas

- Offices, shops, classrooms
- Industrial facilities and warehouses

Specs

Lamp Wattage 10.5W/ 18.5/ 26W

Lumen Output Upto 3900lm

Size L600/L900/L1200/L1500

Color Temperature 3000K /4500K /6500K

Product Lifetime 50000 hrs

CRI 80

Master T5 LED Tubes High Efficiency



Plastic shell

Instant on, no flicker or buzz

Easy installation

Up to 50% energy saving

Application Areas

- Office, Shop, Education, Retail
- Industrial facilities and warehouses

Specs

Lamp Wattage (W) 7W/11.5W/16.5W/20W

Lumen Output (lm) upto 3000 lm

Size L600/ L900/ L1200/ L1500

Color Temp. (K) 3000K/4000K/6500K

Product lifetime 30,000hrs

CRI 80



Master LED Tubes T8 Ultra Efficiency

Rotatable end-cap

Plastic shell

Upto 185lm/W

HACCP-enabled

Application Areas

- Industry & warehouse
- Office, education & retail

Specs

Lamp Wattage (W) 11.9W/13.5W / 17.6W/20W

Lumen Output (lm) Up to 3700lm

Size L1200/L1500

Color Temp. (K) 3000K/4500K/6500K

Product lifetime 75000 to 100000hrs

CRI 80





Master LED Tubes T8 Ultra Output

Retrofit existing T8 lamps on
EM ballast or mains

No mercury

Energy savings

Extra-long life up to
75,000 hours

Application Areas

- Parking lots / covered car parks
- Warehouses / coldrooms / signage
- Transport and distribution areas
- Food & Museum

Specs

Lamp Wattage	14.7W/ 21.7W
Lumen Output	Up to 3700lm
Size	L1200/L1500
Color Temperature	3000K/4500K/6500K
Product Lifetime	75000 HRS
CRI	80



Master LED Tubes T8 High Output



Retrofit existing T8 lamps on EM ballast or mains

Energy saving

No mercury

Extra-long life up to 60,000 hours

Application Areas

- Parking lots / covered car parks
- Warehouses / coldrooms / signage
- Transport and distribution areas
- Museum

Specs

Lamp Wattage (W)	8W/13W
Lumen Output (lm)	Up to 2100lm
Size	L600/L1200
Color Temp. (K)	3000K/4500K/6500K
Product lifetime	60,000hrs
CRI	80

CorePro LED Tubes T8 Ultra Output



Upto 50% Energy saving

Easy Installation

Glass shell

Retrofit solution

Application Areas

- Offices
- Banks
- Education
- Food and Large Retailers
- Light Commercial

Specs

Lamp Wattage (W)	8W/18W/24W
Lumen Output (lm)	Upto 3500 lm
Size	L600, L1200, L1500
Color Temp. (K)	3000K/4500K/ 6500K
Product lifetime	50,000 hrs
CRI	80

CorePro T8 LED Tubes



Glass shell

Instant on, no flicker or buzz

Easy installation

Up to 50% energy saving

Application Areas

- Parking lots and covered car parks, warehouses
- Retail, offices
- Public areas

Specs

Lamp Wattage (W) 9W/16W/20W

Lumen Output (lm) Up to 2200lm

Size L600 , L1200

Color Temp. (K) 4000K/6500K

Product lifetime 30,000hrs

CRI 80

Master Value LED Tubes T8 Ultra Output



Retrofit replacement for T8 lamps

No mercury

Energy savings

Glass shell

Application Areas

- Office
- Retail
- Industrial Buildings & Warehouses
- Parking

Specs

Lamp Wattage 15.5W/23W

Lumen Output Up to 3700lm

Size L1200/L1500

Color Temperature 3000K/4500K/6500k

Product Lifetime 60,000 hrs

CRI 80

Master Value LED Tubes High Output



T8 retrofit solution

Easy to install

Glass shell

> 50% energy savings

Application Areas

- Office
- Retail
- Industrial Buildings & Warehouses
- Parking

Specs

Lamp Wattage (W)	8W/14W/20.5W
Lumen Output (lm)	1000/1050/2000/2100/2900/3100lm
Size	L600, L1200, L1500
Color Temp. (K)	3000K/4000K/6500K
Product lifetime	50,000hrs
CRI	80

Master LED Tube G5 Non-dimmable



Easy Installation

Energy savings

Highly energy efficient

No mercury

Application Areas

- Commercial buildings
- Industrial applications
- Back of house applications
- Utility rooms

Specs

Lamp Wattage	8W/ 20W
Lumen Output	Upto 2200lm
Size	L600/L1200
Color Temperature	12000k
Product Lifetime	15000 hrs
CRI	70

LED PLC



Easy installation

Energy saving

No Mercury

Highly energy efficient

Application Areas

- Hospitality
- Retail
- Office
- Industrial
- Home applications

Specs

Lamp Wattage	6.5W / 9W
Lumen Output	600lm, 650lm, 900lm
Color temperature	3000K/4000K
Product Lifetime	30,000 hrs
CRI	83

TrueForce LED Mains



High energy efficiency

Direct mains connection

Improved lighting quality adoption

Pleasant white light with CRI 80

Application Areas

- Industrial/retail - warehouses, factories, shops, transport hubs

Specs

Lamp Wattage (W)	160W
Lumen Output (lm)	20000/25000lm
Color Temp. (K)	4000K/6500K
Product lifetime	50,000hrs
CRI	90



TrueForce LED Highbay

Multi-purpose relamping solution

Multiple beam angle for every application

High CRI

Long lifetime of 50,000 hours



Application Areas

- Food and large retailers
- Manufacturing
- Retail

Specs

Lamp Wattage (W)	95W/150W
Lumen Output (lm)	13000/20000lm
Color Temp. (K)	4000K
Product lifetime	50,000hrs
CRI	80

TrueForce LED Post Top



Lightweight

Up to 4KV surge protection

High energy efficiency

No rewiring needed retrofit

Application Areas

- Road and street
- Parking garages
- Parks and plazas

Specs

Lamp Wattage (W)	21W/28W/42W
Lumen Output (lm)	2900/3000/3800/4000/5700/6000lm
Color Temp. (K)	3000K/4000K
Product lifetime	50,000hrs
CRI	80

Master – LED HID SON T



High Energy efficient lamps

Direct lamp replacement solution

Surge protection 6KV Applications

Right size and light distribution for retrofit

Application Areas

- Road and Street
- Tunnel
- Parking Garages


Specs

Lamp Wattage	Up to 55W
Lumen Output	Up to 9000 lm
Color Temperature	2700K/3000K/4000K
Product Lifetime	50,000 hrs
CRI	70

Solar-powered Lighting Solutions



Solar Wall light
(BWS010 G2)




Solar Wall light
(Up and Down)(BWC010)



Solar Flood Light
(High Power)(BVC080)



Solar Flood Light
(Med power)(BVC080)



Smart Bright Solar Flood Light
(High power)(BVP080)




Compact Floodlight
(BVS010)




Solar All in-One Streetlight
(Metal body) (BRC010)



Solar All in-One Streetlight
(BRC010)



Solar All in-One Streetlight
with wall mounting KIT(BRC010)



Solar All in- Two Streetlight
(BRP216)



Solar All in- One Post Top
(BPC010)



SmartBright Solar
All in-One Streetlight (BRP110)



Solar Indoor Suspended
(SP010P)

Philips Smartbright & Essential Smartbright Solar Products



Environmentally friendly

By harnessing the power of the sun, solar lighting solution reduces your carbon footprint and minimizes your impact on the environment. Feel good about your choice while enjoying reliable and high-quality illumination.



Zero energy cost

Designed to operate autonomously without any connection with an electrical grid. The solar panels charge the batteries during the day and stored energy powers the LEDs at night.



Low maintenance

Philips solar powered lighting is the low-maintenance solution you've been looking for. It's designed to be reliable and durable, with minimal upkeep required to keep it running smoothly.



Easy to install

Install Philips solar lights in a few easy steps. Consumers who have mounted our products recognize they are easy to install and consider it as an important benefit.



High quality light

Designed to deliver bright and long-lasting illumination with its LED technology, Philips solar lights offers an impressive efficacy of up to 150lm/W. With an autonomy of up to 12 hours, it's a convenient option for any outdoor lighting needs.



High performance battery

With a long battery lifetime and quick 4-5 hour charging time to 100%, our solar lightings can provide bright and reliable illumination for up to 6 hours on a single full charge.



Solar Wall Light (BWS010 G2)



Easy installation

Motion sensor

All in one construction

Easy to use

Application Areas

- External Walls
- Security
- Gates

Specs

Wattage (W)	0.5W/1W/3W
Conventional equivalent (W)	5W/10W/30W
Lumen Output (lm)	50/100/300lm
Color Temp. (K)	6500K
CRI	70
IP Rating	IP54
LED lifetime	25,000 hrs

Solar Wall light (Up and Down)(BWC010)



Easy installation

Up and Down light

All in one construction

High back-up time

Application Areas

- Landscape
- Lawns
- Pathways
- Walls

Specs

Wattage (W)	0.75W
Conventional equivalent (W)	10W
Lumen Output (lm)	100lm
Color Temp. (K)	3000K
CRI	70
IP Rating	IP65
LED Lifetime	15,000 hrs

Solar Flood Light (High Power) (BVC080)



Long lasting

DIY easy configuration

Up to 4000 lumens

All in one solution

Application Areas

- Outdoor courtyard
- Garden
- Farms
- Amenity

Specs

Wattage (W)	20W/23W/26W
Conventional equivalent (W)	250W / 300W/ 400W
Lumen Output (lm)	2500lm/3000lm/4000lm
Color Temp. (K)	3000K/6500K
CRI	70
IP Rating	IP65
LED Lifetime	25,000hrs

Solar Flood Light (Med Power) (BVC080)



Long lasting

DIY easy configuration

Up to 1500 lumens

All in one packaging

Application Areas

- Outdoor parking areas
- Outdoor decoration
- Parks

Specs

Wattage (W)	4W/6W/10W
Conventional equivalent (W)	60W/ 90W/ 150W
Lumen Output (lm)	600lm/900lm/1500lm
Color Temp. (K)	3000K/ 6500K
CRI	80
IP Rating	IP65
LED Lifetime	15,000 hrs

Smart Bright Solar Flood Light (High Power)(BVP080)



Long lasting

DIY easy configuration

Up to 4800 lumens

5 meters cable included

Application Areas

- Outdoor courtyard
- Garden
- Farms
- Amenity

Specs

Wattage (W)	6.5W/13W/20W/32W
Conventional equivalent (W)	100W/ 200W/ 300W/ 500W
Lumen Output (lm)	1000lm/2000lm/3000lm/4800lm
Color Temp. (K)	5700K
CRI	80
IK Rating	IK07
IP rating	IP65
LED Lifetime	25,000 hrs

Compact Floodlight (BVS010)



Adjustable light module

Easy installation

Compact design

In-built motion sensor

Application Areas

- Outdoor courtyard
- Gardens
- Amenity
- Residential

Specs

Wattage (W)	5W/10W
Conventioanl equivalent (W)	50W/100W
Lumen Output (lm)	500lm/1000lm
Color Temperature (K)	3000K/4000K/6500K
Color Rendering Index (CRI)	≥70
IP Rating	IP65

Solar All in-One Streetlight Metal Body (BRC010)



Metal body

Compact design

Up to 4000 lumens

In-built microwave sensor

Application Areas

- Outdoor parking areas
- Residential streets
- Pedestrian areas
- Small roads
- Parks

Specs

Wattage (W)	6.4W/13.1W/25W
Conventional equivalent (W)	100W / 200W/ 400W
Lumen Output (lm)	1000lm/2000lm/4000lm
Color Temp. (K)	6500K
CRI	70
IP Rating	IP65
LED Lifetime	25,000 hrs

Solar All in-One Streetlight (BRC010)



Comes with IR remote

Lightweight

Easy to install

In-built microwave sensor

Application Areas

- Outdoor parking areas
- Residential streets
- Pedestrian areas
- Small roads
- Parks

Specs

Wattage (W)	7.3W/15.2W/24.7W
Conventional equivalent (W)	100W / 200W/ 400W
Lumen Output (lm)	1000lm/2000lm/4000lm
Color Temp. (K)	6500K
CRI	70
IP Rating	IP65
LED Lifetime	15,000 hrs

Solar All in-One Streetlight

With Wall Mounting KIT(BRC010)



Comes with IR remote

Easy to install

With wall mounting bracket

In-built microwave sensor

Application Areas

- Outdoor parking areas
- Residential streets
- Pedestrian areas
- Small roads
- Parks

Specs

Wattage (W)	7.3W/15.2W/24.7W
Conventional equivalent (W)	100W / 200W/ 400W
Lumen Output (lm)	1000lm/2000lm/4000lm
Color Temp. (K)	6500K
CRI	70
IP Rating	IP65
LED Lifetime	15,000 hrs

Solar All in-Two Streetlight

(BRP216)



Easy installation

External solar panel

Die cast aluminum housing

Professional light distribution

Application Areas

- Streets
- Parks & plazas
- Parking
- Pedestrian pathway
- Shopping centers

Specs

Wattage (W)	11W/17W/23W
Conventional equivalent (W)	200W / 300W/ 400W
Lumen Output (lm)	2000lm/3000lm/4000lm
Color Temp. (K)	4000K
CRI	70
IP/IK rating	IP65/IK08 (Luminaire)
Lighting efficacy	>180 lm/W
Additional specs	Inbuilt LiFePO4 battery and MPPT controller

Solar All in-One Post Top (BPC010)



Shock and vibration resistant

Selectable color temperature

Up to 5000 lumens

In-built microwave sensor

Application Areas

- Landscape
- Lawns
- Pathways

Specs

Wattage (W)	12W/18W/24W/30W
Conventional equivalent (W)	200W / 300W/ 400W / 500W
Lumen Output (lm)	2000lm/3000lm/4000lm/5000lm
Color Temp. (K)	3000K/ 4000K/ 6500K (Selectable)
CRI	70
IP Rating	IP65
LED Lifetime	25,000 hrs
Pole entry dia 60mm	Pole entry dia 60mm

SmartBright Solar All in-One Streetlight (BRP110)



Tilt-able LED source

Up to 2 nights back up

Built-in charge controller

Microwave based motion sensor

Application Areas

- Gardens
- Walkways
- Small roads

Specs

Wattage (W)	27W/42W/65W/92W
Lumen Output (lm)	5000lm/8500lm/12000lm/18000lm
Color Temp. (K)	5700K
CRI	70
IP Rating	IP65
IK rating	IK08



Solar Indoor Suspended (SP010P)



Easy to install

Portable solution

DIY kit

Rechargeable batteries

Application Areas

- Home gardens
- General lighting indoor/outdoor
- Portable lighting point

Specs

Wattage (W)	6W
Conventional equivalent (W)	70W
Lumen Output (lm)	700lm
Color Temp. (K)	6500K
CRI	70



©2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.mea.lighting.philips.com