

### PILA candles



Product description	PILA LED 25W E14 WW B35 FR ND	PILA LED 25W B35 E14 WW FR ND 1CT/10	PILA LED 40W B35 E14 WW FR ND 1CT/10	PILA LED 25W E14 WW B35 CL ND
Light output (lm)	250	250	470	250
Power (W)	3.2	3.2	5.5	3.3
сст (к)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	No
Lamp shape	Candle	B35	B35	Candle
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A+	A+	A+	A+
EAN	8718696485248	8727900964158	8727900964196	8718696485224
12NC				

- ▶ Different kinds of versions
- ► Cosy ambience



## PILA candles



Product description	PILA LED 40W B35 E14 WW FR DIM 1CT/10	PILA LED 40W E14 WW B35 FR ND	PILA LED 25W B35 E14 WW CL ND 1CT/10
Light output (lm)	470	470	250
Power (W)	6	5.5	3.2
ССТ (К)	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80
Dimming	Yes	Yes	No
Lamp shape	B35	Candle	B35
Color	Warm White	Warm White	Warm White
Energy efficiency class	A+	A+	A+
EAN	8718696549230	8718696549230	8727900964172
12NC			

- ▶ Different kinds of versions
- ► Cosy ambience



### PILA lustres



Product description	PILA LED 25W E14 WW P45 FR ND	PILA LED 25W E27 WW P45 FR ND	PILA LED 40W P45 E14 WW P45 FR ND	PILA LED 40W E14 WW P45 FR ND
Light output (lm)	250	250	470	470
Power (W)	3.2	3.2	5.5	5.5
ССТ (К)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80	80
Dimming	No	No	No	No
Lamp shape	Lustre	Lustre	P45	Lustre
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A+	A+	Α+	A+
EAN	8718696485309	8718696485323	8727900964271	8718696485347
12NC				

- ▶ Different kinds of versions
- ► Cosy ambience



#### PILA lustres



Product description	PILA LED 40W E14 WW P45 FR ND	PILA LED 40W P45 E27 WW P45 FR ND	PILA LED 25W P45 E27 WW CL ND 1CT/10	PILA LED 25W P45 E14 WW FR ND
Light output (lm)	470	470	250	250
Power (W)	5.5	5.5	3.2	3.2
CCT (K)	2700	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs	15000 hrs
CRI	80	90	80	80
Dimming	No	No	No	No
Lamp shape	Lustre	P45	P45	P45
Color	Warm White	Warm White	Warm White	Warm White
Energy efficiency class	A+	A+	A+	A+
EAN	8718696485347	8727900964295	8727900964257	8727900964752
12NC				

- ▶ Different kinds of versions
- ► Cosy ambience



# PILA lustres



Product description	PILA LED 25W E14 WW P45 CL ND	PILA LED 25W P45 E14 WW CL ND 1CT/10	PILA LED 25W P45 E27 WW FR ND 1CT/10
Light output (lm)	250	250	250
Power (W)	3.3	3.2	3.2
сст (к)	2700	2700	2700
Mains voltage	220-240V / 50Hz	220-240V / 50Hz	220-240V / 50Hz
Lifetime	15000 hrs	15000 hrs	15000 hrs
CRI	80	80	80
Dimming	No	No	No
Lamp shape	Lustre	P45	P45
Color	Warm White	Warm White	Warm White
Energy efficiency class	A+	A+	A+
EAN	8718696485286	8727900964233	8727900964417
12NC			

- ▶ Different kinds of versions
- ► Cosy ambience