

OUTDOOR STOCK LIGHTING



HID CONVERSION GUIDE

LUMARK

Lumark combines value-engineered specification-grade lighting features with market-leading retrofit solutions to enable contractors to get on and off the job quickly and deliver superior illumination coverage.

LUMARK AP

Lumark AP provides high-value outdoor lighting products that are always in stock and supported with decades of experience and expertise in the industry. Simple. Outdoor. Lighting.



HID Equivalent Metal Halide		70W – 100W	150W – 250W	250W – 400W	400W – 750W	750W – 1000W	1000W – 1250W	1250 - 1500W
Area & Site								
Prevail Discrete Series		PRV-P	✓ PA1A, PA1B	✓ PA1C, PA1D				
		PRV	✓ PA1A	✓ PA1B	✓ PA2A, PA2B			
		PRV-XL				✓ PA3A, PA3B, PA4A	✓ PA4B	
		PRV-Maxx				✓ PA6A	✓ PA6B	✓ PA6C
Prevail COB Series		PRV-P	✓ C10, C15	✓ C20, C25				
		PRV	✓ C15	✓ C25	✓ C40, C60			
		PRV-XL				✓ C75, C100, C125, C150	✓ C175	
		PRV-Maxx					✓ C200	✓ C225
LAS		LAS 45	✓ Position 8 - 9	✓ Position 4 - 7	✓ Position 0 - 3			
		LAS 100	✓ Position 8 - 9		✓ Position 4 - 7	✓ Position 0 - 3		

HID Equivalent Metal Halide		70W – 100W	150W – 250W	250W – 400W	400W – 750W	750W – 1000W	1000W – 1250W	1250 - 1500W
Floodlighting								
Night Harrier Series		NHR50				✓		
		NHR100				✓	✓	
Night Falcon Series		Small	✓					
		Medium		✓	✓	✓		
		Large				✓	✓	
LSF		Small	✓					
		Medium	✓	✓				
		Large	✓	✓	✓			

HID Equivalent Metal Halide		70W – 100W	150W – 250W	250W – 400W	400W – 750W	750W – 1000W	1000W – 1250W	1250 – 1500W
Wall Mounted								
Axcent Series		AXCS	✓					
		AXCL	✓	✓	✓			
Crosstour		XTOR	✓					
		XTOR MAXX	✓	✓	✓			
Prevail Petite Wall		PRV-D	✓	✓				
		PRV-COB	✓	✓				
ASWP		ASWP1	✓					
		ASWP2	✓	✓				
WPM Wall Pack		WPM LED15S	✓	✓				
		WPM LED25S		✓	✓			