

Parking garages and other facilities require reliable, efficient lighting solutions or covered spaces with a wide range of performance and configurability. Cooper Lighting Solutions' parking garage and canopy solutions provide superior coverage and flexibility, available with controls and visual comfort optic distributions for even the most discerning lighting professional.



	Lumark AP	Lumark	McGraw-Edison		Metalux		
	CLCS	RPGC	TopTier Nano	TopTier	VT3 LED	APVT-S LED	
<b>Performance / Certifications</b>	LED Type	Polycarbonate Lens	Round Drop Lens	Waveguide	Waveguide	Captive Lens	Captive Lens
	HID Equivalent	up to 400W	up to 250W	--	--	--	--
	Wattage Range	40W - 120W	30W - 60W	10W - 59W	28W - 194W	17W - 70W	22W - 94W
	Del. Lumen (Max)	17,600 Selectable	7,800 Selectable	7,300	22,500	9,000	12,000 Selectable
	Lm/W(Max at 4000K)	153	125	133	146	154	147
	CCT Range	3000K - 5000K Selectable	4000K	3000K - 5000K	3000K - 5000K	3000K - 5000K	3000K - 5000K Selectable
	Distributions	--	--	5	5	3	--
	DLC <sup>1</sup>	Standard	Premium	Standard	Premium	Premium	Standard
	IP Rating	IP65	IP65	IP66	IP66	IP67	IP65
	Emergency Battery	--	--	--	Yes	Yes	--
	Mounting Available	Surface	Surface	Pendant, Stem, Surface, Trunnion	Pendant, Stem, Surface, Trunnion, Wall, Pole	Chain / Suspended Surface	Chain / Suspended Surface
	<b>Driver Options</b>	0-10V Dimming	Yes	Yes	Yes	Yes	Yes
Dali		--	--	Yes	Yes	Yes	--
<b>Integrated Controls</b>	Photocontrol Receptacle	--	--	Yes	Yes	--	--
	Occupancy	--	Yes	Yes	Yes	Yes	Yes
<b>Smart / Connected</b>	Wavelinx	--	Lite	--	Pro & Lite	Pro & Lite	Pro & Lite

	Sure Lites		
	SELD	UX HAZ	
<b>Product Spotlight</b>	Type	--	Box
	Material	Die-Cast Aluminum	Die-Cast Aluminum
	Color	AG / BK / WH	AL / WH / BK
	Mounting	Surface	Surface
	Faces	--	One or Two
	Letter Color	--	Green or Red
	Coverage	60 feet	--
	"2nd Circuit (A/C Only)"	--	Optional
	Battery	Nickel Cadmium	Nickel Cadmium
	Temp Range	-30° C to 50° C	<b>UX6:</b> -40° C to 50° C <b>UX7:</b> -30° C to 50° C
	Self Diagnostics	Standard	Standard
	Laser Test	Standard	Standard
	UL Rating	UL 924 Wet, NEMA 4X, HAZ option	UL 924 Wet, NEMA 4X, HAZ option
	City of Chicago Compliant	Standard	No
	Availability	Stock	Stock

(1) Consult [Designlights.org](http://Designlights.org)