



# LED Bollard II BCP150/151 – reliable landscape lighting for harmonious city living

## LED Bollard II

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience with optimized-quality lighting at minimum cost. Combining reliable low-power LEDs and an integrated driver, the robustly designed LED Bollard II delivers an affordable LED lighting solution to meet your landscaping needs.

### Benefits

- Reliable, robust design
- Easy to install and maintenance-free
- Environmentally friendly: no hazardous substances (no mercury, no lead) or UV

### Features

- Low-power white-light LED light source, available in a choice of warm white (3000 K) or neutral white (4000 K)
- Integrated baseplate and driver for easy installation
- Choice of colors for housing (dark grey RAL7043, light grey RAL9006)
- Height 0.5 m or 0.8 m
- Long lifetime of 25,000 hours (70% lumen maintenance @ T<sub>c</sub> = 25°C)
- IP65 protection and IK10 impact resistance

# LED Bollard II

## Application

- Parks and gardens
- Squares, plazas
- Residential areas

## Versions



LED module 15,000 lm



LED module 15,000 lm

### Approval and Application

Mech. impact protection code IK10

### Controls and Dimming

Dimmable No

### General Information

CE mark CE mark  
 Light source colour Warm white  
 Driver included Yes  
 Lamp family code LED3.4  
 Number of gear units 1 unit  
 Number of light sources 1

### Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature 3000 K

### Mechanical and Housing

Colour Grey

### Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
29887000	BCP150 LED150/WW PSU 220-240V 7043	-
29888700	BCP151 LED150/WW PSU 220-240V 7043	4/4 kV

## General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Optical cover/ lens type	Flammability mark	Light source replaceable
29887000	BCP150 LED150/WW PSU 220-240V 7043	-	PC-UV	-	-
29888700	BCP151 LED150/WW	-	OB	NO	No

Order Code	Full Product Name	Luminaire light beam spread	Optical cover/ lens type	Flammability mark	Light source replaceable
	PSU 220-240V 7043				

## LED Bollard II

### General Information (2/2)

Order Code	Full Product Name	Optic type
29887000	BCP150 LED150/WW PSU 220-240V 7043	-

Order Code	Full Product Name	Optic type
29888700	BCP151 LED150/WW PSU 220-240V 7043	Symmetrical

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Colour Rendering Index	Initial luminous flux
29887000	BCP150 LED150/WW PSU 220-240V 7043	>70	200 lm

Order Code	Full Product Name	Init. Colour Rendering Index	Initial luminous flux
29888700	BCP151 LED150/WW PSU 220-240V 7043	>75	340 lm

### Light Technical

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
29887000	BCP150 LED150/WW PSU 220-240V 7043	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
29888700	BCP151 LED150/WW PSU 220-240V 7043	-	0°	50

