



# Less Hassle, More Savings

## Essential SmartBright LED Downlight

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

### Benefits

- Reliability and safety: meets national and international regulation
- Energy saving: High system efficacy with lower power consumption
- Diversity: One stop shopping with multiple choices of recess round, square as well as surface-mount to fit your dedicated applications
- Easy to install with slim design

### Features

- Long life time: 20Khrs to 30Khrs(L70B50@25°C)
- System efficiency: up to 85lm/W
- One family offers recess round, square and surface mount options
- Slim design: 33mm housing body height

### Application

- Retail
- Office
- Residential


# Essential SmartBright LED Downlight

## Versions




Essential SmartBright DN027C RD

## Dimensional drawing




# Essential SmartBright LED Downlight

## Dimensional drawing




# Essential SmartBright LED Downlight

## Dimensional drawing




# Essential SmartBright LED Downlight

## Dimensional drawing




# Essential SmartBright LED Downlight

## Dimensional drawing



# Essential SmartBright LED Downlight

## Dimensional drawing



## Product details



Essential SmartBright DN027C  
Round

# Essential SmartBright LED Downlight

General Information	
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	80
Operating and Electrical	
Input Voltage	220 to 240 V
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class II

## General Information

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
911401816697	DN027C LED20/NW D225	-	-	-	-
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	-	-	-	-
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	-	-	-	-
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	-	-	-	-
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	-	-	-	-
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	-	-	-	-
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	-	-	-	-

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	-	-	-	-
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	-	-	-	-
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	-	-	-	-
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	-	-	-	-
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	-	-	-	-
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	-	-	-	-
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	-	-	-	-
929002509508	DN020B G3 LED9/NW 10.5W	-	-	-	-



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
	220-240V D125 GM				
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	-	-	-	-
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	-	-	-	-
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	-	-	-	-
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	-	-	-	-
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	-	-	-	-
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	-	-	-	-
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	-	-	-	-
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	-	-	-	-
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	-	-	-	-
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	-	-	-	-
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	-	-	-	-

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	-	-	-	-
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	-	-	-	-
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	-	-	-	-
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	-	-	-	-
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	-	-	-	-
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	-	-	-	-
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	-	-	-	-
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-	-	-	-
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	-	-	-	-
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	-	-	-	-
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	-	-	-	-

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	-	-	-	-
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	-	-	-	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-	-	-	-
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	-	-	-	-
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	-	-	-	-
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	-	-	-	-
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	-	-	-	-
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	-	-	-	-
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	-	-	-	-
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003269510	DN200 G3 LED3 830 3.5W D80 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003269610	DN200 G3 LED3 840 3.5W D80 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003269710	DN200 G3 LED3 865 3.5W D80 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929003269810	DN200 G3 LED4 830 4.5W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003269910	DN200 G3 LED4 840 4.5W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270010	DN200 G3 LED4 865 4.5W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270110	DN200 G3 LED6 830 6W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270210	DN200 G3 LED6 840 6W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270310	DN200 G3 LED6 865 6W D90 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270410	DN200 G3 LED6 830 7W D100 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270510	DN200 G3 LED6 840 7W D100 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270610	DN200 G3 LED6 865 7W D100 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270710	DN200 G3 LED6 830 6W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270810	DN200 G3 LED6 840 6W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003270910	DN200 G3 LED6 865 6W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929003271010	DN200 G3 LED9 830 10.5W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271110	DN200 G3 LED9 840 10.5W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271210	DN200 G3 LED9 865 10.5W D125 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271310	DN200 G3 LED9 830 9W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271410	DN200 G3 LED9 840 9W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271510	DN200 G3 LED9 865 9W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271610	DN200 G3 LED12 830 13W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271710	DN200 G3 LED12 840 13W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271810	DN200 G3 LED12 865 13W D150 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003271910	DN200 G3 LED15 830 16W D175 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003272010	DN200 G3 LED15 840 16W D175 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003272110	DN200 G3 LED15 865 16W D175 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929003272210	DN200 G3 LED20 830 20W D200 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003272310	DN200 G3 LED20 840 20W D200 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003272410	DN200 G3 LED20 865 20W D200 CN	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279417	DN020B G4 LED9/CW 10.5W	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
	220-240V D125				
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

### Light Technical



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous	
		Temperature (Nom)	(rated) (Nom)	Flux	Optic type
911401816697	DN027C LED20/NW D225	4000 K	-	2,000 lm	-
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	3000 K	80.00 lm/W	280 lm	-
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	4000 K	85.00 lm/W	300 lm	-
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	6500 K	85.00 lm/W	300 lm	-
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	3000 K	84.00 lm/W	380 lm	-
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	4000 K	88.00 lm/W	400 lm	-
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	6500 K	88.00 lm/W	400 lm	-
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	3000 K	78.00 lm/W	550 lm	-
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	4000 K	85.00 lm/W	600 lm	-
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	6500 K	85.00 lm/W	600 lm	-
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	3000 K	78.00 lm/W	550 lm	-

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous	
		Temperature (Nom)	(rated) (Nom)	Flux	Optic type
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	4000 K	85.00 lm/W	600 lm	-
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	6500 K	85.00 lm/W	600 lm	-
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	3000 K	80.00 lm/W	850 lm	-
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	4000 K	85.00 lm/W	900 lm	-
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	6500 K	85.00 lm/W	900 lm	-
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	3000 K	80.00 lm/W	850 lm	-
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	4000 K	85.00 lm/W	900 lm	-
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	6500 K	85.00 lm/W	900 lm	-
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	3000 K	82.00 lm/W	1,150 lm	-
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	3000 K	82.00 lm/W	1,150 lm	-
929002510108	DN020B G3 LED12/NW	4000 K	85.00 lm/W	1,200 lm	-

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy	Luminous	
		(Nom)	(Nom)	Flux	Optic type
	14W 220-240V D150 GM				
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	4000 K	85.00 lm/W	1,200 lm	-
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	6500 K	85.00 lm/W	1,200 lm	-
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	6500 K	85.00 lm/W	1,200 lm	-
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	3000 K	80.00 lm/W	1,450 lm	-
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	4000 K	83.00 lm/W	1,500 lm	-
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	6500 K	83.00 lm/W	1,500 lm	-
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	3000 K	82.00 lm/W	1,900 lm	-
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	4000 K	86.00 lm/W	2,000 lm	-
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	6500 K	86.00 lm/W	2,000 lm	-
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	3000 K	84.00 lm/W	380 lm	-
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	4000 K	88.00 lm/W	400 lm	-

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy	Luminous	
		(Nom)	(Nom)	Flux	Optic type
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	6500 K	88.00 lm/W	400 lm	-
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	3000 K	80.00 lm/W	850 lm	-
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	4000 K	85.00 lm/W	900 lm	-
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	6500 K	85.00 lm/W	900 lm	-
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	3000 K	82.00 lm/W	1,150 lm	-
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	4000 K	85.00 lm/W	1,200 lm	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	6500 K	85.00 lm/W	1,200 lm	-
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	3000 K	80.00 lm/W	1,450 lm	-
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	4000 K	83.00 lm/W	1,500 lm	-
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	6500 K	83.00 lm/W	1,500 lm	-
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	3000 K	82.00 lm/W	1,900 lm	-

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 KSA	4000 K	86.00 lm/W	2,000 lm	-
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 KSA	6500 K	86.00 lm/W	2,000 lm	-
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	3000 K	100 lm/W	600 lm	Beam angle 110°
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	4000 K	100 lm/W	600 lm	Beam angle 110°
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	6500 K	100 lm/W	600 lm	Beam angle 110°
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	3000 K	100 lm/W	1,200 lm	Beam angle 110°
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	4000 K	108 lm/W	1,300 lm	Beam angle 110°
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	6500 K	108 lm/W	1,300 lm	Beam angle 110°
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	3000 K	105 lm/W	2,000 lm	Beam angle 110°
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	4000 K	110 lm/W	2,100 lm	Beam angle 110°
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	6500 K	110 lm/W	2,100 lm	Beam angle 110°
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	3000 K	100 lm/W	300 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	4000 K	110 lm/W	330 lm	Beam angle 110°
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	6500 K	110 lm/W	330 lm	Beam angle 110°
929003269510	DN200 G3 LED3 830 3.5W D80 CN	3000 K	80 lm/W	280 lm	Matt optic decorative
929003269610	DN200 G3 LED3 840 3.5W D80 CN	4000 K	85 lm/W	300 lm	Matt optic decorative
929003269710	DN200 G3 LED3 865 3.5W D80 CN	6500 K	85 lm/W	300 lm	Matt optic decorative
929003269810	DN200 G3 LED4 830 4.5W D90 CN	3000 K	84 lm/W	380 lm	Matt optic decorative
929003269910	DN200 G3 LED4 840 4.5W D90 CN	4000 K	88 lm/W	400 lm	Matt optic decorative
929003270010	DN200 G3 LED4 865 4.5W D90 CN	6500 K	88 lm/W	400 lm	Matt optic decorative
929003270110	DN200 G3 LED6 830 6W D90 CN	3000 K	91 lm/W	550 lm	Matt optic decorative
929003270210	DN200 G3 LED6 840 6W D90 CN	4000 K	100 lm/W	600 lm	Matt optic decorative
929003270310	DN200 G3 LED6 865 6W D90 CN	6500 K	100 lm/W	600 lm	Matt optic decorative
929003270410	DN200 G3 LED6 830 7W D100 CN	3000 K	78 lm/W	550 lm	Matt optic decorative
929003270510	DN200 G3 LED6 840 7W D100 CN	4000 K	85 lm/W	600 lm	Matt optic decorative
929003270610	DN200 G3 LED6 865 7W D100 CN	6500 K	85 lm/W	600 lm	Matt optic decorative
929003270710	DN200 G3 LED6 830 6W D125 CN	3000 K	91 lm/W	550 lm	Matt optic decorative

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929003270810	DN200 G3 LED6 840 6W D125 CN	4000 K	100 lm/W	600 lm	Matt optic decorative
929003270910	DN200 G3 LED6 865 6W D125 CN	6500 K	100 lm/W	600 lm	Matt optic decorative
929003271010	DN200 G3 LED9 830 10.5W D125 CN	3000 K	80 lm/W	850 lm	Matt optic decorative
929003271110	DN200 G3 LED9 840 10.5W D125 CN	4000 K	85 lm/W	900 lm	Matt optic decorative
929003271210	DN200 G3 LED9 865 10.5W D125 CN	6500 K	85 lm/W	900 lm	Matt optic decorative
929003271310	DN200 G3 LED9 830 9W D150 CN	3000 K	94 lm/W	850 lm	Matt optic decorative
929003271410	DN200 G3 LED9 840 9W D150 CN	4000 K	100 lm/W	900 lm	Matt optic decorative
929003271510	DN200 G3 LED9 865 9W D150 CN	6500 K	100 lm/W	900 lm	Matt optic decorative
929003271610	DN200 G3 LED12 830 13W D150 CN	3000 K	88 lm/W	1,150 lm	Matt optic decorative
929003271710	DN200 G3 LED12 840 13W D150 CN	4000 K	92 lm/W	1,200 lm	Matt optic decorative
929003271810	DN200 G3 LED12 865 13W D150 CN	6500 K	92 lm/W	1,200 lm	Matt optic decorative
929003271910	DN200 G3 LED15 830 16W D175 CN	3000 K	90 lm/W	1,450 lm	Matt optic decorative
929003272010	DN200 G3 LED15 840 16W D175 CN	4000 K	93 lm/W	1,500 lm	Matt optic decorative
929003272110	DN200 G3 LED15 865 16W D175 CN	6500 K	93 lm/W	1,500 lm	Matt optic decorative
929003272210	DN200 G3 LED20 830 20W D200 CN	3000 K	95 lm/W	1,900 lm	Matt optic decorative
929003272310	DN200 G3 LED20 840 20W D200 CN	4000 K	100 lm/W	2,000 lm	Matt optic decorative

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929003272410	DN200 G3 LED20 865 20W D200 CN	6500 K	100 lm/W	2,000 lm	Matt optic decorative
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002675502	DN027B G3 LED12/NW 12W	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
	220-240V L150 RU				
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	3000 K	80 lm/W	280 lm	Beam angle 110°
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	4000 K	85 lm/W	300 lm	Beam angle 110°
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	6500 K	85 lm/W	300 lm	Beam angle 110°
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	3000 K	84 lm/W	380 lm	Beam angle 110°
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	4000 K	88 lm/W	400 lm	Beam angle 110°
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	6500 K	88 lm/W	400 lm	Beam angle 110°
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	3000 K	91 lm/W	550 lm	Beam angle 110°
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	4000 K	100 lm/W	600 lm	Beam angle 110°
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	6500 K	100 lm/W	600 lm	Beam angle 110°
929003278608	DN020B G4 LED6/WW 7W	3000 K	78 lm/W	550 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
	220-240V D100				
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	4000 K	85 lm/W	600 lm	Beam angle 110°
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	6500 K	85 lm/W	600 lm	Beam angle 110°
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	3000 K	91 lm/W	550 lm	Beam angle 110°
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	4000 K	100 lm/W	600 lm	Beam angle 110°
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	6500 K	100 lm/W	600 lm	Beam angle 110°
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	3000 K	80 lm/W	850 lm	Beam angle 110°
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	4000 K	85 lm/W	900 lm	Beam angle 110°
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	6500 K	85 lm/W	900 lm	Beam angle 110°
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	3000 K	94 lm/W	850 lm	Beam angle 110°
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	4000 K	100 lm/W	900 lm	Beam angle 110°
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	6500 K	100 lm/W	900 lm	Beam angle 110°

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	3000 K	88 lm/W	1,150 lm	Beam angle 110°
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	4000 K	92 lm/W	1,200 lm	Beam angle 110°
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	6500 K	92 lm/W	1,200 lm	Beam angle 110°
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	3000 K	90 lm/W	1,450 lm	Beam angle 110°
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	4000 K	93 lm/W	1,500 lm	Beam angle 110°
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	6500 K	93 lm/W	1,500 lm	Beam angle 110°
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	3000 K	95 lm/W	1,900 lm	Beam angle 110°
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	4000 K	100 lm/W	2,000 lm	Beam angle 110°
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	6500 K	100 lm/W	2,000 lm	Beam angle 110°
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002671602	DN027B G3 LED6/NW 6W	4000 K	100.00 lm/W	600 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
	220-240V D90 RU				
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	4000 K	108.00 lm/W	650 lm	Beam angle 110°
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	6500 K	108.00 lm/W	650 lm	Beam angle 110°
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002672802	DN027B G3 LED9/NW 9W	4000 K	105.00 lm/W	950 lm	Beam angle 110°

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy	Luminous Flux	Optic type
		(Nom)	(Nom)		
	220-240V D125 RU				
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	4000 K	111.00 lm/W	1,000 lm	Beam angle 110°
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	6500 K	111.00 lm/W	1,000 lm	Beam angle 110°
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002673538	DN027B G3 LED12/CW 12W	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy	Luminous Flux	Optic type
		(Nom)	(Nom)		
	220-240V D150 RD				
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	3000 K	100.00 lm/W	1,500 lm	Beam angle 110°
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	3000 K	105.00 lm/W	2,000 lm	Beam angle 110°
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	3000 K	100.00 lm/W	1,500 lm	Beam angle 110°
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	3000 K	105.00 lm/W	2,000 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	3000 K	100.00 lm/W	1,500 lm	Beam angle 110°
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
929002678140	DN500B G3 LED20/WW	3000 K	105.00 lm/W	2,000 lm	Beam angle 110°



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Luminous Optic type
		(K)	(lm/W)	(lm)	(°)
	19W 220V D200 RD				
929002678240	DN500B G3 LED20/NW	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Luminous Optic type
		(K)	(lm/W)	(lm)	(°)
	19W 220V D200 RD				
929002678340	DN500B G3 LED20/CW	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
	19W 220V D200 RD				

### Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
911401816697	DN027C LED20/NW D225	50 or 60 Hz	23 W
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	50 or 60 Hz	3.5 W
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	50 or 60 Hz	3.5 W
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	50 or 60 Hz	3.5 W
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	50 or 60 Hz	4.5 W
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	50 or 60 Hz	4.5 W
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	50 or 60 Hz	4.5 W
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	50 or 60 Hz	7 W
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	50 or 60 Hz	7 W
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	50 or 60 Hz	7 W
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	50 or 60 Hz	7 W
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	50 or 60 Hz	7 W
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	50 or 60 Hz	7 W
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	50 or 60 Hz	10.5 W
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	50 or 60 Hz	10.5 W
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	50 or 60 Hz	10.5 W
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	50 or 60 Hz	10.5 W
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	50 or 60 Hz	10.5 W
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	50 or 60 Hz	10.5 W

Order Code	Full Product Name	Line Frequency	Power Consumption
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	50 or 60 Hz	14 W
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	50 or 60 Hz	14 W
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	50 or 60 Hz	14 W
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	50 or 60 Hz	14 W
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	50 or 60 Hz	14 W
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	50 or 60 Hz	14 W
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	50 or 60 Hz	18 W
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	50 or 60 Hz	18 W
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	50 or 60 Hz	18 W
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	50 or 60 Hz	23 W
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	50 or 60 Hz	23 W
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	50 or 60 Hz	23 W
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	50 or 60 Hz	4.5 W
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	50 or 60 Hz	4.5 W
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	50 or 60 Hz	4.5 W
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	50 or 60 Hz	10.5 W
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	50 or 60 Hz	10.5 W
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	50 or 60 Hz	10.5 W
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	50 or 60 Hz	14 W

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	50 or 60 Hz	14 W
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	50 or 60 Hz	14 W
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	50 or 60 Hz	18 W
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	50 or 60 Hz	18 W
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	50 or 60 Hz	18 W
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	50 or 60 Hz	23 W
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	50 or 60 Hz	23 W
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	50 or 60 Hz	23 W
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	50 or 60 Hz	6 W
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	50 or 60 Hz	6 W
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	50 or 60 Hz	6 W
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	50 or 60 Hz	12 W
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	50 or 60 Hz	12 W
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	50 or 60 Hz	12 W
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	50 or 60 Hz	19 W
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	50 or 60 Hz	19 W
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	50 or 60 Hz	19 W
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	50 or 60 Hz	3 W
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	50 or 60 Hz	3 W
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	50 or 60 Hz	3 W
929003269510	DN200 G3 LED3 830 3.5W D80 CN	50 or 60 Hz	3.5 W
929003269610	DN200 G3 LED3 840 3.5W D80 CN	50 or 60 Hz	3.5 W
929003269710	DN200 G3 LED3 865 3.5W D80 CN	50 or 60 Hz	3.5 W
929003269810	DN200 G3 LED4 830 4.5W D90 CN	50 or 60 Hz	4.5 W
929003269910	DN200 G3 LED4 840 4.5W D90 CN	50 or 60 Hz	4.5 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929003270010	DN200 G3 LED4 865 4.5W D90 CN	50 or 60 Hz	4.5 W
929003270110	DN200 G3 LED6 830 6W D90 CN	50 or 60 Hz	6 W
929003270210	DN200 G3 LED6 840 6W D90 CN	50 or 60 Hz	6 W
929003270310	DN200 G3 LED6 865 6W D90 CN	50 or 60 Hz	6 W
929003270410	DN200 G3 LED6 830 7W D100 CN	50 or 60 Hz	7 W
929003270510	DN200 G3 LED6 840 7W D100 CN	50 or 60 Hz	7 W
929003270610	DN200 G3 LED6 865 7W D100 CN	50 or 60 Hz	7 W
929003270710	DN200 G3 LED6 830 6W D125 CN	50 or 60 Hz	6 W
929003270810	DN200 G3 LED6 840 6W D125 CN	50 or 60 Hz	6 W
929003270910	DN200 G3 LED6 865 6W D125 CN	50 or 60 Hz	6 W
929003271010	DN200 G3 LED9 830 10.5W D125 CN	50 or 60 Hz	10.5 W
929003271110	DN200 G3 LED9 840 10.5W D125 CN	50 or 60 Hz	10.5 W
929003271210	DN200 G3 LED9 865 10.5W D125 CN	50 or 60 Hz	10.5 W
929003271310	DN200 G3 LED9 830 9W D150 CN	50 or 60 Hz	9 W
929003271410	DN200 G3 LED9 840 9W D150 CN	50 or 60 Hz	9 W
929003271510	DN200 G3 LED9 865 9W D150 CN	50 or 60 Hz	9 W
929003271610	DN200 G3 LED12 830 13W D150 CN	50 or 60 Hz	13 W
929003271710	DN200 G3 LED12 840 13W D150 CN	50 or 60 Hz	13 W
929003271810	DN200 G3 LED12 865 13W D150 CN	50 or 60 Hz	13 W
929003271910	DN200 G3 LED15 830 16W D175 CN	50 or 60 Hz	16 W
929003272010	DN200 G3 LED15 840 16W D175 CN	50 or 60 Hz	16 W
929003272110	DN200 G3 LED15 865 16W D175 CN	50 or 60 Hz	16 W
929003272210	DN200 G3 LED20 830 20W D200 CN	50 or 60 Hz	20 W
929003272310	DN200 G3 LED20 840 20W D200 CN	50 or 60 Hz	20 W
929003272410	DN200 G3 LED20 865 20W D200 CN	50 or 60 Hz	20 W

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	50 or 60 Hz	6 W
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	50 or 60 Hz	6 W
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	50 or 60 Hz	9 W
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	50 or 60 Hz	9 W
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	50 or 60 Hz	12 W
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	50 or 60 Hz	12 W
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	-	3.5 W
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	-	3.5 W
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	-	3.5 W
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	-	4.5 W
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	-	4.5 W
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	-	4.5 W
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	-	6 W
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	-	6 W
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	-	6 W
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	-	7 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	-	7 W
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	-	7 W
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	-	6 W
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	-	6 W
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	-	6 W
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	-	10.5 W
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	-	10.5 W
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	-	10.5 W
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	-	9 W
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	-	9 W
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	-	9 W
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	-	13 W
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	-	13 W
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	-	13 W
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	-	16 W
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	-	16 W
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	-	16 W
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	-	20 W
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	-	20 W
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	-	20 W
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	50 or 60 Hz	6 W
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	50 or 60 Hz	6 W
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	50 or 60 Hz	6 W

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	50 or 60 Hz	9 W
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	50 or 60 Hz	9 W
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	50 or 60 Hz	9 W
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	50 or 60 Hz	9 W
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	50 or 60 Hz	9 W
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	50 or 60 Hz	9 W
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	50 or 60 Hz	12 W
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	50 or 60 Hz	12 W
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	50 or 60 Hz	12 W
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	50 or 60 Hz	12 W
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	50 or 60 Hz	12 W
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	50 or 60 Hz	12 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	50 or 60 Hz	15 W
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	50 or 60 Hz	15 W
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	50 or 60 Hz	15 W
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	50 or 60 Hz	19 W
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	50 or 60 Hz	19 W
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	50 or 60 Hz	9 W
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	50 or 60 Hz	9 W
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	50 or 60 Hz	9 W
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	50 or 60 Hz	12 W
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	50 or 60 Hz	12 W
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	50 or 60 Hz	12 W
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	50 or 60 Hz	15 W
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	50 or 60 Hz	15 W
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	50 or 60 Hz	15 W
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	50 or 60 Hz	19 W
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	50 or 60 Hz	19 W
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	50 or 60 Hz	19 W
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	50 or 60 Hz	6 W
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	50 or 60 Hz	6 W

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	50 or 60 Hz	6 W	
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	50 or 60 Hz	9 W	
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	50 or 60 Hz	9 W	
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	50 or 60 Hz	9 W	
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	50 or 60 Hz	12 W	
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	50 or 60 Hz	12 W	
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	50 or 60 Hz	12 W	

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	50 or 60 Hz	15 W	
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	50 or 60 Hz	15 W	
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	50 or 60 Hz	15 W	
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	50 or 60 Hz	19 W	
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	50 or 60 Hz	19 W	
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	50 or 60 Hz	19 W	

### Temperature

Order Code	Full Product Name	Ambient temperature range
911401816697	DN027C LED20/NW D225	-20 to +40 °C
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	-20 to +40 °C
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	-20 to +40 °C
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	-20 to +40 °C
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	-20 to +40 °C
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	-20 to +40 °C
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	-20 to +40 °C
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	-20 to +40 °C
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	-20 to +40 °C
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	-20 to +40 °C
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	-20 to +40 °C
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	-20 to +40 °C
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	-20 to +40 °C
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	-20 to +40 °C
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	-20 to +40 °C
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	-20 to +40 °C
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	-20 to +40 °C
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	-20 to +40 °C
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	-20 to +40 °C
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	-20 to +40 °C
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	-20 to +40 °C
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	-20 to +40 °C
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	-20 to +40 °C
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	-20 to +40 °C
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	-20 to +40 °C
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	-20 to +40 °C
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	-20 to +40 °C
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	-20 to +40 °C
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	-20 to +40 °C
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	-20 to +40 °C
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	-20 to +40 °C
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	-20 to +40 °C

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Ambient temperature range
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-20 to +40 °C
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	-20 to +40 °C
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	-20 to +40 °C
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	-20 to +40 °C
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	-20 to +40 °C
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	-20 to +40 °C
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-20 to +40 °C
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	-20 to +40 °C
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	-20 to +40 °C
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	-20 to +40 °C
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	-20 to +40 °C
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	-20 to +40 °C
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	-20 to +40 °C
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	-20 to +40 °C
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	-20 to +40 °C
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	-20 to +40 °C
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	-20 to +40 °C
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	-20 to +40 °C
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	-20 to +40 °C
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	-20 to +40 °C
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	-20 to +40 °C
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	-20 to +40 °C
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	-20 to +40 °C
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	-20 to +40 °C
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	-20 to +40 °C
929003269510	DN200 G3 LED3 830 3.5W D80 CN	-20 to +40 °C
929003269610	DN200 G3 LED3 840 3.5W D80 CN	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
929003269710	DN200 G3 LED3 865 3.5W D80 CN	-20 to +40 °C
929003269810	DN200 G3 LED4 830 4.5W D90 CN	-20 to +40 °C
929003269910	DN200 G3 LED4 840 4.5W D90 CN	-20 to +40 °C
929003270010	DN200 G3 LED4 865 4.5W D90 CN	-20 to +40 °C
929003270110	DN200 G3 LED6 830 6W D90 CN	-20 to +40 °C
929003270210	DN200 G3 LED6 840 6W D90 CN	-20 to +40 °C
929003270310	DN200 G3 LED6 865 6W D90 CN	-20 to +40 °C
929003270410	DN200 G3 LED6 830 7W D100 CN	-20 to +40 °C
929003270510	DN200 G3 LED6 840 7W D100 CN	-20 to +40 °C
929003270610	DN200 G3 LED6 865 7W D100 CN	-20 to +40 °C
929003270710	DN200 G3 LED6 830 6W D125 CN	-20 to +40 °C
929003270810	DN200 G3 LED6 840 6W D125 CN	-20 to +40 °C
929003270910	DN200 G3 LED6 865 6W D125 CN	-20 to +40 °C
929003271010	DN200 G3 LED9 830 10.5W D125 CN	-20 to +40 °C
929003271110	DN200 G3 LED9 840 10.5W D125 CN	-20 to +40 °C
929003271210	DN200 G3 LED9 865 10.5W D125 CN	-20 to +40 °C
929003271310	DN200 G3 LED9 830 9W D150 CN	-20 to +40 °C
929003271410	DN200 G3 LED9 840 9W D150 CN	-20 to +40 °C
929003271510	DN200 G3 LED9 865 9W D150 CN	-20 to +40 °C
929003271610	DN200 G3 LED12 830 13W D150 CN	-20 to +40 °C
929003271710	DN200 G3 LED12 840 13W D150 CN	-20 to +40 °C
929003271810	DN200 G3 LED12 865 13W D150 CN	-20 to +40 °C
929003271910	DN200 G3 LED15 830 16W D175 CN	-20 to +40 °C
929003272010	DN200 G3 LED15 840 16W D175 CN	-20 to +40 °C
929003272110	DN200 G3 LED15 865 16W D175 CN	-20 to +40 °C
929003272210	DN200 G3 LED20 830 20W D200 CN	-20 to +40 °C
929003272310	DN200 G3 LED20 840 20W D200 CN	-20 to +40 °C
929003272410	DN200 G3 LED20 865 20W D200 CN	-20 to +40 °C
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	-20 to +40 °C
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	-20 to +40 °C
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	-20 to +40 °C
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	-20 to +40 °C
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	-20 to +40 °C
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	-20 to +40 °C
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	-20 to +40 °C
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	-20 to +40 °C
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	-20 to +40 °C
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	-20 to +40 °C
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	-20 to +40 °C
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	-20 to +40 °C

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	-20 to +40 °C	929003280017	DN020B G4 LED12/CW 13W 220-240V D150	-20 °C to 40 °C
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	-20 to +40 °C	929003280117	DN020B G4 LED15/WW 16W 220-240V D175	-20 °C to 40 °C
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	-20 to +40 °C	929003280217	DN020B G4 LED15/NW 16W 220-240V D175	-20 °C to 40 °C
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	-20 °C to 40 °C	929003280317	DN020B G4 LED15/CW 16W 220-240V D175	-20 °C to 40 °C
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	-20 °C to 40 °C	929003280417	DN020B G4 LED20/WW 20W 220-240V D200	-20 °C to 40 °C
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	-20 °C to 40 °C	929003280517	DN020B G4 LED20/NW 20W 220-240V D200	-20 °C to 40 °C
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	-20 °C to 40 °C	929003280617	DN020B G4 LED20/CW 20W 220-240V D200	-20 °C to 40 °C
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	-20 °C to 40 °C	929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	-20 to +40 °C
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	-20 °C to 40 °C	929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	-20 to +40 °C
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	-20 °C to 40 °C	929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	-20 to +40 °C
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	-20 °C to 40 °C	929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	-20 to +40 °C
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	-20 °C to 40 °C	929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	-20 to +40 °C
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	-20 °C to 40 °C	929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	-20 to +40 °C
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	-20 °C to 40 °C	929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	-20 to +40 °C
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	-20 °C to 40 °C	929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	-20 to +40 °C
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	-20 °C to 40 °C	929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	-20 to +40 °C
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	-20 °C to 40 °C	929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	-20 to +40 °C
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	-20 °C to 40 °C	929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	-20 to +40 °C
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	-20 °C to 40 °C	929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	-20 to +40 °C
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	-20 °C to 40 °C	929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	-20 to +40 °C
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	-20 °C to 40 °C	929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	-20 to +40 °C
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	-20 °C to 40 °C	929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	-20 to +40 °C
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	-20 °C to 40 °C	929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	-20 to +40 °C
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	-20 °C to 40 °C	929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	-20 to +40 °C
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	-20 °C to 40 °C	929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	-20 to +40 °C
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	-20 °C to 40 °C	929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	-20 to +40 °C

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	-20 to +40 °C	929002675938	DN027C G3 LED9/CW 9W 220-240V D150	-20 to +40 °C
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	-20 to +40 °C	929002676038	DN027C G3 LED12/WW 12W 220-240V D175	-20 to +40 °C
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	-20 to +40 °C	929002676138	DN027C G3 LED12/NW 12W 220-240V D175	-20 to +40 °C
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	-20 to +40 °C	929002676238	DN027C G3 LED12/CW 12W 220-240V D175	-20 to +40 °C
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	-20 to +40 °C	929002676338	DN027C G3 LED15/WW 15W 220-240V D200	-20 to +40 °C
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	-20 to +40 °C	929002676438	DN027C G3 LED15/NW 15W 220-240V D200	-20 to +40 °C
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	-20 to +40 °C	929002676538	DN027C G3 LED15/CW 15W 220-240V D200	-20 to +40 °C
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	-20 to +40 °C	929002676638	DN027C G3 LED20/WW 19W 220-240V D225	-20 to +40 °C
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	-20 to +40 °C	929002676738	DN027C G3 LED20/NW 19W 220-240V D225	-20 to +40 °C
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	-20 to +40 °C	929002676838	DN027C G3 LED20/CW 19W 220-240V D225	-20 to +40 °C
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	-20 to +40 °C	929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	-20 to +40 °C
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	-20 to +40 °C	929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	-20 to +40 °C
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	-20 to +40 °C	929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	-20 to +40 °C
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	-20 to +40 °C	929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	-20 to +40 °C
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	-20 to +40 °C	929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	-20 to +40 °C
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	-20 to +40 °C	929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	-20 to +40 °C
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	-20 to +40 °C	929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	-20 to +40 °C
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	-20 to +40 °C	929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	-20 to +40 °C
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	-20 to +40 °C	929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	-20 to +40 °C
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	-20 to +40 °C	929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	-20 to +40 °C
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	-20 to +40 °C	929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	-20 to +40 °C
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	-20 to +40 °C	929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	-20 to +40 °C
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	-20 to +40 °C	929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	-20 to +40 °C
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	-20 to +40 °C	929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	-20 to +40 °C
			929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	-20 to +40 °C

### Controls and Dimming



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401816697	DN027C LED20/NW D225	-	929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	No
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	No	929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	No
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	No	929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	No
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	No	929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	No
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	No	929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	No
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	No	929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	No
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	No	929003269510	DN200 G3 LED3 830 3.5W D80 CN	No
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	No	929003269610	DN200 G3 LED3 840 3.5W D80 CN	No
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	No	929003269710	DN200 G3 LED3 865 3.5W D80 CN	No
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	No	929003269810	DN200 G3 LED4 830 4.5W D90 CN	No
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	No	929003269910	DN200 G3 LED4 840 4.5W D90 CN	No
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	No	929003270010	DN200 G3 LED4 865 4.5W D90 CN	No
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	No	929003270110	DN200 G3 LED6 830 6W D90 CN	No
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	No	929003270210	DN200 G3 LED6 840 6W D90 CN	No
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	No	929003270310	DN200 G3 LED6 865 6W D90 CN	No
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	No	929003270410	DN200 G3 LED6 830 7W D100 CN	No
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	No	929003270510	DN200 G3 LED6 840 7W D100 CN	No
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	No	929003270610	DN200 G3 LED6 865 7W D100 CN	No
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	No	929003270710	DN200 G3 LED6 830 6W D125 CN	No
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	No	929003270810	DN200 G3 LED6 840 6W D125 CN	No
929002510020	DN020B G3 LED12/NW 14W 220-240V D150 MY	No	929003270910	DN200 G3 LED6 865 6W D125 CN	No
929002510108	DN020B G3 LED12/CW 14W 220-240V D150 GM	No	929003271010	DN200 G3 LED9 830 10.5W D125 CN	No
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	No	929003271110	DN200 G3 LED9 840 10.5W D125 CN	No
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	No	929003271210	DN200 G3 LED9 865 10.5W D125 CN	No
929002510220	DN020B G3 LED12/NW 14W 220-240V D150 MY	No	929003271310	DN200 G3 LED9 830 9W D150 CN	No
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	No	929003271410	DN200 G3 LED9 840 9W D150 CN	No
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	No	929003271510	DN200 G3 LED9 865 9W D150 CN	No
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	No	929003271610	DN200 G3 LED12 830 13W D150 CN	No
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	No	929003271710	DN200 G3 LED12 840 13W D150 CN	No
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	No	929003271810	DN200 G3 LED12 865 13W D150 CN	No
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	No	929003271910	DN200 G3 LED15 830 16W D175 CN	No
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	No	929003272010	DN200 G3 LED15 840 16W D175 CN	No
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	No	929003272110	DN200 G3 LED15 865 16W D175 CN	No
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	No	929003272210	DN200 G3 LED20 830 20W D200 CN	No
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	No	929003272310	DN200 G3 LED20 840 20W D200 CN	No
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	No	929003272410	DN200 G3 LED20 865 20W D200 CN	No
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	No	929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	No
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	No	929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	No
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	No	929002674938	DN027B G3 LED6/CW 6W 220-240V L100 SQ	No
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	No	929002675002	DN027B G3 LED6/WW 6W 220-240V L100 RU	No
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	No	929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	No
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	No	929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	No
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	No	929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	No
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	No	929002675238	DN027B G3 LED9/CW 9W 220-240V L125 SQ	No
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	No	929002675302	DN027B G3 LED9/WW 9W 220-240V L125 RU	No
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	No	929002675338	DN027B G3 LED9/NW 9W 220-240V L125 SQ	No
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	No	929002675388	DN027B G3 LED9/CW 9W 220-240V L125 SQ	No
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	No	929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	No
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	No	929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	No
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	No	929002675538	DN027B G3 LED12/CW 12W 220-240V L150 SQ	No
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	No	929002675602	DN027B G3 LED12/WW 12W 220-240V L150 RU	No
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	No	929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	No
			929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	No

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	No	929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	No
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	No	929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	No
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	No	929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	No
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	No	929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	No
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	No	929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	No
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	No	929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	No
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	No	929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	No
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	No	929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	No
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	No	929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	No
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	No	929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	No
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	No	929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	No
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	No	929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	No
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	No	929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	No
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	No	929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	No
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	No	929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	No
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	No	929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	No
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	No	929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	No
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	No	929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	No
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	No	929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	No
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	No	929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	No
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	No	929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	No
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	No	929002675738	DN027C G3 LED9/WW 9W 220-240V D150	No
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	No	929002675838	DN027C G3 LED9/NW 9W 220-240V D150	No
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	No	929002675938	DN027C G3 LED9/CW 9W 220-240V D150	No
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	No	929002676038	DN027C G3 LED12/WW 12W 220-240V D175	No
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	No	929002676138	DN027C G3 LED12/NW 12W 220-240V D175	No
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	No	929002676238	DN027C G3 LED12/CW 12W 220-240V D175	No
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	No	929002676338	DN027C G3 LED15/WW 15W 220-240V D200	No
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	No	929002676438	DN027C G3 LED15/NW 15W 220-240V D200	No
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	No	929002676538	DN027C G3 LED15/CW 15W 220-240V D200	No
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	No	929002676638	DN027C G3 LED20/WW 19W 220-240V D225	No
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	No	929002676738	DN027C G3 LED20/NW 19W 220-240V D225	No
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	No	929002676838	DN027C G3 LED20/CW 19W 220-240V D225	No
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	No	929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	No
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	No	929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	No
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	No	929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	No
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	No	929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	No
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	No	929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	No
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	No	929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	No
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	No	929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	No
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	No	929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	No
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	No	929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	No
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	No	929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	No
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	No	929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	No
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	No	929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	No
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	No	929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	No
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	No	929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	No
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	No	929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	No
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	No			

### Approval and Application

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
911401816697	DN027C LED20/NW D225	IK02	IP20
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	IK03	IP20
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	IK03	IP20
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	IK03	IP20
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	IK03	IP20
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	IK03	IP20
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	IK03	IP20
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	IK03	IP20
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	IK03	IP20
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	IK03	IP20
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	IK03	IP20
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	IK03	IP20
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	IK03	IP20
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	IK03	IP20
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	IK03	IP20
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	IK03	IP20
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	IK03	IP20
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	IK03	IP20
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	IK03	IP20
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	IK03	IP20
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	IK03	IP20
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	IK03	IP20
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	IK03	IP20
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	IK03	IP20
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	IK03	IP20

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	IK03	IP20
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	IK03	IP20
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	IK03	IP20
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	IK03	IP20
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	IK03	IP20
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	IK03	IP20
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	IK03	IP20
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	IK03	IP20
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	IK03	IP20
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	IK03	IP20
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	IK03	IP20
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	IK03	IP20
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	IK03	IP20
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	IK03	IP20
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	IK03	IP20
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	IK03	IP20
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	IK03	IP20
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	IK03	IP20
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	IK03	IP20
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	IK03	IP20
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	IK03	IP20
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	IK03	IP20/40
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	IK03	IP20/40
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	IK03	IP20/40
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	IK03	IP20/40

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	IK03	IP20/40
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	IK03	IP20/40
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	IK03	IP20/40
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	IK03	IP20/40
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	IK03	IP20/40
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	IK03	IP20/40
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	IK03	IP20/40
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	IK03	IP20/40
929003269510	DN200 G3 LED3 830 3.5W D80 CN	IK03	IP20
929003269610	DN200 G3 LED3 840 3.5W D80 CN	IK03	IP20
929003269710	DN200 G3 LED3 865 3.5W D80 CN	IK03	IP20
929003269810	DN200 G3 LED4 830 4.5W D90 CN	IK03	IP20
929003269910	DN200 G3 LED4 840 4.5W D90 CN	IK03	IP20
929003270010	DN200 G3 LED4 865 4.5W D90 CN	IK03	IP20
929003270110	DN200 G3 LED6 830 6W D90 CN	IK03	IP20
929003270210	DN200 G3 LED6 840 6W D90 CN	IK03	IP20
929003270310	DN200 G3 LED6 865 6W D90 CN	IK03	IP20
929003270410	DN200 G3 LED6 830 7W D100 CN	IK03	IP20
929003270510	DN200 G3 LED6 840 7W D100 CN	IK03	IP20
929003270610	DN200 G3 LED6 865 7W D100 CN	IK03	IP20
929003270710	DN200 G3 LED6 830 6W D125 CN	IK03	IP20
929003270810	DN200 G3 LED6 840 6W D125 CN	IK03	IP20
929003270910	DN200 G3 LED6 865 6W D125 CN	IK03	IP20
929003271010	DN200 G3 LED9 830 10.5W D125 CN	IK03	IP20
929003271110	DN200 G3 LED9 840 10.5W D125 CN	IK03	IP20
929003271210	DN200 G3 LED9 865 10.5W D125 CN	IK03	IP20
929003271310	DN200 G3 LED9 830 9W D150 CN	IK03	IP20
929003271410	DN200 G3 LED9 840 9W D150 CN	IK03	IP20
929003271510	DN200 G3 LED9 865 9W D150 CN	IK03	IP20
929003271610	DN200 G3 LED12 830 13W D150 CN	IK03	IP20
929003271710	DN200 G3 LED12 840 13W D150 CN	IK03	IP20
929003271810	DN200 G3 LED12 865 13W D150 CN	IK03	IP20
929003271910	DN200 G3 LED15 830 16W D175 CN	IK03	IP20
929003272010	DN200 G3 LED15 840 16W D175 CN	IK03	IP20
929003272110	DN200 G3 LED15 865 16W D175 CN	IK03	IP20
929003272210	DN200 G3 LED20 830 20W D200 CN	IK03	IP20
929003272310	DN200 G3 LED20 840 20W D200 CN	IK03	IP20
929003272410	DN200 G3 LED20 865 20W D200 CN	IK03	IP20
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	IK03	IP20/40
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	IK03	IP20/40

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	IK03	IP20/40
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	IK03	IP20/40
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	IK03	IP20/40
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	IK03	IP20/40
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	IK03	IP20/40
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	IK03	IP20/40
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	IK03	IP20/40
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	IK03	IP20/40
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	IK03	IP20/40
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	IK03	IP20/40
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	IK03	IP20/40
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	IK03	IP20/40
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	IK03	IP20/40
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	IK03	IP20
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	IK03	IP20
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	IK03	IP20
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	IK03	IP20
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	IK03	IP20
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	IK03	IP20
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	IK03	IP20
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	IK03	IP20
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	IK03	IP20
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	IK03	IP20
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	IK03	IP20
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	IK03	IP20

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	IK03	IP20
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	IK03	IP20
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	IK03	IP20
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	IK03	IP20
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	IK03	IP20
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	IK03	IP20
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	IK03	IP20
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	IK03	IP20
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	IK03	IP20
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	IK03	IP20
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	IK03	IP20
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	IK03	IP20
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	IK03	IP20
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	IK03	IP20
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	IK03	IP20
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	IK03	IP20
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	IK03	IP20
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	IK03	IP20
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	IK03	IP20/40
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	IK03	IP20/40
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	IK03	IP20/40
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	IK03	IP20/40
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	IK03	IP20/40
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	IK03	IP20/40
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	IK03	IP20/40

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	IK03	IP20/40
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	IK03	IP20/40
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	IK03	IP20/40
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	IK03	IP20/40
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	IK03	IP20/40
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	IK03	IP20/40
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	IK03	IP20/40
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	IK03	IP20/40
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	IK03	IP20/40
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	IK03	IP20/40
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	IK03	IP20/40
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	IK03	IP20/40
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	IK03	IP20/40
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	IK03	IP20/40
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	IK03	IP20/40
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	IK03	IP20/40
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	IK03	IP20/40
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	IK03	IP20/40
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	IK03	IP20/40
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	IK03	IP20/40
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	IK03	IP20/40
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	IK03	IP20/40
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	IK03	IP20/40
929002673938	DN027B G3 LED15/WW 15W 220-240V D175 RD	IK03	IP20/40
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	IK03	IP20/40

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	IK03	IP20/40
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	IK03	IP20/40
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	IK03	IP20/40
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	IK03	IP20/40
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	IK03	IP20/40
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	IK03	IP20/40
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	IK03	IP20/40
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	IK03	IP20/40
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	IK03	IP20/40
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	IK03	IP20/40
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	IK03	IP20/40
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	IK03	IP20/40
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	IK03	IP20/40
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	IK03	IP20/40
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	IK03	IP20/40
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	IK03	IP20/40
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	IK03	IP20/40
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	IK03	IP20/40

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	IK03	IP20/40
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	IK03	IP20/40
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	IK03	IP20/40
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	IK03	IP20/40
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	IK03	IP20/40
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	IK03	IP20/40
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	IK03	IP20/40
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	IK03	IP20/40
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	IK03	IP20/40
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	IK03	IP20/40
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	IK03	IP20/40
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	IK03	IP20/40
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	IK03	IP20/40
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	IK03	IP20/40
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	IK03	IP20/40
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	IK03	IP20/40
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	IK03	IP20/40
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	IK03	IP20/40

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401816697	DN027C LED20/NW D225	-	-
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	(0.4339, 0.4033) 6	-
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	(0.3818, 0.3797) 6	-
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	(0.3123, 0.3283) 6	-

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	(0.4339, 0.4033) 6	-
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	(0.3818, 0.3797) 6	-
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	(0.3123, 0.3283) 6	-
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	(0.4339, 0.4033) 6	-

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	(0.3818, 0.3797) 6	-
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	(0.3123, 0.3283) 6	-
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	(0.4339, 0.4033) 6	-
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	(0.3818, 0.3797) 6	-
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	(0.3123, 0.3283) 6	-
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	(0.4339, 0.4033) 6	-
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	(0.3818, 0.3797) 6	-
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	(0.3123, 0.3283) 6	-
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	(0.4339, 0.4033) 6	-
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	(0.3818, 0.3797) 6	-
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	(0.3123, 0.3283) 6	-
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	(0.4339, 0.4033) 6	-
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	(0.4339, 0.4033) 6	-
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	(0.3818, 0.3797) 6	-
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	(0.3818, 0.3797) 6	-
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	(0.3123, 0.3283) 6	-
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	(0.3123, 0.3283) 6	-
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	(0.4339, 0.4033) 6	-
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	(0.3818, 0.3797) 6	-
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	(0.3123, 0.3283) 6	-
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	(0.4339, 0.4033) 6	-
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	(0.3818, 0.3797) 6	-
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	(0.3123, 0.3283) 6	-
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	(0.4339, 0.4033) 6	-
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	(0.3818, 0.3797) 6	-

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	(0.3123, 0.3283) 6	-
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	(0.4339, 0.4033) 6	-
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	(0.3818, 0.3797) 6	-
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	(0.3123, 0.3283) 6	-
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	(0.4339, 0.4033) 6	-
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	(0.3818, 0.3797) 6	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	(0.3123, 0.3283) 6	-
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	(0.4339, 0.4033) 6	-
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	(0.3818, 0.3797) 6	-
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	(0.3123, 0.3283) 6	-
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	(0.4339, 0.4033) 6	-
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	(0.3818, 0.3797) 6	-
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	(0.3123, 0.3283) 6	-
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003269510	DN200 G3 LED3 830 3.5W D80 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003269610	DN200 G3 LED3 840 3.5W D80 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003269710	DN200 G3 LED3 865 3.5W D80 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003269810	DN200 G3 LED4 830 4.5W D90 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003269910	DN200 G3 LED4 840 4.5W D90 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003270010	DN200 G3 LED4 865 4.5W D90 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003270110	DN200 G3 LED6 830 6W D90 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003270210	DN200 G3 LED6 840 6W D90 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003270310	DN200 G3 LED6 865 6W D90 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003270410	DN200 G3 LED6 830 7W D100 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003270510	DN200 G3 LED6 840 7W D100 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003270610	DN200 G3 LED6 865 7W D100 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003270710	DN200 G3 LED6 830 6W D125 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003270810	DN200 G3 LED6 840 6W D125 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003270910	DN200 G3 LED6 865 6W D125 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003271010	DN200 G3 LED9 830 10.5W D125 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003271110	DN200 G3 LED9 840 10.5W D125 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003271210	DN200 G3 LED9 865 10.5W D125 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003271310	DN200 G3 LED9 830 9W D150 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003271410	DN200 G3 LED9 840 9W D150 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003271510	DN200 G3 LED9 865 9W D150 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003271610	DN200 G3 LED12 830 13W D150 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003271710	DN200 G3 LED12 840 13W D150 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003271810	DN200 G3 LED12 865 13W D150 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003271910	DN200 G3 LED15 830 16W D175 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003272010	DN200 G3 LED15 840 16W D175 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003272110	DN200 G3 LED15 865 16W D175 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929003272210	DN200 G3 LED20 830 20W D200 CN	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003272310	DN200 G3 LED20 840 20W D200 CN	(X=, 0.3863 ; Y=, 0.3863) 5SDCM	+/-10%
929003272410	DN200 G3 LED20 865 20W D200 CN	(X=, 0.3115 ; Y=, 0.3258) 5SDCM	+/-10%
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	(X=, 0.3874 ; Y=, 0.388) 5SDCM	+/-10%
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	(X=, 0.3139 ; Y=, 0.3326) 5SDCM	+/-10%
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	(X=, 0.3874 ; Y=, 0.388) 5SDCM	+/-10%



## Essential SmartBright LED Downlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	(X=, 0.3139 ; Y=, 0.3326) 5SDCM	+/-10%
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	(X=, 0.3874 ; Y=, 0.388) 5SDCM	+/-10%
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	(X=, 0.3139 ; Y=, 0.3326) 5SDCM	+/-10%
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	(X=, 0.3874 ; Y=, 0.388) 5SDCM	+/-10%
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	(X=, 0.3139 ; Y=, 0.3326) 5SDCM	+/-10%
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	(X=, 0.4377 ; Y=, 0.4055) 5SDCM	+/-10%
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	(X=, 0.3117 ; Y=, 0.3273) 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%

### Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
911401816697	DN027C LED20/NW D225	-

Order Code	Full Product Name	Driver failure rate at 5000 h
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	1.6 %

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver failure rate at 5000 h
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	1.6 %
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	1.6 %
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	1.6 %
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	1.6 %
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	1.6 %
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	1.6 %
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	1.6 %
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	1.6 %
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	1.6 %
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	1.6 %
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	1.6 %
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	1.6 %
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	1.6 %
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	1.6 %
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	1.6 %
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	1.6 %
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	1.6 %
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	1.6 %
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	1.6 %
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	1.6 %
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	1.6 %
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	1.6 %
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	1.6 %
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	1.6 %
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	1.6 %
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	1.6 %
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	1.6 %
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	1.6 %
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	1.6 %
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	1.6 %
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	1.6 %
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	1.6 %
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	1.6 %
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	1.6 %
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	1.6 %
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	1.6 %
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	1.6 %
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	1.6 %
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	1.6 %
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	1.6 %
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	1.6 %
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	1.6 %
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	1.6 %
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	1.6 %
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	0.012 %
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	0.012 %
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	0.012 %
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	0.012 %
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	0.012 %
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	0.012 %
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	0.012 %

Order Code	Full Product Name	Driver failure rate at 5000 h
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	0.012 %
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	0.012 %
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	0.012 %
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	0.012 %
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	0.012 %
929003269510	DN200 G3 LED3 830 3.5W D80 CN	1.2 %
929003269610	DN200 G3 LED3 840 3.5W D80 CN	1.2 %
929003269710	DN200 G3 LED3 865 3.5W D80 CN	1.2 %
929003269810	DN200 G3 LED4 830 4.5W D90 CN	1.2 %
929003269910	DN200 G3 LED4 840 4.5W D90 CN	1.2 %
929003270010	DN200 G3 LED4 865 4.5W D90 CN	1.2 %
929003270110	DN200 G3 LED6 830 6W D90 CN	1.2 %
929003270210	DN200 G3 LED6 840 6W D90 CN	1.2 %
929003270310	DN200 G3 LED6 865 6W D90 CN	1.2 %
929003270410	DN200 G3 LED6 830 7W D100 CN	1.2 %
929003270510	DN200 G3 LED6 840 7W D100 CN	1.2 %
929003270610	DN200 G3 LED6 865 7W D100 CN	1.2 %
929003270710	DN200 G3 LED6 830 6W D125 CN	1.2 %
929003270810	DN200 G3 LED6 840 6W D125 CN	1.2 %
929003270910	DN200 G3 LED6 865 6W D125 CN	1.2 %
929003271010	DN200 G3 LED9 830 10.5W D125 CN	1.2 %
929003271110	DN200 G3 LED9 840 10.5W D125 CN	1.2 %
929003271210	DN200 G3 LED9 865 10.5W D125 CN	1.2 %
929003271310	DN200 G3 LED9 830 9W D150 CN	1.2 %
929003271410	DN200 G3 LED9 840 9W D150 CN	1.2 %
929003271510	DN200 G3 LED9 865 9W D150 CN	1.2 %
929003271610	DN200 G3 LED12 830 13W D150 CN	1.2 %
929003271710	DN200 G3 LED12 840 13W D150 CN	1.2 %
929003271810	DN200 G3 LED12 865 13W D150 CN	1.2 %
929003271910	DN200 G3 LED15 830 16W D175 CN	1.2 %
929003272010	DN200 G3 LED15 840 16W D175 CN	1.2 %
929003272110	DN200 G3 LED15 865 16W D175 CN	1.2 %
929003272210	DN200 G3 LED20 830 20W D200 CN	1.2 %
929003272310	DN200 G3 LED20 840 20W D200 CN	1.2 %
929003272410	DN200 G3 LED20 865 20W D200 CN	1.2 %
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	0.012 %
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	0.012 %
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	0.012 %
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	0.012 %
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	0.012 %
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	0.012 %
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	0.012 %
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	0.012 %
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	0.012 %
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	0.012 %
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	0.012 %
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	0.012 %
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	0.012 %
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	0.012 %
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	0.012 %
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	1.2

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver failure rate at 5000 h
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	1.2
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	1.2
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	1.2
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	1.2
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	1.2
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	1.2
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	1.2
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	1.2
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	1.2
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	1.2
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	1.2
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	1.2
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	1.2
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	1.2
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	1.2
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	1.2
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	1.2
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	1.2
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	1.2
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	1.2
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	1.2
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	1.2
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	1.2
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	1.2
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	1.2
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	1.2
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	1.2
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	1.2
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	1.2
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	0.012 %
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	0.012 %
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	0.012 %
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	0.012 %
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	0.012 %
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	0.012 %
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	0.012 %
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	0.012 %
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	0.012 %
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	0.012 %
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	0.012 %
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	0.012 %
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	0.012 %
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	0.012 %
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	0.012 %
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	0.012 %
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	0.012 %
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	0.012 %
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	0.012 %
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	0.012 %

Order Code	Full Product Name	Driver failure rate at 5000 h
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	0.012 %
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	0.012 %
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	0.012 %
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	0.012 %
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	0.012 %
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	0.012 %
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	0.012 %
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	0.012 %
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	0.012 %
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	0.012 %
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	0.012 %
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	0.012 %
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	0.012 %
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	0.012 %
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	0.012 %
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	0.012 %
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	0.012 %
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	0.012 %
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	0.012 %
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	0.012 %
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	0.012 %
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	0.012 %
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	0.012 %
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	0.012 %
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	0.012 %
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	0.012 %
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	0.012 %
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	0.012 %
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	0.012 %
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	0.012 %
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	0.012 %
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	0.012 %
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	0.012 %
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	0.012 %
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	0.012 %
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	0.012 %
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	0.012 %
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	0.012 %
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	0.012 %
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	0.012 %
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	0.012 %
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	0.012 %
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	0.012 %
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	0.012 %
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	0.012 %
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	0.012 %
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	0.012 %
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	0.012 %

### Application Conditions

## Essential SmartBright LED Downlight

Order Code	Full Product Name	Suitable for random switching
911401816697	DN027C LED20/NW D225	-
929002508208	DN020B G3 LED3/WW 3.5W 220-240V D80 GM	-
929002508308	DN020B G3 LED3/NW 3.5W 220-240V D80 GM	-
929002508408	DN020B G3 LED3/CW 3.5W 220-240V D80 GM	-
929002508508	DN020B G3 LED4/WW 4.5W 220-240V D90 GM	-
929002508608	DN020B G3 LED4/NW 4.5W 220-240V D90 GM	-
929002508708	DN020B G3 LED4/CW 4.5W 220-240V D90 GM	-
929002508808	DN020B G3 LED6/WW 7W 220-240V D100 GM	-
929002508908	DN020B G3 LED6/NW 7W 220-240V D100 GM	-
929002509008	DN020B G3 LED6/CW 7W 220-240V D100 GM	-
929002509108	DN020B G3 LED6/WW 7W 220-240V D125 GM	-
929002509208	DN020B G3 LED6/NW 7W 220-240V D125 GM	-
929002509308	DN020B G3 LED6/CW 7W 220-240V D125 GM	-
929002509408	DN020B G3 LED9/WW 10.5W 220-240V D125 GM	-
929002509508	DN020B G3 LED9/NW 10.5W 220-240V D125 GM	-
929002509608	DN020B G3 LED9/CW 10.5W 220-240V D125 GM	-
929002509708	DN020B G3 LED9/WW 10.5W 220-240V D150 GM	-
929002509808	DN020B G3 LED9/NW 10.5W 220-240V D150 GM	-
929002509908	DN020B G3 LED9/CW 10.5W 220-240V D150 GM	-
929002510008	DN020B G3 LED12/WW 14W 220-240V D150 GM	-
929002510020	DN020B G3 LED12/WW 14W 220-240V D150 MY	-
929002510108	DN020B G3 LED12/NW 14W 220-240V D150 GM	-
929002510120	DN020B G3 LED12/NW 14W 220-240V D150 MY	-
929002510208	DN020B G3 LED12/CW 14W 220-240V D150 GM	-
929002510220	DN020B G3 LED12/CW 14W 220-240V D150 MY	-
929002510308	DN020B G3 LED15/WW 18W 220-240V D175 GM	-
929002510408	DN020B G3 LED15/NW 18W 220-240V D175 GM	-
929002510508	DN020B G3 LED15/CW 18W 220-240V D175 GM	-
929002510608	DN020B G3 LED20/WW 23W 220-240V D200 GM	-
929002510708	DN020B G3 LED20/NW 23W 220-240V D200 GM	-
929002510808	DN020B G3 LED20/CW 23W 220-240V D200 GM	-
929002511217	DN020B G3 LED4/WW 4.5W 220-240V D90 SNI	-
929002511317	DN020B G3 LED4/NW 4.5W 220-240V D90 SNI	-
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-
929002512117	DN020B G3 LED9/WW 10.5W 220-240V D125SNI	-
929002512217	DN020B G3 LED9/NW 10.5W 220-240V D125SNI	-
929002512317	DN020B G3 LED9/CW 10.5W 220-240V D125SNI	-
929002512717	DN020B G3 LED12/WW 14W 220-240V D150 SNI	-
929002512817	DN020B G3 LED12/NW 14W 220-240V D150 SNI	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-
929002513017	DN020B G3 LED15/WW 18W 220-240V D175 SNI	-
929002513117	DN020B G3 LED15/NW 18W 220-240V D175 SNI	-
929002513217	DN020B G3 LED15/CW 18W 220-240V D175 SNI	-
929002513317	DN020B G3 LED20/WW 23W 220-240V D200 SNI	-
929002513417	DN020B G3 LED20/NW 23W 220-240V D200 SNI	-
929002513517	DN020B G3 LED20/CW 23W 220-240V D200 SNI	-
929002672122	DN027B G3 LED6/WW 6W 220-240V D100 KSA	No
929002672222	DN027B G3 LED6/NW 6W 220-240V D100 KSA	No
929002672322	DN027B G3 LED6/CW 6W 220-240V D100 KSA	No
929002673322	DN027B G3 LED12/WW 12W 220-240V D150 KSA	No
929002673422	DN027B G3 LED12/NW 12W 220-240V D150 KSA	No

Order Code	Full Product Name	Suitable for random switching
929002673522	DN027B G3 LED12/CW 12W 220-240V D150 KSA	No
929002674522	DN027B G3 LED20/WW 19W 220-240V D200 KSA	No
929002674622	DN027B G3 LED20/NW 19W 220-240V D200 KSA	No
929002674722	DN027B G3 LED20/CW 19W 220-240V D200 KSA	No
929003250238	DN027B G3 LED3/WW 3W 220-240V D70 KSA	No
929003250338	DN027B G3 LED3/NW 3W 220-240V D70 KSA	No
929003250438	DN027B G3 LED3/CW 3W 220-240V D70 KSA	No
929003269510	DN200 G3 LED3 830 3.5W D80 CN	Not applicable
929003269610	DN200 G3 LED3 840 3.5W D80 CN	Not applicable
929003269710	DN200 G3 LED3 865 3.5W D80 CN	Not applicable
929003269810	DN200 G3 LED4 830 4.5W D90 CN	Not applicable
929003269910	DN200 G3 LED4 840 4.5W D90 CN	Not applicable
929003270010	DN200 G3 LED4 865 4.5W D90 CN	Not applicable
929003270110	DN200 G3 LED6 830 6W D90 CN	Not applicable
929003270210	DN200 G3 LED6 840 6W D90 CN	Not applicable
929003270310	DN200 G3 LED6 865 6W D90 CN	Not applicable
929003270410	DN200 G3 LED6 830 7W D100 CN	Not applicable
929003270510	DN200 G3 LED6 840 7W D100 CN	Not applicable
929003270610	DN200 G3 LED6 865 7W D100 CN	Not applicable
929003270710	DN200 G3 LED6 830 6W D125 CN	Not applicable
929003270810	DN200 G3 LED6 840 6W D125 CN	Not applicable
929003270910	DN200 G3 LED6 865 6W D125 CN	Not applicable
929003271010	DN200 G3 LED9 830 10.5W D125 CN	Not applicable
929003271110	DN200 G3 LED9 840 10.5W D125 CN	Not applicable
929003271210	DN200 G3 LED9 865 10.5W D125 CN	Not applicable
929003271310	DN200 G3 LED9 830 9W D150 CN	Not applicable
929003271410	DN200 G3 LED9 840 9W D150 CN	Not applicable
929003271510	DN200 G3 LED9 865 9W D150 CN	Not applicable
929003271610	DN200 G3 LED12 830 13W D150 CN	Not applicable
929003271710	DN200 G3 LED12 840 13W D150 CN	Not applicable
929003271810	DN200 G3 LED12 865 13W D150 CN	Not applicable
929003271910	DN200 G3 LED15 830 16W D175 CN	Not applicable
929003272010	DN200 G3 LED15 840 16W D175 CN	Not applicable
929003272110	DN200 G3 LED15 865 16W D175 CN	Not applicable
929003272210	DN200 G3 LED20 830 20W D200 CN	Not applicable
929003272310	DN200 G3 LED20 840 20W D200 CN	Not applicable
929003272410	DN200 G3 LED20 865 20W D200 CN	Not applicable
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	No
929002674902	DN027B G3 LED6/NW 6W 220-240V L100 RU	No
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	No
929002675002	DN027B G3 LED6/CW 6W 220-240V L100 RU	No
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	No
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	No
929002675202	DN027B G3 LED9/NW 9W 220-240V L125 RU	No
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	No
929002675302	DN027B G3 LED9/CW 9W 220-240V L125 RU	No
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	No
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	No
929002675502	DN027B G3 LED12/NW 12W 220-240V L150 RU	No
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	No
929002675602	DN027B G3 LED12/CW 12W 220-240V L150 RU	No











## Essential SmartBright LED Downlight

Order Code	Full Product Name	Suitable for random switching
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	No
929003277708	DN020B G4 LED3/WW 3.5W 220-240V D80	Not applicable
929003277808	DN020B G4 LED3/NW 3.5W 220-240V D80	Not applicable
929003277908	DN020B G4 LED3/CW 3.5W 220-240V D80	Not applicable
929003278017	DN020B G4 LED4/WW 4.5W 220-240V D90	Not applicable
929003278117	DN020B G4 LED4/NW 4.5W 220-240V D90	Not applicable
929003278217	DN020B G4 LED4/CW 4.5W 220-240V D90	Not applicable
929003278317	DN020B G4 LED6/WW 6W 220-240V D90	Not applicable
929003278417	DN020B G4 LED6/NW 6W 220-240V D90	Not applicable
929003278517	DN020B G4 LED6/CW 6W 220-240V D90	Not applicable
929003278608	DN020B G4 LED6/WW 7W 220-240V D100	Not applicable
929003278708	DN020B G4 LED6/NW 7W 220-240V D100	Not applicable
929003278808	DN020B G4 LED6/CW 7W 220-240V D100	Not applicable
929003278908	DN020B G4 LED6/WW 6W 220-240V D125	Not applicable
929003279008	DN020B G4 LED6/NW 6W 220-240V D125	Not applicable
929003279108	DN020B G4 LED6/CW 6W 220-240V D125	Not applicable
929003279217	DN020B G4 LED9/WW 10.5W 220-240V D125	Not applicable
929003279317	DN020B G4 LED9/NW 10.5W 220-240V D125	Not applicable
929003279417	DN020B G4 LED9/CW 10.5W 220-240V D125	Not applicable
929003279508	DN020B G4 LED9/WW 9W 220-240V D150	Not applicable
929003279608	DN020B G4 LED9/NW 9W 220-240V D150	Not applicable
929003279708	DN020B G4 LED9/CW 9W 220-240V D150	Not applicable
929003279817	DN020B G4 LED12/WW 13W 220-240V D150	Not applicable
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	Not applicable
929003280017	DN020B G4 LED12/CW 13W 220-240V D150	Not applicable
929003280117	DN020B G4 LED15/WW 16W 220-240V D175	Not applicable
929003280217	DN020B G4 LED15/NW 16W 220-240V D175	Not applicable
929003280317	DN020B G4 LED15/CW 16W 220-240V D175	Not applicable
929003280417	DN020B G4 LED20/WW 20W 220-240V D200	Not applicable
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	Not applicable
929003280617	DN020B G4 LED20/CW 20W 220-240V D200	Not applicable
929002671502	DN027B G3 LED6/WW 6W 220-240V D90 RU	No
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	No
929002671602	DN027B G3 LED6/NW 6W 220-240V D90 RU	No
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	No
929002671702	DN027B G3 LED6/CW 6W 220-240V D90 RU	No
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	No
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	No
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	No
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	No
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	No
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	No
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	No
929002672702	DN027B G3 LED9/WW 9W 220-240V D125 RU	No
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	No
929002672802	DN027B G3 LED9/NW 9W 220-240V D125 RU	No
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	No
929002672902	DN027B G3 LED9/CW 9W 220-240V D125 RU	No
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	No
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	No
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	No






Order Code	Full Product Name	Suitable for random switching
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	No
929002673302	DN027B G3 LED12/WW 12W 220-240V D150 RU	No
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	No
929002673402	DN027B G3 LED12/NW 12W 220-240V D150 RU	No
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	No
929002673502	DN027B G3 LED12/CW 12W 220-240V D150 RU	No
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	No
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	No
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	No
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	No
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	No
929002674002	DN027B G3 LED15/NW 15W 220V D175 RU	No
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	No
929002674102	DN027B G3 LED15/CW 15W 220V D175 RU	No
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	No
929002674338	DN027B G3 LED15/NW 15W 220-240 D200 RD	No
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	No
929002674602	DN027B G3 LED20/NW 19W 220-240V D200 RU	No
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	No
929002674702	DN027B G3 LED20/CW 19W 220-240V D200 RU	No
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	No
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	No
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	No
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	No
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	No
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	No
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	No
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	No
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	No
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	No
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	No
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	No
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	No
929002676940	DN500B G3 LED6/WW 6W 220V D90 RD	No
929002677040	DN500B G3 LED6/NW 6W 220V D90 RD	No
929002677140	DN500B G3 LED6/CW 6W 220V D90 RD	No
929002677240	DN500B G3 LED9/WW 9W 220V D125 RD	No
929002677340	DN500B G3 LED9/NW 9W 220V D125 RD	No
929002677440	DN500B G3 LED9/CW 9W 220V D125 RD	No
929002677540	DN500B G3 LED12/WW 12W 220V D150 RD	No
929002677640	DN500B G3 LED12/NW 12W 220V D150 RD	No
929002677740	DN500B G3 LED12/CW 12W 220V D150 RD	No
929002677840	DN500B G3 LED15/WW 15W 220V D175 RD	No
929002677940	DN500B G3 LED15/NW 15W 220V D175 RD	No
929002678040	DN500B G3 LED15/CW 15W 220V D175 RD	No
929002678140	DN500B G3 LED20/WW 19W 220V D200 RD	No
929002678240	DN500B G3 LED20/NW 19W 220V D200 RD	No
929002678340	DN500B G3 LED20/CW 19W 220V D200 RD	No








# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight













(cd/1000lm) 0°













(cd/1000lm) 0°








# Essential SmartBright LED Downlight








# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight





(cd/1000lm) 0°













(cd/1000lm) 0°

# Essential SmartBright LED Downlight













# Essential SmartBright LED Downlight















# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight








(cd/1000lm) 0°








(cd/1000lm) 0°



# Essential SmartBright LED Downlight















(cd/1000lm)













(cd/1000lm)











# Essential SmartBright LED Downlight













# Essential SmartBright LED Downlight















# Essential SmartBright LED Downlight













# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight



# Essential SmartBright LED Downlight

