



# The most competitive specification downlight for TCO attractiveness with diversity and system compatibility

## GreenSpace G5

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

### Benefits

- Energy efficient
- Design compactness
- Smart lighting

### Features

- High optical efficiency
- Compact form factor
- DALI/DALI-VLC/POE compatible

### Application

- Office
- shopping mall
- hotel
- retail etc.













# GreenSpace G5

## Versions




GreenSpace Gen5 DN39XB D200 WH

## Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Optical cover type	Transparent bowl with white cover
Color rendering index (CRI)	>80
Optic type	High-gloss high reflectance
Mechanical and Housing	
Housing Color	Black and white
Approval and Application	
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

## General Information

Order Code	Full Product Name	CE mark
911401571941	DN390B LED6/840 PSU D100 ALU GC	-
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-
911401576541	DN391B LED11/830 PSU D100 ALU GC	-
911401576641	DN391B LED11/840 PSU D100 ALU GC	-
911401576841	DN391B LED11/840 PSD D100 ALU GC	-
911401578141	DN390B LED6/840 PSU D100 ALU GM	CE mark
911401578241	DN390B LED6/865 PSU D100 ALU GM	CE mark
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	CE mark
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	CE mark
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	CE mark
911401571641	DN390B LED6/830 PSU D100 WH GC	-
911401571741	DN390B LED6/840 PSU D100 WH GC	-
911401577741	DN390B LED6/830 PSU D100 WH GM	CE mark
911401577841	DN390B LED6/840 PSU D100 WH GM	CE mark
911401577941	DN390B LED6/865 PSU D100 WH GM	CE mark
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	CE mark
911401572341	DN391B LED11/830 PSU D150 ALU GC	-
911401572441	DN391B LED11/840 PSU D150 ALU GC	-
911401572541	DN391B LED11/865 PSU D150 ALU GC	-
911401572841	DN391B LED11/830 PSD D150 ALU GC	-
911401572941	DN391B LED11/840 PSD D150 ALU GC	-
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-
911401577141	DN392B LED16/830 PSU D150 ALU GC	-
911401577241	DN392B LED16/840 PSU D150 ALU GC	-
911401577641	DN392B LED16/840 PSD D150 ALU GC	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	CE mark
911401578741	DN391B LED11/840 PSU D150 ALU GM	CE mark
911401578841	DN391B LED11/865 PSU D150 ALU GM	CE mark
911401579241	DN392B LED16/830 PSU D150 ALU GM	CE mark
911401579341	DN392B LED16/840 PSU D150 ALU GM	CE mark
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	CE mark
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	CE mark
911401581841	DN391B LED11/830 PSD D150 ALU GM	CE mark
911401581941	DN391B LED11/840 PSD D150 ALU GM	CE mark
911401584441	DN391B LED11/830 PSD D150 ALU CAU	CE mark
911401585741	DN392B LED16/840 PSD D150 ALU GM	CE mark
911401572041	DN391B LED11/830 PSU D150 WH GC	-
911401572141	DN391B LED11/840 PSU D150 WH GC	-
911401572241	DN391B LED11/865 PSU D150 WH GC	-
911401572741	DN391B LED11/840 PSD D150 WH GC	-
911401575741	DN392B LED16/830 POE D150 WH GC	-
911401576941	DN392B LED16/830 PSU D150 WH GC	-
911401577041	DN392B LED16/840 PSU D150 WH GC	-
911401577341	DN392B LED16/830 PSD D150 WH GC	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-

Order Code	Full Product Name	CE mark
911401578341	DN391B LED11/830 PSU D150 WH GM	CE mark
911401578541	DN391B LED11/865 PSU D150 WH GM	CE mark
911401578941	DN392B LED16/830 PSU D150 WH GM	CE mark
911401579141	DN392B LED16/865 PSU D150 WH GM	CE mark
911401581741	DN391B LED11/840 PSD D150 WH GM	CE mark
911401583041	DN391B LED11/830 PSU D150 WH CAU	CE mark
911401583141	DN391B LED11/840 PSU D150 WH CAU	CE mark
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	CE mark
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	CE mark
911401584241	DN391B LED11/830 PSD D150 WH CAU	CE mark
911401584341	DN391B LED11/840 PSD D150 WH CAU	CE mark
911401585541	DN392B LED16/840 PSD D150 WH GM	CE mark
911401586041	DN391B LED11/840 PSU D150 WH R	-
911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401574241	DN393B LED22/830 PSU D200 ALU GC	-
911401574341	DN393B LED22/840 PSU D200 ALU GC	-
911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401579841	DN392B LED16/830 PSU D200 ALU GM	CE mark
911401579941	DN392B LED16/840 PSU D200 ALU GM	CE mark
911401580041	DN392B LED16/865 PSU D200 ALU GM	CE mark
911401580441	DN393B LED22/830 PSU D200 ALU GM	CE mark
911401580541	DN393B LED22/840 PSU D200 ALU GM	CE mark
911401580641	DN393B LED22/865 PSU D200 ALU GM	CE mark
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	CE mark
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	CE mark
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	CE mark
911401582641	DN393B LED22/830 PSD D200 ALU GM	CE mark
911401582741	DN393B LED22/840 PSD D200 ALU GM	CE mark
911401585241	DN393B LED22/830 PSD D200 ALU CAU	CE mark
911401585341	DN393B LED22/840 PSD D200 ALU CAU	CE mark
911401573041	DN392B LED16/830 PSU D200 WH GC	-
911401573141	DN392B LED16/840 PSU D200 WH GC	-
911401573241	DN392B LED16/865 PSU D200 WH GC	-
911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401574041	DN393B LED22/830 PSU D200 WH GC	-
911401574141	DN393B LED22/840 PSU D200 WH GC	-
911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401579541	DN392B LED16/830 PSU D200 WH GM	CE mark
911401579641	DN392B LED16/840 PSU D200 WH GM	CE mark
911401579741	DN392B LED16/865 PSU D200 WH GM	CE mark
911401580141	DN393B LED22/830 PSU D200 WH GM	CE mark
911401580341	DN393B LED22/865 PSU D200 WH GM	CE mark
911401582141	DN392B LED16/840 PSD D200 WH GM	CE mark
911401582441	DN393B LED22/830 PSD D200 WH GM	CE mark
911401582541	DN393B LED22/840 PSD D200 WH GM	CE mark
911401583341	DN392B LED16/840 PSU D200 WH CAU	CE mark
911401583441	DN393B LED22/830 PSU D200 WH CAU	CE mark
911401583541	DN393B LED22/840 PSU D200 WH CAU	CE mark
911401584741	DN392B LED16/840 PSD D200 WH CAU	CE mark
911401585141	DN393B LED22/840 PSD D200 WH CAU	CE mark

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401571941	DN390B LED6/840 PSU D100 ALU GC	60 degree(s)	4000 K	109 lm/W	600 lm
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	104 lm/W	570 lm
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	109 lm/W	600 lm
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401576541	DN391B LED11/830 PSU D100 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401576641	DN391B LED11/840 PSU D100 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401576841	DN391B LED11/840 PSD D100 ALU GC	60 degree(s)	4000 K	82 lm/W	950 lm
911401578141	DN390B LED6/840 PSU D100 ALU GM	60 degree(s)	4000 K	109 lm/W	600 lm
911401578241	DN390B LED6/865 PSU D100 ALU GM	60 degree(s)	6500 K	109 lm/W	600 lm
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	60 degree(s)	3000 K	104 lm/W	570 lm
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	60 degree(s)	4000 K	109 lm/W	600 lm
911401580941	DN390B LED6/865 PSU	60 degree(s)	6500 K	109 lm/W	600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	D100 ALU WP GM				
911401571641	DN390B LED6/830 PSU D100 WH GC	72 degree(s)	3000 K	104 lm/W	570 lm
911401571741	DN390B LED6/840 PSU D100 WH GC	72 degree(s)	4000 K	109 lm/W	600 lm
911401577741	DN390B LED6/830 PSU D100 WH GM	72 degree(s)	3000 K	104 lm/W	570 lm
911401577841	DN390B LED6/840 PSU D100 WH GM	72 degree(s)	4000 K	109 lm/W	600 lm
911401577941	DN390B LED6/865 PSU D100 WH GM	72 degree(s)	6500 K	109 lm/W	600 lm
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	72 degree(s)	3000 K	104 lm/W	570 lm
911401572341	DN391B LED11/830 PSU D150 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401572441	DN391B LED11/840 PSU D150 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401572541	DN391B LED11/865 PSU D150 ALU GC	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401572841	DN391B LED11/830 PSD D150 ALU GC	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401572941	DN391B LED11/840 PSD D150 ALU GC	60 degree(s)	4000 K	96 lm/W	1,100 lm
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	60 degree(s)	6500 K	110 lm/W	1,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401577141	DN392B LED16/830 PSU D150 ALU GC	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401577241	DN392B LED16/840 PSU D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401577641	DN392B LED16/840 PSD D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401578641	DN391B LED11/830 PSU D150 ALU GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401578741	DN391B LED11/840 PSU D150 ALU GM	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401578841	DN391B LED11/865 PSU D150 ALU GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401579241	DN392B LED16/830 PSU D150 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401579341	DN392B LED16/840 PSU D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401581841	DN391B LED11/830 PSD D150 ALU GM	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401581941	DN391B LED11/840 PSD D150 ALU GM	60 degree(s)	4000 K	96 lm/W	1,100 lm
911401584441	DN391B LED11/830 PSD D150 ALU CAU	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401585741	DN392B LED16/840 PSD D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401572041	DN391B LED11/830 PSU D150 WH GC	85 degree(s)	3000 K	111 lm/W	1,050 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401572141	DN391B LED11/840 PSU D150 WH GC	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401572241	DN391B LED11/865 PSU D150 WH GC	85 degree(s)	6500 K	116 lm/W	1,100 lm
911401572741	DN391B LED11/840 PSD D150 WH GC	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401575741	DN392B LED16/830 POE D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401576941	DN392B LED16/830 PSU D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401577041	DN392B LED16/840 PSU D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401577341	DN392B LED16/830 PSD D150 WH GC	85 degree(s)	3000 K	97 lm/W	1,500 lm
911401577441	DN392B LED16/840 PSD D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401578341	DN391B LED11/830 PSU D150 WH GM	85 degree(s)	3000 K	111 lm/W	1,050 lm
911401578541	DN391B LED11/865 PSU D150 WH GM	85 degree(s)	6500 K	116 lm/W	1,100 lm
911401578941	DN392B LED16/830 PSU D150 WH GM	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401579141	DN392B LED16/865 PSU D150 WH GM	85 degree(s)	6500 K	110 lm/W	1,600 lm
911401581741	DN391B LED11/840 PSD D150 WH GM	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401583041	DN391B LED11/830 PSU D150 WH CAU	85 degree(s)	3000 K	111 lm/W	1,050 lm
911401583141	DN391B LED11/840 PSU D150 WH CAU	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	85 degree(s)	3000 K	111 lm/W	1,050 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401584241	DN391B LED11/830 PSD D150 WH CAU	85 degree(s)	3000 K	91 lm/W	1,050 lm
911401584341	DN391B LED11/840 PSD D150 WH CAU	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401585541	DN392B LED16/840 PSD D150 WH GM	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401586041	DN391B LED11/840 PSU D150 WH R	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401573941	DN392B LED16/840 PSD D200 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401574241	DN393B LED22/830 PSU D200 ALU GC	60 degree(s)	3000 K	111 lm/W	2,100 lm
911401574341	DN393B LED22/840 PSU D200 ALU GC	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401574641	DN393B LED22/830 PSD D200 ALU GC	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401574741	DN393B LED22/840 PSD D200 ALU GC	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401579841	DN392B LED16/830 PSU D200 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401579941	DN392B LED16/840 PSU D200 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401580041	DN392B LED16/865 PSU D200 ALU GM	60 degree(s)	6500 K	110 lm/W	1,600 lm
911401580441	DN393B LED22/830 PSU D200 ALU GM	60 degree(s)	3000 K	111 lm/W	2,100 lm
911401580541	DN393B LED22/840 PSU D200 ALU GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401580641	DN393B LED22/865 PSU D200 ALU GM	60 degree(s)	6500 K	116 lm/W	2,200 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	60 degree(s)	3000 K	111 lm/W	2,100 lm
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	60 degree(s)	6500 K	116 lm/W	2,200 lm
911401582641	DN393B LED22/830 PSD D200 ALU GM	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401582741	DN393B LED22/840 PSD D200 ALU GM	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401585241	DN393B LED22/830 PSD D200 ALU CAU	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401585341	DN393B LED22/840 PSD D200 ALU CAU	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401573041	DN392B LED16/830 PSU D200 WH GC	92 degree(s)	3000 K	103 lm/W	1,500 lm
911401573141	DN392B LED16/840 PSU D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401573241	DN392B LED16/865 PSU D200 WH GC	92 degree(s)	6500 K	110 lm/W	1,600 lm
911401573741	DN392B LED16/840 PSD D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401574041	DN393B LED22/830 PSU D200 WH GC	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401574141	DN393B LED22/840 PSU D200 WH GC	92 degree(s)	4000 K	116 lm/W	2,200 lm
911401574541	DN393B LED22/840 PSD D200 WH GC	92 degree(s)	4000 K	107 lm/W	2,200 lm
911401579541	DN392B LED16/830 PSU D200 WH GM	92 degree(s)	3000 K	103 lm/W	1,500 lm



Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous Flux
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
911401579641	DN392B LED16/840 PSU D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401579741	DN392B LED16/865 PSU D200 WH GM	92 degree(s)	6500 K	110 lm/W	1,600 lm
911401580141	DN393B LED22/830 PSU D200 WH GM	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401580341	DN393B LED22/865 PSU D200 WH GM	92 degree(s)	6500 K	116 lm/W	2,200 lm
911401582141	DN392B LED16/840 PSD D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401582441	DN393B LED22/830 PSD D200 WH GM	92 degree(s)	3000 K	102 lm/W	2,100 lm

Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous Flux
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
911401582541	DN393B LED22/840 PSD D200 WH GM	92 degree(s)	4000 K	107 lm/W	2,200 lm
911401583341	DN392B LED16/840 PSU D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401583441	DN393B LED22/830 PSU D200 WH CAU	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401583541	DN393B LED22/840 PSU D200 WH CAU	92 degree(s)	4000 K	116 lm/W	2,200 lm
911401584741	DN392B LED16/840 PSD D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401585141	DN393B LED22/840 PSD D200 WH CAU	92 degree(s)	4000 K	107 lm/W	2,200 lm

## Operating and Electrical

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401571941	DN390B LED6/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	5.5 W
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401576541	DN391B LED11/830 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576641	DN391B LED11/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576841	DN391B LED11/840 PSD D100 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401578141	DN390B LED6/840 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401578241	DN390B LED6/865 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401571641	DN390B LED6/830 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401571741	DN390B LED6/840 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401577741	DN390B LED6/830 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577841	DN390B LED6/840 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577941	DN390B LED6/865 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	220-240 V	50 or 60 Hz	5.5 W
911401572341	DN391B LED11/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572441	DN391B LED11/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572541	DN391B LED11/865 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572841	DN391B LED11/830 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401572941	DN391B LED11/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401577141	DN392B LED16/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577241	DN392B LED16/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577641	DN392B LED16/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401578641	DN391B LED11/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578741	DN391B LED11/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578841	DN391B LED11/865 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401579241	DN392B LED16/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579341	DN392B LED16/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581841	DN391B LED11/830 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401581941	DN391B LED11/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401584441	DN391B LED11/830 PSD D150 ALU CAU	220-240 V	50 or 60 Hz	11.5 W
911401585741	DN392B LED16/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401572041	DN391B LED11/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572141	DN391B LED11/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572241	DN391B LED11/865 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572741	DN391B LED11/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	11.5 W
911401575741	DN392B LED16/830 POE D150 WH GC	53 V	- Hz	14.5 W
911401576941	DN392B LED16/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577041	DN392B LED16/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577341	DN392B LED16/830 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401577441	DN392B LED16/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401578341	DN391B LED11/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578541	DN391B LED11/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578941	DN392B LED16/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579141	DN392B LED16/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401581741	DN391B LED11/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	11.5 W
911401583041	DN391B LED11/830 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583141	DN391B LED11/840 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401584241	DN391B LED11/830 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401584341	DN391B LED11/840 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401585541	DN392B LED16/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401586041	DN391B LED11/840 PSU D150 WH R	220-240 V	50 or 60 Hz	9.5 W
911401573941	DN392B LED16/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401574241	DN393B LED22/830 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574341	DN393B LED22/840 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574641	DN393B LED22/830 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401574741	DN393B LED22/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401579841	DN392B LED16/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579941	DN392B LED16/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401580041	DN392B LED16/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401580441	DN393B LED22/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580541	DN393B LED22/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580641	DN393B LED22/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401582641	DN393B LED22/830 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401582741	DN393B LED22/840 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401585241	DN393B LED22/830 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401585341	DN393B LED22/840 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401573041	DN392B LED16/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573141	DN392B LED16/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573241	DN392B LED16/865 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573741	DN392B LED16/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401574041	DN393B LED22/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574141	DN393B LED22/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574541	DN393B LED22/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	20.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401579541	DN392B LED16/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579641	DN392B LED16/840 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579741	DN392B LED16/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401580141	DN393B LED22/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401580341	DN393B LED22/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401582141	DN392B LED16/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401582441	DN393B LED22/830 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401582541	DN393B LED22/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401583341	DN392B LED16/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	14.5 W
911401583441	DN393B LED22/830 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401583541	DN393B LED22/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401584741	DN392B LED16/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	15.5 W
911401585141	DN393B LED22/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	20.5 W

## Temperature

Order Code	Full Product Name	Ambient temperature range
911401571941	DN390B LED6/840 PSU D100 ALU GC	-20 to +40 °C
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-20 to +40 °C
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-20 to +40 °C
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-20 to +40 °C
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-20 to +40 °C
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-20 to +40 °C
911401576541	DN391B LED11/830 PSU D100 ALU GC	-20 to +40 °C
911401576641	DN391B LED11/840 PSU D100 ALU GC	-20 to +40 °C
911401576841	DN391B LED11/840 PSD D100 ALU GC	-20 to +40 °C
911401578141	DN390B LED6/840 PSU D100 ALU GM	-20 to +40 °C
911401578241	DN390B LED6/865 PSU D100 ALU GM	-20 to +40 °C
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	-20 to +40 °C
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	-20 to +40 °C
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	-20 to +40 °C
911401571641	DN390B LED6/830 PSU D100 WH GC	-20 to +40 °C
911401571741	DN390B LED6/840 PSU D100 WH GC	-20 to +40 °C
911401577741	DN390B LED6/830 PSU D100 WH GM	-20 to +40 °C
911401577841	DN390B LED6/840 PSU D100 WH GM	-20 to +40 °C
911401577941	DN390B LED6/865 PSU D100 WH GM	-20 to +40 °C
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	-20 to +40 °C
911401572341	DN391B LED11/830 PSU D150 ALU GC	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401572441	DN391B LED11/840 PSU D150 ALU GC	-20 to +40 °C
911401572541	DN391B LED11/865 PSU D150 ALU GC	-20 to +40 °C
911401572841	DN391B LED11/830 PSD D150 ALU GC	-20 to +40 °C
911401572941	DN391B LED11/840 PSD D150 ALU GC	-20 to +40 °C
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-20 to +40 °C
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-20 to +40 °C
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-20 to +40 °C
911401577141	DN392B LED16/830 PSU D150 ALU GC	-20 to +40 °C
911401577241	DN392B LED16/840 PSU D150 ALU GC	-20 to +40 °C
911401577641	DN392B LED16/840 PSD D150 ALU GC	-20 to +40 °C
911401578641	DN391B LED11/830 PSU D150 ALU GM	-20 to +40 °C
911401578741	DN391B LED11/840 PSU D150 ALU GM	-20 to +40 °C
911401578841	DN391B LED11/865 PSU D150 ALU GM	-20 to +40 °C
911401579241	DN392B LED16/830 PSU D150 ALU GM	-20 to +40 °C
911401579341	DN392B LED16/840 PSU D150 ALU GM	-20 to +40 °C
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	-20 to +40 °C
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	-20 to +40 °C
911401581841	DN391B LED11/830 PSD D150 ALU GM	-20 to +40 °C
911401581941	DN391B LED11/840 PSD D150 ALU GM	-20 to +40 °C
911401584441	DN391B LED11/830 PSD D150 ALU CAU	-20 to +40 °C
911401585741	DN392B LED16/840 PSD D150 ALU GM	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401572041	DN391B LED11/830 PSU D150 WH GC	-20 to +40 °C
911401572141	DN391B LED11/840 PSU D150 WH GC	-20 to +40 °C
911401572241	DN391B LED11/865 PSU D150 WH GC	-20 to +40 °C
911401572741	DN391B LED11/840 PSD D150 WH GC	-20 to +40 °C
911401575741	DN392B LED16/830 POE D150 WH GC	0 to +40 °C
911401576941	DN392B LED16/830 PSU D150 WH GC	-20 to +40 °C
911401577041	DN392B LED16/840 PSU D150 WH GC	-20 to +40 °C
911401577341	DN392B LED16/830 PSD D150 WH GC	-20 to +40 °C
911401577441	DN392B LED16/840 PSD D150 WH GC	-20 to +40 °C
911401578341	DN391B LED11/830 PSU D150 WH GM	-20 to +40 °C
911401578541	DN391B LED11/865 PSU D150 WH GM	-20 to +40 °C
911401578941	DN392B LED16/830 PSU D150 WH GM	-20 to +40 °C
911401579141	DN392B LED16/865 PSU D150 WH GM	-20 to +40 °C
911401581741	DN391B LED11/840 PSD D150 WH GM	-20 to +40 °C
911401583041	DN391B LED11/830 PSU D150 WH CAU	-20 to +40 °C
911401583141	DN391B LED11/840 PSU D150 WH CAU	-20 to +40 °C
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	-20 to +40 °C
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	-20 to +40 °C
911401584241	DN391B LED11/830 PSD D150 WH CAU	-20 to +40 °C
911401584341	DN391B LED11/840 PSD D150 WH CAU	-20 to +40 °C
911401585541	DN392B LED16/840 PSD D150 WH GM	-20 to +40 °C
911401586041	DN391B LED11/840 PSU D150 WH R	-20 to +40 °C
911401573941	DN392B LED16/840 PSD D200 ALU GC	-20 to +40 °C
911401574241	DN393B LED22/830 PSU D200 ALU GC	-20 to +40 °C
911401574341	DN393B LED22/840 PSU D200 ALU GC	-20 to +40 °C
911401574641	DN393B LED22/830 PSD D200 ALU GC	-20 to +40 °C
911401574741	DN393B LED22/840 PSD D200 ALU GC	-20 to +40 °C
911401579841	DN392B LED16/830 PSU D200 ALU GM	-20 to +40 °C
911401579941	DN392B LED16/840 PSU D200 ALU GM	-20 to +40 °C
911401580041	DN392B LED16/865 PSU D200 ALU GM	-20 to +40 °C
911401580441	DN393B LED22/830 PSU D200 ALU GM	-20 to +40 °C
911401580541	DN393B LED22/840 PSU D200 ALU GM	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401580641	DN393B LED22/865 PSU D200 ALU GM	-20 to +40 °C
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	-20 to +40 °C
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	-20 to +40 °C
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	-20 to +40 °C
911401582641	DN393B LED22/830 PSD D200 ALU GM	-20 to +40 °C
911401582741	DN393B LED22/840 PSD D200 ALU GM	-20 to +40 °C
911401585241	DN393B LED22/830 PSD D200 ALU CAU	-20 to +40 °C
911401585341	DN393B LED22/840 PSD D200 ALU CAU	-20 to +40 °C
911401573041	DN392B LED16/830 PSU D200 WH GC	-20 to +40 °C
911401573141	DN392B LED16/840 PSU D200 WH GC	-20 to +40 °C
911401573241	DN392B LED16/865 PSU D200 WH GC	-20 to +40 °C
911401573741	DN392B LED16/840 PSD D200 WH GC	-20 to +40 °C
911401574041	DN393B LED22/830 PSU D200 WH GC	-20 to +40 °C
911401574141	DN393B LED22/840 PSU D200 WH GC	-20 to +40 °C
911401574541	DN393B LED22/840 PSD D200 WH GC	-20 to +40 °C
911401579541	DN392B LED16/830 PSU D200 WH GM	-20 to +40 °C
911401579641	DN392B LED16/840 PSU D200 WH GM	-20 to +40 °C
911401579741	DN392B LED16/865 PSU D200 WH GM	-20 to +40 °C
911401580141	DN393B LED22/830 PSU D200 WH GM	-20 to +40 °C
911401580341	DN393B LED22/865 PSU D200 WH GM	-20 to +40 °C
911401582141	DN392B LED16/840 PSD D200 WH GM	-20 to +40 °C
911401582441	DN393B LED22/830 PSD D200 WH GM	-20 to +40 °C
911401582541	DN393B LED22/840 PSD D200 WH GM	-20 to +40 °C
911401583341	DN392B LED16/840 PSU D200 WH CAU	-20 to +40 °C
911401583441	DN393B LED22/830 PSU D200 WH CAU	-20 to +40 °C
911401583541	DN393B LED22/840 PSU D200 WH CAU	-20 to +40 °C
911401584741	DN392B LED16/840 PSD D200 WH CAU	-20 to +40 °C
911401585141	DN393B LED22/840 PSD D200 WH CAU	-20 to +40 °C

## Controls and Dimming

Order Code	Full Product Name	Dimmable
911401571941	DN390B LED6/840 PSU D100 ALU GC	No
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	No
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	No
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	No
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	No
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	No
911401576541	DN391B LED11/830 PSU D100 ALU GC	No
911401576641	DN391B LED11/840 PSU D100 ALU GC	No
911401576841	DN391B LED11/840 PSD D100 ALU GC	Yes
911401578141	DN390B LED6/840 PSU D100 ALU GM	No
911401578241	DN390B LED6/865 PSU D100 ALU GM	No
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	No
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	No
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	No
911401571641	DN390B LED6/830 PSU D100 WH GC	No
911401571741	DN390B LED6/840 PSU D100 WH GC	No

Order Code	Full Product Name	Dimmable
911401577741	DN390B LED6/830 PSU D100 WH GM	No
911401577841	DN390B LED6/840 PSU D100 WH GM	No
911401577941	DN390B LED6/865 PSU D100 WH GM	No
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	No
911401572341	DN391B LED11/830 PSU D150 ALU GC	No
911401572441	DN391B LED11/840 PSU D150 ALU GC	No
911401572541	DN391B LED11/865 PSU D150 ALU GC	No
911401572841	DN391B LED11/830 PSD D150 ALU GC	Yes
911401572941	DN391B LED11/840 PSD D150 ALU GC	Yes
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	No
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	No
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	No
911401577141	DN392B LED16/830 PSU D150 ALU GC	No
911401577241	DN392B LED16/840 PSU D150 ALU GC	No
911401577641	DN392B LED16/840 PSD D150 ALU GC	Yes
911401578641	DN391B LED11/830 PSU D150 ALU GM	No

Order Code	Full Product Name	Dimmable
911401578741	DN391B LED11/840 PSU D150 ALU GM	No
911401578841	DN391B LED11/865 PSU D150 ALU GM	No
911401579241	DN392B LED16/830 PSU D150 ALU GM	No
911401579341	DN392B LED16/840 PSU D150 ALU GM	No
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	No
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	No
911401581841	DN391B LED11/830 PSD D150 ALU GM	Yes
911401581941	DN391B LED11/840 PSD D150 ALU GM	Yes
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Yes
911401585741	DN392B LED16/840 PSD D150 ALU GM	Yes
911401572041	DN391B LED11/830 PSU D150 WH GC	No
911401572141	DN391B LED11/840 PSU D150 WH GC	No
911401572241	DN391B LED11/865 PSU D150 WH GC	No
911401572741	DN391B LED11/840 PSD D150 WH GC	Yes
911401575741	DN392B LED16/830 POE D150 WH GC	Yes
911401576941	DN392B LED16/830 PSU D150 WH GC	No
911401577041	DN392B LED16/840 PSU D150 WH GC	No
911401577341	DN392B LED16/830 PSD D150 WH GC	Yes
911401577441	DN392B LED16/840 PSD D150 WH GC	Yes
911401578341	DN391B LED11/830 PSU D150 WH GM	No
911401578541	DN391B LED11/865 PSU D150 WH GM	No
911401578941	DN392B LED16/830 PSU D150 WH GM	No
911401579141	DN392B LED16/865 PSU D150 WH GM	No
911401581741	DN391B LED11/840 PSD D150 WH GM	Yes
911401583041	DN391B LED11/830 PSU D150 WH CAU	No
911401583141	DN391B LED11/840 PSU D150 WH CAU	No
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	No
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	No
911401584241	DN391B LED11/830 PSD D150 WH CAU	Yes
911401584341	DN391B LED11/840 PSD D150 WH CAU	Yes
911401585541	DN392B LED16/840 PSD D150 WH GM	Yes
911401586041	DN391B LED11/840 PSU D150 WH R	No
911401573941	DN392B LED16/840 PSD D200 ALU GC	Yes
911401574241	DN393B LED22/830 PSU D200 ALU GC	No
911401574341	DN393B LED22/840 PSU D200 ALU GC	No

Order Code	Full Product Name	Dimmable
911401574641	DN393B LED22/830 PSD D200 ALU GC	Yes
911401574741	DN393B LED22/840 PSD D200 ALU GC	Yes
911401579841	DN392B LED16/830 PSU D200 ALU GM	No
911401579941	DN392B LED16/840 PSU D200 ALU GM	No
911401580041	DN392B LED16/865 PSU D200 ALU GM	No
911401580441	DN393B LED22/830 PSU D200 ALU GM	No
911401580541	DN393B LED22/840 PSU D200 ALU GM	No
911401580641	DN393B LED22/865 PSU D200 ALU GM	No
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	No
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	No
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	No
911401582641	DN393B LED22/830 PSD D200 ALU GM	Yes
911401582741	DN393B LED22/840 PSD D200 ALU GM	Yes
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Yes
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Yes
911401573041	DN392B LED16/830 PSU D200 WH GC	No
911401573141	DN392B LED16/840 PSU D200 WH GC	No
911401573241	DN392B LED16/865 PSU D200 WH GC	No
911401573741	DN392B LED16/840 PSD D200 WH GC	Yes
911401574041	DN393B LED22/830 PSU D200 WH GC	No
911401574141	DN393B LED22/840 PSU D200 WH GC	No
911401574541	DN393B LED22/840 PSD D200 WH GC	Yes
911401579541	DN392B LED16/830 PSU D200 WH GM	No
911401579641	DN392B LED16/840 PSU D200 WH GM	No
911401579741	DN392B LED16/865 PSU D200 WH GM	No
911401580141	DN393B LED22/830 PSU D200 WH GM	No
911401580341	DN393B LED22/865 PSU D200 WH GM	No
911401582141	DN392B LED16/840 PSD D200 WH GM	Yes
911401582441	DN393B LED22/830 PSD D200 WH GM	Yes
911401582541	DN393B LED22/840 PSD D200 WH GM	Yes
911401583341	DN392B LED16/840 PSU D200 WH CAU	No
911401583441	DN393B LED22/830 PSU D200 WH CAU	No
911401583541	DN393B LED22/840 PSU D200 WH CAU	No
911401584741	DN392B LED16/840 PSD D200 WH CAU	Yes
911401585141	DN393B LED22/840 PSD D200 WH CAU	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401571941	DN390B LED6/840 PSU D100 ALU GC	Safety class I	IP20
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Safety class I	IP20/54
911401576541	DN391B LED11/830 PSU D100 ALU GC	Safety class I	IP20
911401576641	DN391B LED11/840 PSU D100 ALU GC	Safety class I	IP20
911401576841	DN391B LED11/840 PSD D100 ALU GC	Safety class I	IP20
911401578141	DN390B LED6/840 PSU D100 ALU GM	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401578241	DN390B LED6/865 PSU D100 ALU GM	Safety class I	IP20
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Safety class I	IP20/54
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Safety class I	IP20/54
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Safety class I	IP20/54
911401571641	DN390B LED6/830 PSU D100 WH GC	Safety class I	IP20
911401571741	DN390B LED6/840 PSU D100 WH GC	Safety class I	IP20
911401577741	DN390B LED6/830 PSU D100 WH GM	Safety class I	IP20
911401577841	DN390B LED6/840 PSU D100 WH GM	Safety class I	IP20
911401577941	DN390B LED6/865 PSU D100 WH GM	Safety class I	IP20
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Safety class I	IP20/54
911401572341	DN391B LED11/830 PSU D150 ALU GC	Safety class I	IP20
911401572441	DN391B LED11/840 PSU D150 ALU GC	Safety class I	IP20
911401572541	DN391B LED11/865 PSU D150 ALU GC	Safety class I	IP20
911401572841	DN391B LED11/830 PSD D150 ALU GC	Safety class I	IP20
911401572941	DN391B LED11/840 PSD D150 ALU GC	Safety class I	IP20
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Safety class I	IP20/54
911401577141	DN392B LED16/830 PSU D150 ALU GC	Safety class I	IP20
911401577241	DN392B LED16/840 PSU D150 ALU GC	Safety class I	IP20
911401577641	DN392B LED16/840 PSD D150 ALU GC	Safety class I	IP20
911401578641	DN391B LED11/830 PSU D150 ALU GM	Safety class I	IP20
911401578741	DN391B LED11/840 PSU D150 ALU GM	Safety class I	IP20
911401578841	DN391B LED11/865 PSU D150 ALU GM	Safety class I	IP20
911401579241	DN392B LED16/830 PSU D150 ALU GM	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401579341	DN392B LED16/840 PSU D150 ALU GM	Safety class I	IP20
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581841	DN391B LED11/830 PSD D150 ALU GM	Safety class I	IP20
911401581941	DN391B LED11/840 PSD D150 ALU GM	Safety class I	IP20
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Safety class I	IP20
911401585741	DN392B LED16/840 PSD D150 ALU GM	Safety class I	IP20
911401572041	DN391B LED11/830 PSU D150 WH GC	Safety class I	IP20
911401572141	DN391B LED11/840 PSU D150 WH GC	Safety class I	IP20
911401572241	DN391B LED11/865 PSU D150 WH GC	Safety class I	IP20
911401572741	DN391B LED11/840 PSD D150 WH GC	Safety class I	IP20
911401575741	DN392B LED16/830 POE D150 WH GC	Safety class III	IP20
911401576941	DN392B LED16/830 PSU D150 WH GC	Safety class I	IP20
911401577041	DN392B LED16/840 PSU D150 WH GC	Safety class I	IP20
911401577341	DN392B LED16/830 PSD D150 WH GC	Safety class I	IP20
911401577441	DN392B LED16/840 PSD D150 WH GC	Safety class I	IP20
911401578341	DN391B LED11/830 PSU D150 WH GM	Safety class I	IP20
911401578541	DN391B LED11/865 PSU D150 WH GM	Safety class I	IP20
911401578941	DN392B LED16/830 PSU D150 WH GM	Safety class I	IP20
911401579141	DN392B LED16/865 PSU D150 WH GM	Safety class I	IP20
911401581741	DN391B LED11/840 PSD D150 WH GM	Safety class I	IP20
911401583041	DN391B LED11/830 PSU D150 WH CAU	Safety class I	IP20
911401583141	DN391B LED11/840 PSU D150 WH CAU	Safety class I	IP20
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Safety class I	IP20/54
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401584241	DN391B LED11/830 PSD D150 WH CAU	Safety class I	IP20
911401584341	DN391B LED11/840 PSD D150 WH CAU	Safety class I	IP20
911401585541	DN392B LED16/840 PSD D150 WH GM	Safety class I	IP20
911401586041	DN391B LED11/840 PSU D150 WH R	Safety class II	IP20
911401573941	DN392B LED16/840 PSD D200 ALU GC	Safety class I	IP20
911401574241	DN393B LED22/830 PSU D200 ALU GC	Safety class I	IP20
911401574341	DN393B LED22/840 PSU D200 ALU GC	Safety class I	IP20
911401574641	DN393B LED22/830 PSD D200 ALU GC	Safety class I	IP20
911401574741	DN393B LED22/840 PSD D200 ALU GC	Safety class I	IP20
911401579841	DN392B LED16/830 PSU D200 ALU GM	Safety class I	IP20
911401579941	DN392B LED16/840 PSU D200 ALU GM	Safety class I	IP20
911401580041	DN392B LED16/865 PSU D200 ALU GM	Safety class I	IP20
911401580441	DN393B LED22/830 PSU D200 ALU GM	Safety class I	IP20
911401580541	DN393B LED22/840 PSU D200 ALU GM	Safety class I	IP20
911401580641	DN393B LED22/865 PSU D200 ALU GM	Safety class I	IP20
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Safety class I	IP20/54
911401582641	DN393B LED22/830 PSD D200 ALU GM	Safety class I	IP20
911401582741	DN393B LED22/840 PSD D200 ALU GM	Safety class I	IP20
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Safety class I	IP20
911401573041	DN392B LED16/830 PSU D200 WH GC	Safety class I	IP20
911401573141	DN392B LED16/840 PSU D200 WH GC	Safety class I	IP20
911401573241	DN392B LED16/865 PSU D200 WH GC	Safety class I	IP20
911401573741	DN392B LED16/840 PSD D200 WH GC	Safety class I	IP20
911401574041	DN393B LED22/830 PSU D200 WH GC	Safety class I	IP20
911401574141	DN393B LED22/840 PSU D200 WH GC	Safety class I	IP20
911401574541	DN393B LED22/840 PSD D200 WH GC	Safety class I	IP20
911401579541	DN392B LED16/830 PSU D200 WH GM	Safety class I	IP20
911401579641	DN392B LED16/840 PSU D200 WH GM	Safety class I	IP20
911401579741	DN392B LED16/865 PSU D200 WH GM	Safety class I	IP20
911401580141	DN393B LED22/830 PSU D200 WH GM	Safety class I	IP20
911401580341	DN393B LED22/865 PSU D200 WH GM	Safety class I	IP20
911401582141	DN392B LED16/840 PSD D200 WH GM	Safety class I	IP20
911401582441	DN393B LED22/830 PSD D200 WH GM	Safety class I	IP20
911401582541	DN393B LED22/840 PSD D200 WH GM	Safety class I	IP20
911401583341	DN392B LED16/840 PSU D200 WH CAU	Safety class I	IP20
911401583441	DN393B LED22/830 PSU D200 WH CAU	Safety class I	IP20
911401583541	DN393B LED22/840 PSU D200 WH CAU	Safety class I	IP20
911401584741	DN392B LED16/840 PSD D200 WH CAU	Safety class I	IP20
911401585141	DN393B LED22/840 PSD D200 WH CAU	Safety class I	IP20

**Initial Performance (IEC Compliant)**

Order Code	Full Product Name	Initial chromaticity
911401571941	DN390B LED6/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	(0.31,0.32) SDCM<5
911401576541	DN391B LED11/830 PSU D100 ALU GC	(0.44,0.403) SDCM<5
911401576641	DN391B LED11/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401576841	DN391B LED11/840 PSD D100 ALU GC	(0.38,0.38) SDCM<5
911401578141	DN390B LED6/840 PSU D100 ALU GM	(0.38,0.38) SDCM<5
911401578241	DN390B LED6/865 PSU D100 ALU GM	(0.31,0.32) SDCM<5
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	(0.44,0.403) SDCM<5
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	(0.38,0.38) SDCM<5
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	(0.31,0.32) SDCM<5
911401571641	DN390B LED6/830 PSU D100 WH GC	(0.44,0.403) SDCM<5
911401571741	DN390B LED6/840 PSU D100 WH GC	(0.38,0.38) SDCM<5
911401577741	DN390B LED6/830 PSU D100 WH GM	(0.44,0.403) SDCM<5
911401577841	DN390B LED6/840 PSU D100 WH GM	(0.38,0.38) SDCM<5
911401577941	DN390B LED6/865 PSU D100 WH GM	(0.31,0.32) SDCM<5
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	(0.44,0.403) SDCM<5
911401572341	DN391B LED11/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401572441	DN391B LED11/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401572541	DN391B LED11/865 PSU D150 ALU GC	(0.31,0.32) SDCM<5
911401572841	DN391B LED11/830 PSD D150 ALU GC	(0.44,0.403) SDCM<5
911401572941	DN391B LED11/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	(0.44,0.403) SDCM<5
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	(0.38,0.38) SDCM<5
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	(0.31,0.32) SDCM<5
911401577141	DN392B LED16/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401577241	DN392B LED16/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401577641	DN392B LED16/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401578641	DN391B LED11/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401578741	DN391B LED11/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401578841	DN391B LED11/865 PSU D150 ALU GM	(0.31,0.32) SDCM<5
911401579241	DN392B LED16/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401579341	DN392B LED16/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	(0.44,0.403) SDCM<5
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	(0.31,0.32) SDCM<5
911401581841	DN391B LED11/830 PSD D150 ALU GM	(0.44,0.403) SDCM<5
911401581941	DN391B LED11/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401584441	DN391B LED11/830 PSD D150 ALU CAU	(0.44,0.403) SDCM<5
911401585741	DN392B LED16/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401572041	DN391B LED11/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401572141	DN391B LED11/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401572241	DN391B LED11/865 PSU D150 WH GC	(0.31,0.32) SDCM<5
911401572741	DN391B LED11/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401575741	DN392B LED16/830 POE D150 WH GC	(0.44,0.403) SDCM<5
911401576941	DN392B LED16/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401577041	DN392B LED16/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401577341	DN392B LED16/830 PSD D150 WH GC	(0.44,0.403) SDCM<5
911401577441	DN392B LED16/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401578341	DN391B LED11/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401578541	DN391B LED11/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
911401578941	DN392B LED16/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401579141	DN392B LED16/865 PSU D150 WH GM	(0.31,0.32) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401581741	DN391B LED11/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401583041	DN391B LED11/830 PSU D150 WH CAU	(0.44,0.403) SDCM<5
911401583141	DN391B LED11/840 PSU D150 WH CAU	(0.38,0.38) SDCM<5
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	(0.44,0.403) SDCM<5
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	(0.38,0.38) SDCM<5
911401584241	DN391B LED11/830 PSD D150 WH CAU	(0.44,0.403) SDCM<5
911401584341	DN391B LED11/840 PSD D150 WH CAU	(0.38,0.38) SDCM<5
911401585541	DN392B LED16/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401586041	DN391B LED11/840 PSU D150 WH R	(0.38,0.38) SDCM<5
911401573941	DN392B LED16/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401574241	DN393B LED22/830 PSU D200 ALU GC	(0.44,0.403) SDCM<5
911401574341	DN393B LED22/840 PSU D200 ALU GC	(0.38,0.38) SDCM<5
911401574641	DN393B LED22/830 PSD D200 ALU GC	(0.44,0.403) SDCM<5
911401574741	DN393B LED22/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401579841	DN392B LED16/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401579941	DN392B LED16/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580041	DN392B LED16/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401580441	DN393B LED22/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401580541	DN393B LED22/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580641	DN393B LED22/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	(0.44,0.403) SDCM<5
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	(0.38,0.38) SDCM<5
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	(0.31,0.32) SDCM<5
911401582641	DN393B LED22/830 PSD D200 ALU GM	(0.44,0.403) SDCM<5
911401582741	DN393B LED22/840 PSD D200 ALU GM	(0.38,0.38) SDCM<5
911401585241	DN393B LED22/830 PSD D200 ALU CAU	(0.44,0.403) SDCM<5
911401585341	DN393B LED22/840 PSD D200 ALU CAU	(0.38,0.38) SDCM<5
911401573041	DN392B LED16/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401573141	DN392B LED16/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401573241	DN392B LED16/865 PSU D200 WH GC	(0.31,0.32) SDCM<5
911401573741	DN392B LED16/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401574041	DN393B LED22/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401574141	DN393B LED22/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401574541	DN393B LED22/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401579541	DN392B LED16/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401579641	DN392B LED16/840 PSU D200 WH GM	(0.38,0.38) SDCM<5
911401579741	DN392B LED16/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401580141	DN393B LED22/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401580341	DN393B LED22/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401582141	DN392B LED16/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401582441	DN393B LED22/830 PSD D200 WH GM	(0.44,0.403) SDCM<5
911401582541	DN393B LED22/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401583341	DN392B LED16/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401583441	DN393B LED22/830 PSU D200 WH CAU	(0.44,0.403) SDCM<5
911401583541	DN393B LED22/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401584741	DN392B LED16/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5
911401585141	DN393B LED22/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5

Over Time Performance (IEC Compliant)



Order Code	Full Product Name	Driver failure rate at 5000	
		h	
911401571941	DN390B LED6/840 PSU D100 ALU GC	0.12	%
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	0.12	%
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	0.12	%
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	0.12	%
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	0.12	%
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	0.12	%
911401576541	DN391B LED11/830 PSU D100 ALU GC	0.12	%
911401576641	DN391B LED11/840 PSU D100 ALU GC	0.12	%
911401576841	DN391B LED11/840 PSD D100 ALU GC	0.12	%
911401578141	DN390B LED6/840 PSU D100 ALU GM	0.12	%
911401578241	DN390B LED6/865 PSU D100 ALU GM	0.12	%
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	0.12	%
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	0.12	%
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	0.12	%
911401571641	DN390B LED6/830 PSU D100 WH GC	0.12	%
911401571741	DN390B LED6/840 PSU D100 WH GC	0.12	%
911401577741	DN390B LED6/830 PSU D100 WH GM	0.12	%
911401577841	DN390B LED6/840 PSU D100 WH GM	0.12	%
911401577941	DN390B LED6/865 PSU D100 WH GM	0.12	%
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	0.12	%
911401572341	DN391B LED11/830 PSU D150 ALU GC	0.12	%
911401572441	DN391B LED11/840 PSU D150 ALU GC	0.12	%
911401572541	DN391B LED11/865 PSU D150 ALU GC	0.12	%
911401572841	DN391B LED11/830 PSD D150 ALU GC	0.12	%
911401572941	DN391B LED11/840 PSD D150 ALU GC	0.12	%
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	0.16	%
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	0.16	%
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	0.16	%
911401577141	DN392B LED16/830 PSU D150 ALU GC	0.16	%
911401577241	DN392B LED16/840 PSU D150 ALU GC	0.16	%
911401577641	DN392B LED16/840 PSD D150 ALU GC	0.16	%
911401578641	DN391B LED11/830 PSU D150 ALU GM	0.12	%
911401578741	DN391B LED11/840 PSU D150 ALU GM	0.12	%
911401578841	DN391B LED11/865 PSU D150 ALU GM	0.12	%
911401579241	DN392B LED16/830 PSU D150 ALU GM	0.16	%
911401579341	DN392B LED16/840 PSU D150 ALU GM	0.16	%
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	0.12	%
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	0.12	%
911401581841	DN391B LED11/830 PSD D150 ALU GM	0.12	%
911401581941	DN391B LED11/840 PSD D150 ALU GM	0.12	%
911401584441	DN391B LED11/830 PSD D150 ALU CAU	0.12	%
911401585741	DN392B LED16/840 PSD D150 ALU GM	0.16	%
911401572041	DN391B LED11/830 PSU D150 WH GC	0.12	%
911401572141	DN391B LED11/840 PSU D150 WH GC	0.12	%
911401572241	DN391B LED11/865 PSU D150 WH GC	0.12	%
911401572741	DN391B LED11/840 PSD D150 WH GC	0.12	%
911401575741	DN392B LED16/830 POE D150 WH GC	0.16	%
911401576941	DN392B LED16/830 PSU D150 WH GC	0.16	%
911401577041	DN392B LED16/840 PSU D150 WH GC	0.16	%
911401577341	DN392B LED16/830 PSD D150 WH GC	0.16	%
911401577441	DN392B LED16/840 PSD D150 WH GC	0.16	%

Order Code	Full Product Name	Driver failure rate at 5000	
		h	
911401578341	DN391B LED11/830 PSU D150 WH GM	0.12	%
911401578541	DN391B LED11/865 PSU D150 WH GM	0.12	%
911401578941	DN392B LED16/830 PSU D150 WH GM	0.16	%
911401579141	DN392B LED16/865 PSU D150 WH GM	0.16	%
911401581741	DN391B LED11/840 PSD D150 WH GM	0.12	%
911401583041	DN391B LED11/830 PSU D150 WH CAU	0.12	%
911401583141	DN391B LED11/840 PSU D150 WH CAU	0.12	%
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	0.12	%
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	0.12	%
911401584241	DN391B LED11/830 PSD D150 WH CAU	0.12	%
911401584341	DN391B LED11/840 PSD D150 WH CAU	0.12	%
911401585541	DN392B LED16/840 PSD D150 WH GM	0.16	%
911401586041	DN391B LED11/840 PSU D150 WH R	0.12	%
911401573941	DN392B LED16/840 PSD D200 ALU GC	0.16	%
911401574241	DN393B LED22/830 PSU D200 ALU GC	0.12	%
911401574341	DN393B LED22/840 PSU D200 ALU GC	0.12	%
911401574641	DN393B LED22/830 PSD D200 ALU GC	0.12	%
911401574741	DN393B LED22/840 PSD D200 ALU GC	0.12	%
911401579841	DN392B LED16/830 PSU D200 ALU GM	0.16	%
911401579941	DN392B LED16/840 PSU D200 ALU GM	0.16	%
911401580041	DN392B LED16/865 PSU D200 ALU GM	0.16	%
911401580441	DN393B LED22/830 PSU D200 ALU GM	0.12	%
911401580541	DN393B LED22/840 PSU D200 ALU GM	0.12	%
911401580641	DN393B LED22/865 PSU D200 ALU GM	0.12	%
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	0.12	%
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	0.12	%
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	0.12	%
911401582641	DN393B LED22/830 PSD D200 ALU GM	0.12	%
911401582741	DN393B LED22/840 PSD D200 ALU GM	0.12	%
911401585241	DN393B LED22/830 PSD D200 ALU CAU	0.12	%
911401585341	DN393B LED22/840 PSD D200 ALU CAU	0.12	%
911401573041	DN392B LED16/830 PSU D200 WH GC	0.16	%
911401573141	DN392B LED16/840 PSU D200 WH GC	0.16	%
911401573241	DN392B LED16/865 PSU D200 WH GC	0.16	%
911401573741	DN392B LED16/840 PSD D200 WH GC	0.16	%
911401574041	DN393B LED22/830 PSU D200 WH GC	0.12	%
911401574141	DN393B LED22/840 PSU D200 WH GC	0.12	%
911401574541	DN393B LED22/840 PSD D200 WH GC	0.12	%
911401579541	DN392B LED16/830 PSU D200 WH GM	0.16	%
911401579641	DN392B LED16/840 PSU D200 WH GM	0.16	%
911401579741	DN392B LED16/865 PSU D200 WH GM	0.16	%
911401580141	DN393B LED22/830 PSU D200 WH GM	0.12	%
911401580341	DN393B LED22/865 PSU D200 WH GM	0.12	%
911401582141	DN392B LED16/840 PSD D200 WH GM	0.16	%
911401582441	DN393B LED22/830 PSD D200 WH GM	0.12	%
911401582541	DN393B LED22/840 PSD D200 WH GM	0.12	%
911401583341	DN392B LED16/840 PSU D200 WH CAU	0.16	%
911401583441	DN393B LED22/830 PSU D200 WH CAU	0.12	%
911401583541	DN393B LED22/840 PSU D200 WH CAU	0.12	%
911401584741	DN392B LED16/840 PSD D200 WH CAU	0.16	%
911401585141	DN393B LED22/840 PSD D200 WH CAU	0.12	%

Application Conditions

Order Code	Full Product Name	Maximum dim level	Order Code	Full Product Name	Maximum dim level
911401571941	DN390B LED6/840 PSU D100 ALU GC	Not applicable	911401578341	DN391B LED11/830 PSU D150 WH GM	Not applicable
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Not applicable	911401578541	DN391B LED11/865 PSU D150 WH GM	Not applicable
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Not applicable	911401578941	DN392B LED16/830 PSU D150 WH GM	Not applicable
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Not applicable	911401579141	DN392B LED16/865 PSU D150 WH GM	Not applicable
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Not applicable	911401581741	DN391B LED11/840 PSD D150 WH GM	-
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Not applicable	911401583041	DN391B LED11/830 PSU D150 WH CAU	Not applicable
911401576541	DN391B LED11/830 PSU D100 ALU GC	Not applicable	911401583141	DN391B LED11/840 PSU D150 WH CAU	Not applicable
911401576641	DN391B LED11/840 PSU D100 ALU GC	Not applicable	911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Not applicable
911401576841	DN391B LED11/840 PSD D100 ALU GC	-	911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Not applicable
911401578141	DN390B LED6/840 PSU D100 ALU GM	Not applicable	911401584241	DN391B LED11/830 PSD D150 WH CAU	-
911401578241	DN390B LED6/865 PSU D100 ALU GM	Not applicable	911401584341	DN391B LED11/840 PSD D150 WH CAU	-
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Not applicable	911401585541	DN392B LED16/840 PSD D150 WH GM	-
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Not applicable	911401586041	DN391B LED11/840 PSU D150 WH R	Not applicable
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Not applicable	911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401571641	DN390B LED6/830 PSU D100 WH GC	Not applicable	911401574241	DN393B LED22/830 PSU D200 ALU GC	Not applicable
911401571741	DN390B LED6/840 PSU D100 WH GC	Not applicable	911401574341	DN393B LED22/840 PSU D200 ALU GC	Not applicable
911401577741	DN390B LED6/830 PSU D100 WH GM	Not applicable	911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401577841	DN390B LED6/840 PSU D100 WH GM	Not applicable	911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401577941	DN390B LED6/865 PSU D100 WH GM	Not applicable	911401579841	DN392B LED16/830 PSU D200 ALU GM	Not applicable
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Not applicable	911401579941	DN392B LED16/840 PSU D200 ALU GM	Not applicable
911401572341	DN391B LED11/830 PSU D150 ALU GC	Not applicable	911401580041	DN392B LED16/865 PSU D200 ALU GM	Not applicable
911401572441	DN391B LED11/840 PSU D150 ALU GC	Not applicable	911401580441	DN393B LED22/830 PSU D200 ALU GM	Not applicable
911401572541	DN391B LED11/865 PSU D150 ALU GC	Not applicable	911401580541	DN393B LED22/840 PSU D200 ALU GM	Not applicable
911401572841	DN391B LED11/830 PSD D150 ALU GC	-	911401580641	DN393B LED22/865 PSU D200 ALU GM	Not applicable
911401572941	DN391B LED11/840 PSD D150 ALU GC	-	911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Not applicable
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Not applicable	911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Not applicable
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Not applicable	911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Not applicable
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Not applicable	911401582641	DN393B LED22/830 PSD D200 ALU GM	-
911401577141	DN392B LED16/830 PSU D150 ALU GC	Not applicable	911401582741	DN393B LED22/840 PSD D200 ALU GM	-
911401577241	DN392B LED16/840 PSU D150 ALU GC	Not applicable	911401585241	DN393B LED22/830 PSD D200 ALU CAU	-
911401577641	DN392B LED16/840 PSD D150 ALU GC	-	911401585341	DN393B LED22/840 PSD D200 ALU CAU	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	Not applicable	911401573041	DN392B LED16/830 PSU D200 WH GC	Not applicable
911401578741	DN391B LED11/840 PSU D150 ALU GM	Not applicable	911401573141	DN392B LED16/840 PSU D200 WH GC	Not applicable
911401578841	DN391B LED11/865 PSU D150 ALU GM	Not applicable	911401573241	DN392B LED16/865 PSU D200 WH GC	Not applicable
911401579241	DN392B LED16/830 PSU D150 ALU GM	Not applicable	911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401579341	DN392B LED16/840 PSU D150 ALU GM	Not applicable	911401574041	DN393B LED22/830 PSU D200 WH GC	Not applicable
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Not applicable	911401574141	DN393B LED22/840 PSU D200 WH GC	Not applicable
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Not applicable	911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401581841	DN391B LED11/830 PSD D150 ALU GM	-	911401579541	DN392B LED16/830 PSU D200 WH GM	Not applicable
911401581941	DN391B LED11/840 PSD D150 ALU GM	-	911401579641	DN392B LED16/840 PSU D200 WH GM	Not applicable
911401584441	DN391B LED11/830 PSD D150 ALU CAU	-	911401579741	DN392B LED16/865 PSU D200 WH GM	Not applicable
911401585741	DN392B LED16/840 PSD D150 ALU GM	-	911401580141	DN393B LED22/830 PSU D200 WH GM	Not applicable
911401572041	DN391B LED11/830 PSU D150 WH GC	Not applicable	911401580341	DN393B LED22/865 PSU D200 WH GM	Not applicable
911401572141	DN391B LED11/840 PSU D150 WH GC	Not applicable	911401582141	DN392B LED16/840 PSD D200 WH GM	-
911401572241	DN391B LED11/865 PSU D150 WH GC	Not applicable	911401582441	DN393B LED22/830 PSD D200 WH GM	-
911401572741	DN391B LED11/840 PSD D150 WH GC	-	911401582541	DN393B LED22/840 PSD D200 WH GM	-
911401575741	DN392B LED16/830 POE D150 WH GC	-	911401583341	DN392B LED16/840 PSU D200 WH CAU	Not applicable
911401576941	DN392B LED16/830 PSU D150 WH GC	Not applicable	911401583441	DN393B LED22/830 PSU D200 WH CAU	Not applicable
911401577041	DN392B LED16/840 PSU D150 WH GC	Not applicable	911401583541	DN393B LED22/840 PSU D200 WH CAU	Not applicable
911401577341	DN392B LED16/830 PSD D150 WH GC	-	911401584741	DN392B LED16/840 PSD D200 WH CAU	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-	911401585141	DN393B LED22/840 PSD D200 WH CAU	-

