



# Make roads safer and sustainable.

## GreenVision Xceed Gen2

Sustainability, citizen well being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving this goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads & streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, highways and rural areas – our luminaires provide the optimal light for all application areas. And, GreenVision Xceed Gen2 is ready to be connected and work with smart city ecosystem. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

### Benefits

- Robust & Reliable with a long service lifetime
- Elegant finless design
- Equipped with a Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation, and spare part information

### Features

- System efficacy 140lm/W  $\pm 10\%$
- Long service lifetime 100Khrs L70@Ta 35°C
- With 10kV or 15kV Surge protection Device

### Application


- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)
- Traffic routes and main access road
- Urban and residential area

# GreenVision Xceed Gen2

## Specifications

<b>Material</b>	Housing: die-cast aluminiumOptic: polycarbonateOptic cover: glass	<b>Power</b>	up to 390W
<b>Light Source</b>	3030 LED5050 LEDHigh Power LED	<b>Mains Voltage</b>	220-240V / 50-60HzOptional 120-277V / 50-60Hz
<b>Installation</b>	Side entry 42-60mmOptional adjustable spigot	<b>Control system input</b>	DALI / 1-10V / D4i
<b>Luminous flux</b>	System flux up to 55000lm	<b>Dimming</b>	PSR: 1-10VPSD: DALIPSC: Coded mainsSPRD: 1-10V, Step dimming, AOCSR: D4i
<b>Correlated color temperature - CCT</b>	5700K4000K3000K2700K2200K	<b>Operating Temperature range</b>	-40 to +50C Ta
<b>Luminaire efficacy</b>	4000K: 140lm/WOptional 4000K 160lm/W	<b>Ingress protection</b>	IP66
<b>Color Rendering index - 70 CRI</b>		<b>Certification</b>	IECEE CB, CE, CQC, RCM, D4i

## Dimensional drawing



## General Information

CE mark	CE mark
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces

## Light Technical

Color rendering index (CRI)	>70
-----------------------------	-----

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Housing Color	Gray
---------------	------

## Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP66

## General Information

Order Code	Full Product Name	Light source replaceable
911401675506	BRP383 LED199/NW 150W 220-240V DWV P7 HP	-
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	No
911401874298	BRP383 LED374/NW 270W 220-240V DM PSR	No
911401874398	BRP383 LED363/NW 260W 220-240V DM PSR	No
911401874498	BRP383 LED338/NW 240W 220-240V DM PSR	No
911401874598	BRP383 LED326/NW 235W 220-240V DM PSR	No
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	No
911401874798	BRP383 LED292/NW 210W 220-240V DM PSR	No
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	No
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	No
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	No
911401875198	BRP383 LED232/NW 165W 220-240V DM PSR	No
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	No
911401876198	BRP383 LED368/WW 280W 220-240V DM PSR	No
911401876298	BRP383 LED356/WW 270W 220-240V DM PSR	No
911401876398	BRP383 LED346/WW 260W 220-240V DM PSR	No
911401876498	BRP383 LED322/WW 240W 220-240V DM PSR	No
911401876598	BRP383 LED311/WW 235W 220-240V DM PSR	No
911401876698	BRP383 LED300/WW 225W 220-240V DM PSR	No
911401876798	BRP383 LED278/WW 210W 220-240V DM PSR	No
911401876898	BRP383 LED267/WW 200W 220-240V DM PSR	No
911401876998	BRP383 LED255/WW 190W 220-240V DM PSR	No
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	No
911401877198	BRP383 LED221/WW 165W 220-240V DM PSR	No
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	No
911401629107	BRP384 LED455/NW 350W 220-240V DWV P7 HP	-
911401629207	BRP384 LED489/NW 350W DW1 PSR P7	-
911401629307	BRP384 LED489/NW 350W 220-240V DW1 PSR	-
911401629407	BRP384 LED476/WW 350W 220-240V DW1 PSR	-
911401669606	BRP381 LED132/NW 100W 220-240V DWP P7 HP	-
911401675106	BRP381 LED23/NW 20W 220-240V DWP P7 HP	-
911401675206	BRP381 LED45/NW 35W 220-240V DWP P7 HP	-
911401675306	BRP381 LED78/NW 60W 220-240V DWP P7 HP	-
911401675406	BRP381 LED111/NW 90W 220-240V DWP P7 HP	-
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	No
911401869497	BRP381 LED94/WW 70W 220-240V DW2 PSR	No
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	No
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	No
911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	No
911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	No
911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	No
911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	No
911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	No
911401877898	BRP381 LED116/WW 85W 220-240V DM PSR	No
911401877998	BRP381 LED94/WW 70W 220-240V DM PSR	No
911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	No
911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	No
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	No
911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	No
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	No
911401875498	BRP382 LED181/NW 130W 220-240V DM PSR	No

Order Code	Full Product Name	Light source replaceable
911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	No
911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	No
911401877498	BRP382 LED172/WW 130W 220-240V DM PSR	No
911401877598	BRP382 LED162/WW 120W 220-240V DM PSR	No

## Light Technical

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Optical cover type	Luminous Flux
911401675506	BRP383 LED199/NW 150W 220-240V DWV P7 HP	740 neutral white	4000 K	Tempered glass	19,900 lm
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	38,600 lm
911401874298	BRP383 LED374/NW 270W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	37,400 lm
911401874398	BRP383 LED363/NW 260W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	36,300 lm
911401874498	BRP383 LED338/NW 240W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	33,800 lm
911401874598	BRP383 LED326/NW 235W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	32,600 lm
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	31,500 lm
911401874798	BRP383 LED292/NW 210W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	29,200 lm

Order Code	Full Product Name	Light source color	Correlated		
			Color Temperature (Nom)	Optical cover type	Luminous Flux
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	28,000 lm
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	26,800 lm
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	24,300 lm
911401875198	BRP383 LED232/NW 165W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	23,200 lm
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	22,000 lm
911401876198	BRP383 LED368/WW 280W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	36,800 lm
911401876298	BRP383 LED356/WW 270W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	35,600 lm
911401876398	BRP383 LED346/WW 260W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	34,600 lm

## GreenVision Xceed Gen2

Order Code	Full Product Name	Light source color	Correlated Color		
			Temperature (Nom)	Optical cover type	Luminous Flux
911401876498	BRP383 LED322/WW 240W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	32,200 lm
911401876598	BRP383 LED311/WW 235W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	31,100 lm
911401876698	BRP383 LED300/WW 225W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	30,000 lm
911401876798	BRP383 LED278/WW 210W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	27,800 lm
911401876898	BRP383 LED267/WW 200W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	26,700 lm
911401876998	BRP383 LED255/WW 190W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	25,500 lm
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	23,200 lm
911401877198	BRP383 LED221/WW 165W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	22,100 lm
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic	21,000 lm
911401629107	BRP384 LED455/NW 350W	740 neutral white	4000 K	Polycarbonate micro lens optic	45,500 lm

Order Code	Full Product Name	Light source color	Correlated Color		
			Temperature (Nom)	Optical cover type	Luminous Flux
	220-240V DWV P7 HP				
911401629207	BRP384 LED489/NW 350W DW1 PSR P7	740 neutral white	4000 K	Polycarbonate micro lens optic	48,900 lm
911401629307	BRP384 LED489/NW 350W 220-240V DW1 PSR	740 neutral white	4000 K	Polycarbonate micro lens optic	48,900 lm
911401629407	BRP384 LED476/WW 350W 220-240V DW1 PSR	730 warm white	3000 K	Polycarbonate micro lens optic	47,600 lm
911401669606	BRP381 LED132/NW 100W 220-240V DWP P7 HP	740 neutral white	4000 K	Tempered glass	13,200 lm
911401675106	BRP381 LED23/NW 20W 220-240V DWP P7 HP	740 neutral white	4000 K	Tempered glass	2,300 lm
911401675206	BRP381 LED45/NW 35W 220-240V DWP P7 HP	740 neutral white	4000 K	Tempered glass	4,500 lm
911401675306	BRP381 LED78/NW 60W 220-240V DWP P7 HP	740 neutral white	4000 K	Tempered glass	7,800 lm
911401675406	BRP381 LED111/NW 90W 220-240V DWP P7 HP	740 neutral white	4000 K	Tempered glass	11,100 lm
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	730 warm white	3000 K	Polycarbonate micro lens optic	12,700 lm
911401869497	BRP381 LED94/WW 70W	730 warm white	3000 K	Polycarbonate micro lens optic	9,400 lm

## GreenVision Xceed Gen2

Order Code	Full Product Name	Light source color	Correlated Color			Luminous Flux
			Temperature (Nom)	Optical cover type	Optical cover	
	220-240V DW2 PSR					
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		14,500 lm
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		13,300 lm
911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		12,200 lm
911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		9,900 lm
911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		8,700 lm
911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		13,800 lm
911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		12,700 lm
911401877898	BRP381 LED116/WW 85W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		11,600 lm
911401877998	BRP381 LED94/WW 70W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		9,400 lm

Order Code	Full Product Name	Light source color	Correlated Color			Luminous Flux
			Temperature (Nom)	Optical cover type	Optical cover	
911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		8,300 lm
911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		7,500 lm
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		7,100 lm
911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		17,000 lm
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		19,300 lm
911401875498	BRP382 LED181/NW 130W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		18,100 lm
911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	740 neutral white	4000 K	Polycarbonate micro lens optic		17,000 lm
911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		18,400 lm
911401877498	BRP382 LED172/WW 130W 220-240V DM PSR	730 warm white	3000 K	Polycarbonate micro lens optic		17,200 lm
911401877598	BRP382 LED162/WW 120W white	730 warm white	3000 K	Polycarbonate micro lens optic		16,200 lm

# GreenVision Xceed Gen2

Order Code	Full Product Name	Light source color	Correlated Color		
			Temperature (Nom)	Optical cover type	Luminous Flux
	220-240V DM				
	PSR				

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401675506	BRP383 LED199/NW 150W 220-240V DWV P7 HP	150 W
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	280 W
911401874298	BRP383 LED374/NW 270W 220-240V DM PSR	270 W
911401874398	BRP383 LED363/NW 260W 220-240V DM PSR	260 W
911401874498	BRP383 LED338/NW 240W 220-240V DM PSR	240 W
911401874598	BRP383 LED326/NW 235W 220-240V DM PSR	235 W
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	225 W
911401874798	BRP383 LED292/NW 210W 220-240V DM PSR	210 W
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	200 W
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	190 W
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	175 W
911401875198	BRP383 LED232/NW 165W 220-240V DM PSR	165 W
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	160 W
911401876198	BRP383 LED368/WW 280W 220-240V DM PSR	280 W
911401876298	BRP383 LED356/WW 270W 220-240V DM PSR	270 W
911401876398	BRP383 LED346/WW 260W 220-240V DM PSR	260 W
911401876498	BRP383 LED322/WW 240W 220-240V DM PSR	240 W
911401876598	BRP383 LED311/WW 235W 220-240V DM PSR	235 W
911401876698	BRP383 LED300/WW 225W 220-240V DM PSR	225 W
911401876798	BRP383 LED278/WW 210W 220-240V DM PSR	210 W
911401876898	BRP383 LED267/WW 200W 220-240V DM PSR	200 W
911401876998	BRP383 LED255/WW 190W 220-240V DM PSR	190 W
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	175 W
911401877198	BRP383 LED221/WW 165W 220-240V DM PSR	165 W
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	160 W
911401629107	BRP384 LED455/NW 350W 220-240V DWV P7 HP	350 W
911401629207	BRP384 LED489/NW 350W DW1 PSR P7	350 W

Order Code	Full Product Name	Power Consumption
911401629307	BRP384 LED489/NW 350W 220-240V DW1 PSR	350 W
911401629407	BRP384 LED476/WW 350W 220-240V DW1 PSR	350 W
911401669606	BRP381 LED132/NW 100W 220-240V DWP P7 HP	100 W
911401675106	BRP381 LED23/NW 20W 220-240V DWP P7 HP	20 W
911401675206	BRP381 LED45/NW 35W 220-240V DWP P7 HP	35 W
911401675306	BRP381 LED78/NW 60W 220-240V DWP P7 HP	60 W
911401675406	BRP381 LED111/NW 90W 220-240V DWP P7 HP	90 W
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	95 W
911401869497	BRP381 LED94/WW 70W 220-240V DW2 PSR	70 W
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	105 W
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	95 W
911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	85 W
911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	70 W
911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	60 W
911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	105 W
911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	95 W
911401877898	BRP381 LED116/WW 85W 220-240V DM PSR	85 W
911401877998	BRP381 LED94/WW 70W 220-240V DM PSR	70 W
911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	60 W
911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	55 W
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	55 W
911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	120 W
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	140 W
911401875498	BRP382 LED181/NW 130W 220-240V DM PSR	130 W
911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	120 W
911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	140 W
911401877498	BRP382 LED172/WW 130W 220-240V DM PSR	130 W
911401877598	BRP382 LED162/WW 120W 220-240V DM PSR	120 W

## Application Conditions

Order Code	Full Product Name	Maximum dim level
911401675506	BRP383 LED199/NW 150W 220-240V DWV P7 HP	-
911401874198	BRP383 LED386/NW 280W 220-240V DM PSR	10%
911401874298	BRP383 LED374/NW 270W 220-240V DM PSR	10%
911401874398	BRP383 LED363/NW 260W 220-240V DM PSR	10%
911401874498	BRP383 LED338/NW 240W 220-240V DM PSR	10%
911401874598	BRP383 LED326/NW 235W 220-240V DM PSR	10%
911401874698	BRP383 LED315/NW 225W 220-240V DM PSR	10%
911401874798	BRP383 LED292/NW 210W 220-240V DM PSR	10%
911401874898	BRP383 LED280/NW 200W 220-240V DM PSR	10%
911401874998	BRP383 LED268/NW 190W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
911401875098	BRP383 LED243/NW 175W 220-240V DM PSR	10%
911401875198	BRP383 LED232/NW 165W 220-240V DM PSR	10%
911401875298	BRP383 LED220/NW 160W 220-240V DM PSR	10%
911401876198	BRP383 LED368/WW 280W 220-240V DM PSR	10%
911401876298	BRP383 LED356/WW 270W 220-240V DM PSR	10%
911401876398	BRP383 LED346/WW 260W 220-240V DM PSR	10%
911401876498	BRP383 LED322/WW 240W 220-240V DM PSR	10%
911401876598	BRP383 LED311/WW 235W 220-240V DM PSR	10%
911401876698	BRP383 LED300/WW 225W 220-240V DM PSR	10%
911401876798	BRP383 LED278/WW 210W 220-240V DM PSR	10%

## GreenVision Xceed Gen2

Order Code	Full Product Name	Maximum dim level
911401876898	BRP383 LED267/WW 200W 220-240V DM PSR	10%
911401876998	BRP383 LED255/WW 190W 220-240V DM PSR	10%
911401877098	BRP383 LED232/WW 175W 220-240V DM PSR	10%
911401877198	BRP383 LED221/WW 165W 220-240V DM PSR	10%
911401877298	BRP383 LED210/WW 160W 220-240V DM PSR	10%
911401629107	BRP384 LED455/NW 350W 220-240V DWV P7 HP	-
911401629207	BRP384 LED489/NW 350W DW1 PSR P7	-
911401629307	BRP384 LED489/NW 350W 220-240V DW1 PSR	-
911401629407	BRP384 LED476/WW 350W 220-240V DW1 PSR	-
911401669606	BRP381 LED132/NW 100W 220-240V DWP P7 HP	-
911401675106	BRP381 LED23/NW 20W 220-240V DWP P7 HP	-
911401675206	BRP381 LED45/NW 35W 220-240V DWP P7 HP	-
911401675306	BRP381 LED78/NW 60W 220-240V DWP P7 HP	-
911401675406	BRP381 LED111/NW 90W 220-240V DWP P7 HP	-
911401869297	BRP381 LED127/WW 95W 220-240V DW2 PSR	10%
911401869497	BRP381 LED94/WW 70W 220-240V DW2 PSR	10%
911401875698	BRP381 LED145/NW 105W 220-240V DM PSR	10%
911401875798	BRP381 LED133/NW 95W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
911401875898	BRP381 LED122/NW 85W 220-240V DM PSR	10%
911401875998	BRP381 LED99/NW 70W 220-240V DM PSR	10%
911401876098	BRP381 LED87/NW 60W 220-240V DM PSR	10%
911401877698	BRP381 LED138/WW 105W 220-240V DM PSR	10%
911401877798	BRP381 LED127/WW 95W 220-240V DM PSR	10%
911401877898	BRP381 LED116/WW 85W 220-240V DM PSR	10%
911401877998	BRP381 LED94/WW 70W 220-240V DM PSR	10%
911401878098	BRP381 LED83/WW 60W 220-240V DM PSR	10%
911401878198	BRP381 LED75/NW 55W 220-240V DM PSR	10%
911401878298	BRP381 LED71/WW 55W 220-240V DM PSR	10%
911401867097	BRP382 LED170/NW 120W 220-240V DW2 PSR	10%
911401875398	BRP382 LED193/NW 140W 220-240V DM PSR	10%
911401875498	BRP382 LED181/NW 130W 220-240V DM PSR	10%
911401875598	BRP382 LED170/NW 120W 220-240V DM PSR	10%
911401877398	BRP382 LED184/WW 140W 220-240V DM PSR	10%
911401877498	BRP382 LED172/WW 130W 220-240V DM PSR	10%
911401877598	BRP382 LED162/WW 120W 220-240V DM PSR	10%

