



Image
not
available

Platines Faible Puissance EGS350

EGS350 SON-T250W LV

EGS350, SON-T, 250 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Données du produit

Informations générales	
Code famille lampe	SON-T [SON-T]
Code famille de produits	EGS350 [EGS350]
Marquage CE	Oui
Marquage ENEC	Marquage ENEC
Fonctionnement et électricité	
Tension d'entrée	230 V
Consommation électrique	250 W
Approbation et application	
Indice de protection	IP21 [Protection des doigts, protection contre les gouttes]
Classe de protection CEI	Classe de sécurité I

Données du produit	
Nom du produit de la commande	EGS350 SON-T250W LV
Nom de produit complet	EGS350 SON-T250W LV
Code EOC	871155916866100
Code de commande	16866100
Code 12NC	913663010418
Quantité par pack	1
Code EAN – Produit/Boîte	8711559168661
Conditionnement par carton	1
Codes EAN/UPC – Boîte	8711559168661

Platines Faible Puissance EGS350

Schéma dimensionnel

Image
not
available

