



Image
not
available

Platines Faible Puissance EGS350

EGS350 2xSON-T150W LV

EGS350, 2, SON-T, 150 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

Données du produit

Informations générales		Classe de protection CEI		Classe de sécurité I	
Code famille lampe	SON-T [SON-T]				
Code famille de produits	EGS350 [EGS350]				
Marquage CE	Oui				
Marquage ENEC	Marquage ENEC				
Données techniques de l'éclairage		Données du produit			
Nombre de sources lumineuses	2	Nom du produit de la commande	EGS350 2xSON-T150W LV		
Fonctionnement et électricité		Nom de produit complet	EGS350 2xSON-T150W LV		
Tension d'entrée	230 V	Code EOC	871155984882200		
Consommation électrique	150 W	Code de commande	84882200		
Approbation et application		Code 12NC	913665000418		
Indice de protection	IP21 [Protection des doigts, protection contre les gouttes]	Quantité par pack	1		
		Code EAN – Produit/Boîte	8711559848822		
		Conditionnement par carton	1		
		Codes EAN/UPC – Boîte	8711559848822		

Platines Faible Puissance EGS350

Schéma dimensionnel

Image
not
available

