



Image  
not  
available

# Platines Faible Puissance EGS350

## EGS350 2xSON-T400W LV

EGS350, 2, SON-T, 400 W

A range of prewired foot pole gear trays is available for Road Lighting luminaires. A gear tray consists of a metal tray on which electrical components (capacitors, ballast, ignitor), wiring and terminal blocks are mounted. These gear trays are normally used in combination with Road luminaires, which cannot integrate electrical components because of lack of space or because of high temperatures.

### Données du produit

Informations générales		Classe de protection CEI		Classe de sécurité I	
Code famille lampe	SON-T [SON-T]				
Code famille de produits	EGS350 [EGS350]				
Marquage CE	Oui				
Marquage ENEC	Marquage ENEC				
Données techniques de l'éclairage		<b>Données du produit</b>			
Nombre de sources lumineuses	2	Nom du produit de la commande	EGS350 2xSON-T400W LV		
<b>Fonctionnement et électricité</b>		Nom de produit complet	EGS350 2xSON-T400W LV		
Tension d'entrée	230 V	Code EOC	871155916872200		
Consommation électrique	400 W	Code de commande	16872200		
<b>Approbation et application</b>		Code 12NC	913667000418		
Indice de protection	IP21 [Protection des doigts, protection contre les gouttes]	Quantité par pack	1		
		Code EAN – Produit/Boîte	8711559168722		
		Conditionnement par carton	1		
		Codes EAN/UPC – Boîte	8711559168722		

## Platines Faible Puissance EGS350

Schéma dimensionnel

Image  
not  
available

