



Dynalite Phase-Cut Dimmers

DDLE802

Leading Edge Dimmer Controllers are ideal for lighting circuits with resistive and inductive properties, including mains voltage incandescent fittings, neon and low voltage lamps with a compatible electronic transformer. Available in both DIN-rail and wall box configuration, Dynalite supports a vast range of leading edge dimmer controllers with a variety of circuit numbers and sizes to work individually or part of a system, fitting any project requirement. Wall box dimmer controllers have been engineered to achieve rise times of over 100µs producing reduced filament sing, reduced supply voltage noise, resulting in extended lamp life. The dimmers are engineered to be compatible with electronic transformers, requiring less de-rating, therefore allowing full capacity of channel to be utilised.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DDLE802

Full product name	DDLE802
Full product code	871016350500800
Order code	913703000009
Material Nr. (12NC)	913703000009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163505008
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163505015

Dynalite Phase-Cut Dimmers

Dimensional drawing

