



Standard A-shape clear

Stan 100W E27 220-240V A55 CL 1CT/5X10F

Conventional pear-shaped incandescent lamps

Product data

General Information	
Cap-Base	E27
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	1,340 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	220-240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

Product Data	
Order product name	Stan 100W E27 220-240V A55 CL 1CT/5X10F
Full product name	Stan 100W E27 220-240V A55 CL 1CT/5X10F
Full product code	871829112393400
Order code	920056543301
Material Nr. (12NC)	920056543301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500011213
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291123958

Standard A-shape clear

Dimensional drawing



Product	D (max)	D	C (max)
Stan 100W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm

