



# Reflector Flood

## 65BR30/FL55 120V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	620 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	65 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30
Product Data	
Order product name	65BR30/FL55 120V 12/1
Full product name	65BR30/FL55 120V 12/1
Order code	920681036369
Material Nr. (12NC)	920681036369
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677225193
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677225198

# Reflector Flood

## Dimensional drawing



### Product

65BR30/FL55 120V 12/1

