



DuraMax Reflector Flood

65BR30/FL55/LL 120V 4/3

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux (Max)	620 lm
Luminous Flux	610 lm


Operating and Electrical	
Power Consumption	65 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30

Product Data	
Order product name	65BR30/FL55/LL 120V 4/3
Full product name	65BR30/FL55/LL 120V 4/3
Order code	167718
Material Nr. (12NC)	920681636372
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677167745
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677167719

DuraMax Reflector Flood

Dimensional drawing



Product

65BR30/FL55/LL 120V 4/3

