



Reflector PAR38 Krypton

Refl 250W Med Skt 120-130V PAR38 FL 1CT

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These PAR Krypton flood lamps are available with medium skirted bases.

Product data

General Information	
Cap-Base	E26/50X39 [Skirted Medium Screw (PAR Lamps)]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Beam Angle (Nom)	30 degree(s)
Luminous Flux	3,100 lumen
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	250 W
Voltage (Nom)	120-130 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]

Product Data	
Full product code	904667737432715
Order product name	Refl 250W Med Skt 120-130V PAR38 FL 1CT
Order code	923834636104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	923834636104
Full product name	Refl 250W Med Skt 120-130V PAR38 FL 1CT
EAN/UPC - Case	50046677374322
EAN/UPC - Product/Case	046677374327

Reflector PAR38 Krypton

Dimensional drawing



Product	D (max)	C (max)	C1
Refl 250W Med Skt 120-130V PAR38 FL 1CT	122.5 mm	135 mm	121 mm

