



Halogen non-reflector

7748XHP EHJ-S 250W G6.35 24V

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Cap-Base	G6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	50 hour(s)

Light Technical	
Correlated Color Temperature (Nom)	3550 K
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	250 W
Voltage (Nom)	24 V
Voltage (Nom)	24 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	7748XHP EHJ-S 250W G6.35 24V
Full product name	7748XHP EHJ-S 250W G6.35 24V
Full product code	871150041029050
Order code	924006520503
Material Nr. (12NC)	924006520503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410290
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500423153

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7748XHP EHJ-	12.5 mm	32.75	33.25	33	1.05 mm	1 mm	0.95	55 mm
S 250W G6.35		mm	mm	mm			mm	
24V								

