



MR16

50MR16/FL36 EXN 50PK

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50.0 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	50MR16/FL36 EXN 50PK
Order code	924047417122
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	924047417122
Full product name	50MR16/FL36 EXN 50PK
EAN/UPC - Case	50046677378054
EAN/UPC - Product/Case	046677378059

MR16

Dimensional drawing



Product	D (max)	C (max)
50MR16/FL36 EXN 50PK	51 mm	46 mm

