



Halogen non-reflector

14623 95W G6.35 17V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


Product data

General Information	
Cap-Base	G6.35
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	2,000 hour(s)
Light Technical	
Color rendering index (CRI)	-
Operating and Electrical	
Power Consumption	95 W
Voltage (Nom)	17 V
Voltage (Nom)	17 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	14623 95W G6.35 17V 1CT/10X10F
Full product name	14623 95W G6.35 17V 1CT/10X10F
Full product code	871150042667350
Order code	924049819103
Material Nr. (12NC)	924049819103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500426673
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500426697

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14623 95W	11.5 mm	31.5 mm	32.25	32	1.05 mm	1 mm	0.95 mm	50 mm
G6.35 17V			mm	mm				
1CT/10X10F								

