



Halogen reflector

13865 75W G5.3/4.8 12V 1CT/10X5F


Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data

General Information		Mechanical and Housing	
Cap-Base	G5.3	Bulb Material	Quartz-UV Open
Operating Position	UNIVERSAL [Any or Universal (U)]	Reflector Finish	Smooth
Life to 50% Failures (Nom)	35 hour(s)	Bulb Shape	R35
Light Technical		Product Data	
Color rendering index (CRI)	100	Order product name	13865 75W G5.3/4.8 12V 1CT/10X5F
		Full product name	13865 75W G5.3/4.8 12V 1CT/10X5F
Operating and Electrical		Full product code	871869668102200
Power Consumption	75 W	Order code	924060017101
Voltage (Nom)	12 V	Material Nr. (12NC)	924060017101
Voltage (Nom)	12 V	Numerator - Quantity Per Pack	1
Controls and Dimming		EAN/UPC - Product/Case	8718696681022
Dimmable	Yes	Numerator - Packs per outer box	50
		EAN/UPC - Case	8718696681046

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
13865 75W G5,3/4.8 12V 1CT/10X5F	35 mm	35.5 mm

