



DuraMax Deco Globe

40G25/W/LL 120V 12/1 TP

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	370 lm
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	White

Bulb Shape	G25
Product Data	
Order product name	40G25/W/LL 120V 12/1 TP
Full product name	40G25/W/LL 120V 12/1 TP
Order code	925244036357
Material Nr. (12NC)	925244036357
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677167462
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677167467

DuraMax Deco Globe

Dimensional drawing

Product

40G25/W/LL 120V 12/1 TP

