



DuraMax Deco Globe

BC40G16-1/2C/CL/LL 120V 6/2TP

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	300 lm
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	G16.5 [G16.5]
Product Data	
Order product name	BC40G16-1/2C/CL/LL 120V 6/2TP
Full product name	BC40G16-1/2C/CL/LL 120V 6/2TP
Order code	925261636308
Material Nr. (12NC)	925261636308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168469
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677168464

DuraMax Deco Globe

Dimensional drawing

Product

BC40G16-1/2C/CL/LL 120V 6/2TP

