



Silicone Coated Rough Service

100A/RS/TF 120-130V 60PK

The Philips Family of Silicone Coated Rough Service bulbs are the perfect choice in areas where there is concern if a bulb drops or shatters. Since Silicone Coated Rough Service bulbs resist breakage or shattering, they are perfect for food serving areas, as well as, standard, industrial rough surface, appliance and sign use.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	1,050 lm


Operating and Electrical	
Power Consumption	100 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120-130 V

Mechanical and Housing	
Bulb Finish	Frost Silicone
Bulb Shape	A21 [A 21mm]

Product Data	
Order product name	100A/RS/TF 120-130V 60PK
Full product name	100A/RS/TF 120-130V 60PK
Order code	149716
Material Nr. (12NC)	925286736303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677279851
Numerator - Packs per outer box	60
EAN/UPC - Case	50046677149715

Silicone Coated Rough Service

Dimensional drawing



Product

100A/RS/TF 120-130V 60PK

