



# DuraMax Deco Blunt Tip

## BC60B10-1/2C/CL/LL 120V 6/2TP

Philips DuraMax® Long Life Decorative blunt tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative blunt tip bulbs are available in a variety of shapes, sizes and wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent

  

Light Technical	
Luminous Flux	550 lm

  

Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

  

Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	B10 1/2
------------	---------

  

Product Data	
Order product name	BC60B10-1/2C/CL/LL 120V 6/2TP
Full product name	BC60B10-1/2C/CL/LL 120V 6/2TP
Order code	925288736309
Material Nr. (12NC)	925288736309
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168261
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677168266

## DuraMax Deco Blunt Tip

### Dimensional drawing

#### Product

BC60B10-1/2C/CL/LL 120V 6/2TP

