



Halogen A19

43A19/EV 120V 12/2

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Halogen
Operating and Electrical	
Power Consumption	43 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	White
Bulb Material	Glass

Bulb Shape	A19 [A 19mm]
Product Data	
Order product name	43A19/EV 120V 12/2
Full product name	43A19/EV 120V 12/2
Order code	925701736301
Material Nr. (12NC)	925701736301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409845
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677409840

Halogen A19

Dimensional drawing



Product	D	C (max)
43A19/EV 120V 12/2	2.375 inch	4.13 inch

