



# Mini-Candelabra

## BC100Q/CL ESN 12/1P

Bright, white light with higher performance for accent lighting. Halogen Mini Candelabra T4 Capsule lamps provide bright, white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with mini candelabra base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product. Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

### Product data

General Information	
Cap-Base	E11 [Mini Candelabra]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T-4
Product Data	
Order product name	BC100Q/CL ESN 12/1P
Full product name	BC100Q/CL ESN 12/1P
Order code	926000850098
Material Nr. (12NC)	926000850098
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677416331
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677416336

## Mini-Candelabra

### Dimensional drawing

#### Product

BC100Q/CL ESN 12/1P

