



# U-Bent Rapid Start T8

## FB31T8/TL830/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

| General Information                |  |
|------------------------------------|--|
| Cap-Base                           | G13 [Medium Bi-Pin Fluorescent]                    |
| Features                           | ALTO® (ALTO)                                       |
| Light Technical                    |  |
| Color Code                         | TL830 [CCT of 3000K (830)]                         |
| Luminous Flux                      | 2,750 lm   |
| Color Designation                  | TL830  |
| Correlated Color Temperature (Nom) | 3000 K   |
| Color rendering index (CRI)        | 85   |
| Operating and Electrical           |  |
| Power Consumption                  | 31 W   |
| Mechanical and Housing             |  |
| Bulb Shape                         | T8-1-5/8U [U-bent T 1inch with 1-5/8" leg spacing] |

| Approval and Application        |                        |
|---------------------------------|------------------------|
| Energy Saving Product           | Energy Saving          |
| Mercury (Hg) Content (Nom)      | 3.0 mg                 |
| Product Data                    |                        |
| Order product name              | FB31T8/TL830/ALTO 15/1 |
| Full product name               | FB31T8/TL830/ALTO 15/1 |
| Order code                      | 927861283002           |
| Material Nr. (12NC)             | 927861283002           |
| Numerator - Quantity Per Pack   | 1                      |
| EAN/UPC - Product/Case          | 046677226718           |
| Numerator - Packs per outer box | 15                     |
| EAN/UPC - Case                  | 50046677226713         |

## U-Bent Rapid Start T8

### Dimensional drawing

#### Product

FB31T8/TL830/ALTO 15/1

