



High CRI T12

F40T12/C50Supreme/ALTO 30pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Luminous Flux | 2,545 lm |
| Color Designation | C50 Supreme |
| Correlated Color Temperature (Nom) | 5000 K |
| Color rendering index (CRI) | 90 |
| Operating and Electrical | |
| Power Consumption | 40 W |
| Mechanical and Housing | |
| Bulb Shape | T-12 (T12) |

| Approval and Application | |
|---------------------------------|-----------------------------|
| Energy Saving Product | Energy Saving |
| Mercury (Hg) Content (Nom) | 4.4 mg |
| Product Data | |
| Order product name | F40T12/C50Supreme/ALTO 30pk |
| Full product name | F40T12/C50Supreme/ALTO 30pk |
| Order code | 927888000213 |
| Material Nr. (12NC) | 927888000213 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677423896 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 50046677423891 |

High CRI T12

Dimensional drawing

Product

F40T12/C50Supreme/ALTO 30pk

