



# Retail Sales T12

## F40T12/PLANT/48 6PK

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		Mercury (Hg) Content (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		16.0 mg
Light Technical		Product Data	
Color Code	7	Order product name	F40T12/PLANT/48 6PK
Luminous Flux	1,600 lm	Full product name	F40T12/PLANT/48 6PK
Color Designation	Plant and Aquarium (PLANT)	Order code	392282
Operating and Electrical		Material Nr. (12NC)	92788000702
Power Consumption	40 W	Numerator - Quantity Per Pack	1
Mechanical and Housing		EAN/UPC - Product/Case	046677392284
Bulb Shape	T-12 (T12)	Numerator - Packs per outer box	6
Approval and Application		EAN/UPC - Case	50046677392289
Energy Saving Product	Not Applicable		

## Retail Sales T12

### Dimensional drawing

**Product**

F40T12/PLANT/48 6PK

