



# Slimline T12

## Slimline F48T12/D/ALTO 15PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	FA8 [FA8]
Features	ALTO® (ALTO)
Light Technical	
Color Code	54
Luminous Flux	2,500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	39 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F48T12/D/ALTO 15PK
Full product name	Slimline F48T12/D/ALTO 15PK
Order code	362194
Material Nr. (12NC)	927890005402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677362195
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677362190

## Slimline T12

### Dimensional drawing

#### Product

F48T12/D/ALTO 15PK

