



# Slimline T12

## Slimline F72T12/CW ALTO 15PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	FA8 [FA8]
Features	ALTO® (ALTO)

  

Light Technical	
Color Code	33
Luminous Flux	4,450 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62

  

Operating and Electrical	
Power Consumption	56 W

  

Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg

  

Product Data	
Order product name	F72T12/CW ALTO 15PK
Full product name	Slimline F72T12/CW ALTO 15PK
Order code	369892
Material Nr. (12NC)	927893003308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677369897
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677369892

# Slimline T12

## Dimensional drawing

### Product

F72T12/CW ALTO 15PK

