



# TUV PL-L

## TUV PL-L 24W/4P UNP/50

TUV PL-L lamps are compact UV-C lamps emitting a peak at 253.7 nm. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime. Thanks to the single-ended lamp base, lamp replacement is easy.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

### Product data


General Information		Voltage (Nom)	
Cap-Base	2G11	87 V	
Useful Life (Nom)	9,000 hour(s)	Mechanical and Housing	
<b>Light Technical</b>		Bulb Shape	2xT16
Color Code	TUV	Approval and Application	
Color Designation	- [Not Specified]	Mercury (Hg) Content (Nom)	4.4 mg
Depreciation at Useful Lifetime	20 %	UV	
<b>Operating and Electrical</b>		UV-C Radiation at 100 hr	7.6 W
Power Consumption	24 W	Product Data	
Lamp Current (Nom)	0.345 A	Order product name	TUV PL-L 24W/4P UNP/50
Voltage (Nom)	87 V	Full product name	TUV PL-L 24W/4P UNP/50

# TUV PL-L

Full product code	871150061294665
Order code	927903204016
Material Nr. (12NC)	927903204016
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500612946


Numerator - Packs per outer box	50
EAN/UPC - Case	8711500612953

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 24W/4P UNP/50	18 mm	39 mm	290 mm	315 mm	320 mm

## Photometric data



Spectral Power Distribution Colour - TUV PL-L 24W/4P UNP/50

