



PL-T Triple 4-Pin Base

PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	GX24Q-3 [GX24q-3]
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,750 lm
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	64.8 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	27.0 W

Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO
Full product name	PL-T 26W/827/A/4P 1CT/5X10BOX ALTO
Order code	458240
Material Nr. (12NC)	927910982750
Numerator - Quantity Per Pack	1

PL-T Triple 4-Pin Base


EAN/UPC - Product/Case	046677384401
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677458244

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/827/A/4P 1CT/5X10BOX ALTO	1-5/8 inch	3-7/16 inch	4-3/8 inch	5 inch

Photometric data




Spectral Power Distribution Colour - PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

Lifetime




Lumen Maintenance Diagram - PL-T 26W/827/A/4P 1CT/5X10BOX ALTO



Life Expectancy Diagram - PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

PL-T Triple 4-Pin Base

Lifetime



Life Expectancy Diagram - PL-T 26W/827/A/4P 1CT/5X10BOX ALTO

