



MASTER PL-S 2 Pin



MASTER PL-S 9W/840/2P 1CT/5X10CC

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G23		67 lm/W
Flux measurement reference	Sphere	Color rendering index (CRI)	80
Life to 50% Failures (Nom)	10,000 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	8.8 W
Color Code	840 [CCT of 4000K]	Lamp Current (Nom)	0.170 A
Luminous Flux	590 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Chromaticity Coordinate X (Nom)	0.38	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.38	Energy Efficiency Class	G
Correlated Color Temperature (Nom)	4000 K		

MASTER PL-S 2 Pin


Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	9 kWh
EPREL Registration Number	423591

Product Data

Order product name	MASTER PL-S 9W/840/2P 1CT/5X10CC
Full product name	MASTER PL-S 9W/840/2P 1CT/5X10CC
Full product code	871150026087170


Order code	927936084011
Material Nr. (12NC)	927936084011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260871
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500260895

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 9W/840/2P 1CT/5X10CC	28 mm	13 mm	129 mm	145 mm	167 mm



Photometric data



Spectral Power Distribution Colour - MASTER PL-S 9W/840/2P 1CT/5X10CC


MASTER PL-S 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-S 9W/840/2P 1CT/5X10CC

Life Expectancy Diagram - MASTER PL-S 9W/840/2P 1CT/5X10CC



Lumen Maintenance Diagram - MASTER PL-S 9W/840/2P 1CT/5X10CC

