



MASTER TL5 High Efficiency Eco 高效率省電日光燈管

MASTER TL5 HE Eco 25=28W/830 UNP/40

直徑 16 mm 的螢光燈管

安全提示

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊		演色性指數 (CRI)		82
燈座基底	G5 [G5]	運轉與電力		
功能	na [Not Applicable]	耗電量	25.4 W	
通量測量參考	Sphere	燈具電流 (標稱)	0.170 A	
照明技術		控制與調光		
色碼	830 [CCT of 3000K]	可調光	是	
光通量	2,520 lm	機械與外罩		
色彩名稱	暖白光 (WW)	燈泡形狀	T5 [16 mm (T5)]	
色度坐標 x (標稱)	0.44	認證與應用		
色度坐標 Y (Nom)	0.403	節能省電等級	F	
相關色彩溫度 (規範)	3000 K			
光效 (額定) (標準)	103 lm/W			

MASTER TL5 High Efficiency Eco 高效率省電日光燈管

汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	26 kWh
EPREL 註冊碼	423467
產品資料	
下訂產品名稱	MASTER TL5 HE Eco 25=28W/830 UNP/40
完整產品名稱	MASTER TL5 HE Eco 25=28W/830 UNP/40
完整產品代碼	872790082588600


訂單代碼	927990983031
材質 Nr. (12NC)	927990983031
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500880000
分子 - 每一外盒包裝	40
EAN/UPC - 箱	8727900825886

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/830 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm


光度数据




Spectral Power Distribution Colour - MASTER TL5 HE Eco 25=28W/830 UNP/40

MASTER TL5 High Efficiency Eco 高效率省電日光燈管


壽命



Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/830 UNP/40



Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/830 UNP/40



Lumen Maintenance Diagram - MASTER TL5 HE Eco 25=28W/830 UNP/40

