



MASTER TL5 High Efficiency Eco 高效率省電日光燈管

MASTER TL5 HE Eco 25=28W/830 1SL/40

直徑 16 mm 的螢光燈管

安全提示

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5 [G5]
功能	na [Not Applicable]
照明技術	
色碼	830 [CCT of 3000K]
光通量	2,900 lm
色彩名稱	暖白光 (WW)
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	103 lm/W
演色性指數 (CRI)	82
運轉與電力	
耗電量	25.2 W


燈具電流 (標稱)	0.170 A
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T5 [16 mm (T5)]
認證與應用	
汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	28 kWh
產品資料	
下訂產品名稱	MASTER TL5 HE Eco 25=28W/830 1SL/40

MASTER TL5 High Efficiency Eco 高效率省電日光燈管

完整產品名稱	MASTER TL5 HE Eco 25=28W/830 1SL/40
完整產品代碼	872790090818301
訂單代碼	927990983033
材質 Nr. (12NC)	927990983033
分子 - 每個包裝的數量	1


EAN/UPC - 產品/案例	8727900908183
分子 - 每一外盒包裝	40
EAN/UPC - 箱	8718291224709

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/830 1SL/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 HE Eco 25=28W/830 1SL/40

壽命




Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/830 1SL/40



Life Expectancy Diagram - MASTER TL5 HE Eco 25=28W/830 1SL/40

MASTER TL5 High Efficiency Eco 高效率省電日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL5 HE Eco 25=28W/830 1SL/40

