



T5 Preheat

F13T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Product data

| General Information | |
|----------------------------|---------------|
| Cap-Base | G5 |
| Life to 50% Failures (Nom) | 8,000 hour(s) |

| Light Technical | |
|------------------------------------|-----------------|
| Color Code | 33-640 |
| Luminous Flux | 930 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4100 K |
| Luminous Efficacy (rated) (Nom) | 71 lm/W |
| Color rendering index (CRI) | 60 |

| Operating and Electrical | |
|--------------------------|---------|
| Power Consumption | 13.0 W |
| Lamp Current (Nom) | 0.170 A |
| Voltage (Nom) | 90 V |
| Voltage (Nom) | 90 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|----|
| Bulb Shape | T5 |


| Approval and Application | |
|-------------------------------|--------|
| Mercury (Hg) Content (Nom) | 4.4 mg |
| Energy Consumption kWh/1000 h | 14 kWh |

| Product Data | |
|---------------------------------|------------------|
| Order product name | F13T5/CW PH 25PK |
| Full product name | F13T5/CW PH 25PK |
| Order code | 928001503332 |
| Material Nr. (12NC) | 928001503332 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677115142 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 50046677115147 |


T5 Preheat

Dimensional drawing

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|------------------|---------|----------|----------|----------|----------|
| F13T5/CW PH 25PK | 16 mm | 516.9 mm | 524.0 mm | 521.6 mm | 531.1 mm |



Photometric data



Spectral Power Distribution Colour - F13T5/CW PH 25PK

