



# TL-E LIFEMAX

## Standard Colours JIS

### TL-E 30W/54 JIS 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important. The lamp complies with the Japanese Industrial Standard.


#### 产品数据

一般資訊	
燈座基底	G10Q [G10q]
標稱使用壽命	8,000 h
壽命 (故障率 50%) (標稱)	13,000 h
照明技術	
色碼	54
光通量	1,410 lm
色彩名稱	冷日光色
相關色彩溫度 (規範)	6200 K
光效 (額定) (標準)	47 lm/W
演色性指數 (CRI)	75
運轉與電力	
耗電量	28.0 W
燈具電流 (標稱)	0.600 A
電壓 (標稱)	55 V
電壓 (標稱)	55 V

控制與調光	
可調光	否
機械與外罩	
燈泡形狀	C-T9 [C-T9 29 mm]
產品資料	
下訂產品名稱	TL-E 30W/54 JIS 1CT/20
完整產品名稱	TL-E 30W/54 JIS 1CT/20
完整產品代碼	871150064034502
訂單代碼	928026105436
材質 Nr. (12NC)	928026105436
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500640345
分子 - 每一外盒包裝	20
EAN/UPC - 箱	8711500640352

## TL-E LIFEMAX Standard Colours JIS

### 二维绘图



Product	E (min)	E (max)	I (min)	I (max)
TL-E 30W/54 JIS 1CT/20	220.5 mm	225.5 mm	163.5 mm	167 mm

