



TL-D Standard Colours

TL-D 18W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h
Light Technical	
Colour code	54-765
Luminous flux (nom.)	1050 lm
Colour designation	Cool Daylight
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Correlated colour temperature (nom.)	6200 K
Color rendering index (nom.)	72
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	59 V


Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	871150070267840
Order product name	TL-D 18W/54-765 1SL/25
EAN/UPC – product	8711500702678
Order code	70267840
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048005436
Net weight (piece)	0.070 kg
ILCOS Code	FD-18/62/2A-E-G13

TL-D Standard Colours

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Dimensional drawing



TL-D 18W/54-765



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data



Lightcolour /54-765

Lifetime



TL-D Standard Colours

Lifetime

